



# Industrial Specification Grade Hart-Lock® Locking Devices

**3 Pole, 4 Wire Grounding**  
**NEMA L14-30, 30A 125/250V**  
**NEMA L15-30, 30A 250V 3Ø**  
**NEMA L16-30, 30A 480V 3Ø**  
**NEMA L17-30, 30A 600V 3Ø**

## 30A 3 Pole, 4 Wire Industrial Specification Grade Flanged Inlet and Outlet

### FEATURES

- All nylon construction.
- Mounting holes interchangeable with competitive units.
- Back wire terminal clamps for easy secure wiring.
- Individual wiring compartments with tapered channel for easy insertion of wires.
- Combination head screws standard – slot/Phillips in the US.
- Add -C to catalog number for Canadian screws – slot/Robertson head combination.



**CWL1430FI**



**CWL1530FI**



**CWL1730FI**

### Industrial Specification Grade Flanged Inlets and Outlets

Rating A	V/AC	NEMA	Color	Catalog No.	
				Inlet	Outlet
30	125/250	L14-30	Black & White	CWL1430FI	CWL1430FO
30	250V 3Ø	L15-30	Black & White	CWL1530FI	CWL1530FO
30	480V 3Ø	L16-30	Black & White	CWL1630FI	CWL1630FO
30	600V 3Ø	L17-30	Black & White	CWL1730FI	CWL1730FO

NOTE: Weather Protective Covers and Enclosures from Cooper Wiring Devices that may be used with these products are described on pages E-71, E-73 and E-74 in this section.

INDUSTRIAL  
COMMERCIAL

**E-23**  
LOCKING  
DEVICES

### TESTING & CODE COMPLIANCE

- Listed to UL 498 Flanged Inlets: (file no. E3663); Flanged Outlets (file no. E2369).
- cUL Certified to CSA C22.2 no.42 (file no. E3663 and E2369).

### MATERIAL CHARACTERISTICS

Nylon.  
 Environmental flammability per UL 94 requirements, V2 rated.  
 Temperature Rating: -40°C to 80°C.

