



# Industrial Specification Grade Hart-Lock® Locking Devices

4 Pole, 5 Wire Grounding  
 NEMA L21-30, 30A 120/208V 3ØY  
 NEMA FSL4-30, 30A 120/208V 3ØY 400Hz  
 NEMA L22-30, 30A 277/480V 3ØY  
 NEMA L23-30, 30A 347/600V 3ØY

INDUSTRIAL  
COMMERCIAL


## E-31 LOCKING DEVICES

### TESTING & CODE COMPLIANCE


· Listed to UL 498 (file no. E2369) except Flanged Inlets: (file no. E3663).  
 CWL2130R  
 UL Listed to Federal Spec. WC-596.  
 Receptacles:  
 · CSA Certified to C22.2 no. 42 (file no. LR7087)  
 Inlets and Outlets:  
 cUL Certified to CSA C22.2 no. 42, Inlets (file no. E3663), Outlets (file no. E2369).

### MATERIAL CHARACTERISTICS

Glass filled Nylon  
 Environmental:  
 Flammability per UL 94 requirements.  
 VO rated except FSL430R,  
 Inlets/Outlets:  
 V2 rated.  
 Temperature Rating:  
 -40°C to 105°C except FSL430R:  
 -40°C to 60°C.  
 Inlets/Outlets:  
 -40°C to 80°C.



**CWL2130R**



**FSL430R**



**CWL2130FI**



**CWL2330FO**

## 30A 4 Pole, 5 Wire Non-Grounding Industrial Specification Grade Locking Receptacles

### FEATURES

- Rugged fiberglass reinforced nylon body.
- Clearly marked rating, NEMA configuration and approval listings on receptacle face.
- One piece brass contacts offer superior performance and minimum heat rise.
- Back wire terminal clamps for secure wiring.
- Combination head screws standard - slot/Phillips in the U.S.
- Add -C to catalog number for Canadian screws - slot/Robertson head combination.
- Safety ground clip provided for fast installation.

### Industrial Specification Grade Single Receptacles - Back and Side Wire

Rating	A	V/AC	NEMA	Description	Color	Catalog No.
30	120/208V	3ØY	L21-30	Standard	Black	CWL2130R
				Isolated Ground	Orange	IGL2130R
30	120/208V	3ØY 400HZ	FSL4-30	Standard	Black	FSL430R*
				Isolated Ground	Orange	IGL2230R
30	277/480V	3ØY	L22-30	Standard	Black	CWL2230R
				Isolated Ground	Orange	IGL2230R
30	347/600V	3ØY	L23-30	Standard	Black	CWL2330R
				Isolated Ground	Orange	IGL2330R

\*UL (file no. 2558), CSA (file no. LR16215), Urea.

## 30A 4 Pole, 5 Wire Industrial Specification Grade Flanged Inlet and Outlet

### FEATURES

- All nylon construction.
- Mounting holes interchangeable with competitive units.
- Back wire terminal clamps for easy secure wiring.
- Individual wiring compartments with tapered channel for easy insertion of wires.
- Combination head screws standard - slot/Phillips in the U.S.
- Add -C to catalog number for Canadian screws - slot/Robertson head combination.

### Industrial Specification Grade Flanged Inlets and Outlets

Rating	A	V/AC	NEMA	Color	Catalog No.	
					Inlet	Outlet
30	120/208V	3ØY	L21-30	Black & White	CWL2130FI	CWL2130FO
30	277/480V	3ØY	L22-30	Black & White	CWL2230FI	CWL2230FO
30	347/600V	3ØY	L23-30	Black & White	CWL2330FI	CWL2330FO

NOTE: Weather Protective Covers and Enclosures from Cooper Wiring Devices that may be used with these products are described on pages E-71, E-73 and E-74 in this section.



# Industrial Specification Grade Hart-Lock® Locking Devices

4 Pole, 5 Wire Grounding  
 NEMA L21-30, 30A 120/208V 3ØY  
 NEMA FSL4-30, 30A 120/208V 3ØY 400Hz  
 NEMA L22-30, 30A 277/480V 3ØY  
 NEMA L23-30, 30A 347/600V 3ØY



INDUSTRIAL COMMERCIAL

## E-32 LOCKING DEVICES

### TESTING & CODE COMPLIANCE

· Listed to UL 498 (file no. E3663) except FSL430P, FSL430C (file no. E1381).  
 cUL Certified to CSA C22.2 no. 42 (file no. E3663) except FSL430P and FSL430C:  
 CSA Certified to C22.2 no. 42 (file no. LR16215).

### MATERIAL CHARACTERISTICS

Nylon.  
 Temperature Rating: -40°C to 75°C except FSL430P, FSL430C: -40°C to 60°C.

### 30A 4 Pole, 5 Wire Grounding Industrial Specification Grade Plugs and Connectors

#### FEATURES

- Nylon construction.
- Back wire Dead-Front design.
- Neoprene gasket seals cord hole from dust and debris.
- Inserts included for three separate cord grip ranges.
- Back wire terminal clamps for secure wiring.
- Individual wiring compartments with tapered channel for easy insertion of wires.
- Clear cover allows easy inspection of wiring terminations.
- Combination head screws standard - slot/Phillips in the U.S.
- Add -C to catalog number for Canadian screws - slot/Robertson head combination.

#### Industrial Specification Grade Locking Plugs and Connectors

Rating A	V/AC	NEMA	Cord Diameter	Color	Catalog No.	
					Plug	Connector
30	120/208V 3ØY	L21-30	0.63"-1.16" (15.9mm-29.4mm)	Black & White	CWL2130P	CWL2130C
			0.63"-1.16" (15.9mm-29.4mm)	Black	6612BK	6614BK
30	120/208V 3ØY 400Hz	FSL4-30	0.47"-1.15" (11.9mm-29.2mm)	Black & White	FSL430P	FSL430C
30	277/480V 3ØY	L22-30	0.63"-1.16" (15.9mm-29.4mm)	Black & White	CWL2230P	CWL2230C
30	347/600V 3ØY	L23-30	0.63"-1.16" (15.9mm-29.4mm)	Black & White	CWL2330P	CWL2330C

NOTE: Weather Protective Boots from Cooper Wiring Devices that may be used with these products are described on page E-72 in this section.

