

2 MP HDCVI PTZ Camera

30x Starlight IR WDR





- 1/2.8-in. 2 MP STARVIS™ Progressive-scan CMOS Sensor
- Powerful 30x Optical Zoom
- Supports Multiple Video Formats: HDCVI, CVBS, AHD and TVI
- Starlight Technology for Ultra-low Light Sensitivity
- 1080p at 30 fps or 720p at 30/60 fps, Maximum Resolution
- True Wide Dynamic Range (120 dB), 3D DNR
- Maximum IR Distance up to 150 m (492 ft)
- IP66 Ingress Protection
- Designed for Extreme Temperature Environments
- Five-year Warranty*









System Overview

The 2 MP Starlight IR PTZ Dome camera features a 1/2.8-in. STARVIS™ CMOS imager with a 30x optical zoom lens, and provides an all in one solution for capturing long-distance video surveillance for outdoor applications, day or night. The camera offers a built-in heater and IP66 Ingress Protection to extend its use to the harshest environments. The PTZ camera is equipped with quick and accurate pan/tilt/zoom control and True WDR for applications with direct sunlight or glare.

Functions

Starlight Technology

For challenging low-light applications, Dahua's Starlight Ultra-low Light Technology offers light sensitivity that captures details in low light down to 0.005 lux. The camera uses a set of optical features to balance light throughout the scene, resulting in clear images in dark environments.

Multi-Format Output Support

The camera supports multiple video formats including, HDCVI, CVBS, AHD, and TVI. The camera can switch between these four formats via the OSD menu making the camera compatible with not only HDCVI DVRs but also most existing HD/SD DVRs.

Simplicity

HDCVI technology seamlessly integrates traditional analog surveillance systems with upgraded, high-quality HD video, making it the best choice to protect security investments. The plug and play approach enables full HD video surveillance without the hassles of configuring a network.

Dual Video Output Signals

The camera offers one (1) BNC video output connection to transmit either an HDCVI or a CVBS signal. These output signals allow the camera to integrate with various devices, including analog matrix systems and monitors.

True Wide Dynamic Range

The camera achieves vivid images, even in the most intense contrast lighting conditions, using industry-leading wide dynamic range (WDR) technology. For applications with both bright and low lighting conditions that change quickly, True WDR (120 dB) optimizes both the bright and dark areas of a scene at the same time to provide usable video.

Defog

Utilizing Dahua's advanced algorithm technology, the Defog feature dynamically adjusts the camera's contrast settings to provide improved image quality in scenes affected by fog, smog, mist, smoke or other low-contrast interference.

Environmental

With a built-in heater and a temperature range of $-40\,^{\circ}\text{C}$ to $+60\,^{\circ}\text{C}$ ($-40\,^{\circ}\text{F}$ to $+140\,^{\circ}\text{F}$), the camera is designed for extreme temperature environments. Subjected to rigorous dust and water immersion tests and certified to the IP66 Ingress Protection rating makes it suitable for demanding outdoor applications.

Protection

This camera suits even the harsh conditions for outdoor applications. Its 6KV lightning rating provides protection against the camera and its structure from the effects of lightning.

Technical Specification Camera 1/2.8 in. STARVIS™ CMOS Image Sensor 1920(H) x 1080(V), 2 MP **Effective Pixels** Scanning System Progressive Electronic Shutter Speed 1/3 s to 1/300,000 s Color: 0.005 lux at F1.6 Minimum Illumination 0 lux at F1.6 with IR on S/N Ratio More than 55 dB Distance up to 150.0 m (492.13 ft) IR Distance IR On/Off Control Auto/Manual IR LEDs Four (4) Lens Focal Length 4.5 mm to 135 mm Max. Aperture F1.6 to F5.0 Angle of View Horizontal: 2.4° to 67.8° Optical Zoom **Focus Control** Auto, Manual Close Focus Distance 100 mm to 1000 mm (3.94 in. to 39.37 in.) DORI Distance¹

Detect (8 ppf)	Observe (19 ppf)	Recognize (38 ppf)	Identify (76 ppf)
1862 m (6109 ft)	744 m (2441 ft)	372 m (1220 ft)	186 m (610 ft)

PTZ

Pan/Tilt Range	Pan: 0° to 360° endless; Tilt: –15° to 90° Auto flip 180°
Manual Control Speed	Pan: 0.1° to 300° /s; Tilt: 0.1° to 200° /s
Preset Speed	Pan: 400° /s Tilt: 300° /s
Presets	300
PTZ Mode	5 Pattern, 8 Tour, Auto Pan, Auto Scan
Speed Setup	Human-oriented Focal Length / Speed Adaptation
Power up Action	Auto restore to previous PTZ and lens status after power failure
Idle Motion	Activate Preset, Scan, Tour, Pattern if there is no command in the specified period
Protocol	DH-SD, Pelco-P/D (Auto recognition)

The DORI distance is a measure of the general proximity for a specific classification to help pinpoint the right camera for your needs. The DORI distance is calculated based on sensor specifications and lab test results according to EN 62676-4, the standard that defines the criteria for the Detect, Observe, Recognize and Identify classifications.

Video

Resolution	1080p (1920 × 1080) 720p (1280 × 720)	
Frame Rate	1080p at 30 fps or 720p at 30/60 fps	
Video Output	One (1) Channel, BNC High-definition Video Output (HDCVI, AHD, TVI) or CVBS Standard Definition Video Output (switchable)	
	RG-59/U Coax	720p: 500 m (1640.42 ft) 1080p: 400 m (1312.34 ft)
Transmission Distance ²	RG-6/U Coax	720p: 800 m (2624.67 ft) 1080p: 600 m (1968.50 ft)
	CAT 6 UTP (balun required)	720p: 380 m (1246.72 ft) 1080p: 380 m (1246.72 ft)
Day/Night	Auto (ICR), Color, B/W	
OSD Menu	English, French, German, Italian, Japanese, Polish, Portuguese, Russian, Spanish	
Backlight Compensation	BLC, HLC, WDR (120 dB)	
White Balance	Auto, ATW, Indoor, Outdoor, Manual	
Gain Control	Auto, Manual	
Noise Reduction	Ultra DNR (2D/3D)	
Advanced Features	Defog	
Digital Zoom	16x	
Flip	180°	
Privacy Masking	Up to 24 areas	
C 1:t. 1:		

Certifications

CE	EN55032, EN55024, EN50130-4
Safety	UL60950-1+CAN/CSA C22.2,No.60950-1
Electromagnetic Compatibility (EMC)	FCC Part 15 subpart B ANSI C63.4- 2014

Interface

Video	Output: One (1) BNC
Audio	Input: One (1) Channel
RS485	One (1) Port
Alarm	Input: Two (2) Channels Output: One (1) Channel

Electrical

Power Supply	24 VAC, 3 A (±10%)
Power Consumption	13 W, 23 W with IR on

Environmental

Operating Conditions	-40 °C to 60 °C (-40 °F to $+140$ °F), Less than 90% RH
Ingress Protection	IP66

Construction

Casing	Metal
Dimensions	Ø186.0 mm x 309.0 mm (Ø7.32 in. x 12.17 in.)
Net Weight	3.50 kg (7.72 lb)
Gross Weight	6.80 kg (14.99 lb)

Transmission distance results verified by real-scene testing in Dahua's test laboratory. Actual transmission distances may vary due to external influences, cable quality, and wiring structures.

Ordering Information		
Туре	Part Number	Description
2 MP PTZ Camera	59230IC	2 MP 30x Starlight IR PTZ HDCVI Camera, Built-in Heater, True WDR
	AC24V/3A	Power Supply
Accessories, included	PFA110	Mount Adapter
	PFB300S	Wall Mount
	PFA120	Junction Box
	PFA140	Power Supply Box
Accessories,	PFA150	Pole Mount
optional	PFA151	Corner Mount
	PFB300C	Ceiling Mount
	PFB303S	Parapet Mount

Accessories

Included:



PFB300S Wall Mount Optional:



PFA110 Mount Adapter



AC24V/3A Power Supply



PFA140 Power Box



PFB300C Ceiling Mount



PFA120 Junction Box



PFA150 Pole Mount



PFA151 Corner Mount



PFB303S Parapet Mount

Calling Manuat	lumation Beaums
Ceiling Mount	Junction Mount
PFA110 + PFB300C	PFA110 + PFB300S + PFA120
Power Box Mount	Pole Mount
PFA110 + PFB300S + PFA140	PFA110 + PFB300S + PFA150
Corner Mount	Parapet Mount
PFA110 + PFB300S + PFA151	PFA110 + PFB303S

Dimensions (mm)



