

# Uninterrupted Power Supply



- Compact Uninterrupted Power Supply (UPS)
- 36 VDC Maximum Power Output

## Technical Specifications

Cycle Life	≥ 300 times
Power Input	6 VDC to 36 VDC (Battery charged after the voltage exceeds 12 V)
Power Output	6 VDC to 36 VDC (Output is 6 VDC to 8.2 VDC when there is no constant power supply)
Battery Capacity	7.4 V at 5200 mAh
Power Energy at Average Time	12 W at 2 hours 10 minutes 51 seconds 24 W at 38 minutes 57 seconds 36 W at 19 minutes 12 seconds 48 W at 9 minutes 10 seconds 60 W at 4 minutes 7 seconds
Working Temperature (Charge)	0° C to +45° C (32° F to +113° F)
Working Temperature (Discharge)	-20° C to +60° C (-4° F to +140° F)
Dimensions (L x W x H)	150.40 mm x 132.0 mm (5.92 in. x 5.20 in.)

## Dimensions (mm)

