

# DH-SD60230U-HNI-SL

2MP 30x Anti-corrosion PTZ Network Camera



- · 1/2.8" 2Megapixel STARVIS™ CMOS
- · Powerful 30x optical zoom
- Starlight technology
- · H.265 Encoding
- Max. 50/60fps@1080P
- · Auto-tracking and IVS
- · Support PoE+
- · IP68, IK10, NEMA 4X
- · Material: 316L Stainless steel













# **System Overview**

Featuring powerful optical zoom and accurate pan/tilt/zoom performance, this camera provides an all-in-one solution for capturing long distance video surveillance for outdoor applications. Together with infrared illumination and Starlight technology, the camera is the perfect solution for dark, lowlight applications. The series combines a day/night mechanical IR cut filter for the highest image quality in variable lighting conditions during the day, and True WDR for applications with direct sunlight or glare.

### **Functions**

### Starlight Technology

For challenging low-light applications, Dahua's Starlight Ultra-low Light Technology offers best-in-class light sensitivity, capturing color details in low light down to 0.005 lux. The camera uses a set of optical features to balance light throughout the scene, resulting in clear images in dark environments.

### **Wide Dynamic Range**

The camera achieves vivid images, even in the most intense contrast lighting conditions, using industry-leading wide dynamic range (WDR) technology. For applications with both bright and low lighting conditions that change quickly, True WDR (120 dB) optimizes both the bright and dark areas of a scene at the same time to provide usable video.

### **Auto-tracking**

This feature controls the pan/tilt/zoom actions of the camera to automatically track an object in motion and to keep it in the scene. The tracking action can be triggered manually or automatically by defined rules. Once a rule is triggered, the camera can zoom in and track the defined target automatically.

### Smart H.265+

Smart H.265+ is the optimized implementation of the H.265 codec that uses a scene-adaptive encoding strategy, dynamic GOP, dynamic ROI, flexible multi-frame reference structure and intelligent noise reduction to deliver high-quality video without straining the network. Smart H.265+ technology reduces bit rate and storage requirements by up to 70% when compared to standard H.265 video compression.

### **PFA Technology**

PFA technology has innovatively introduced new methods of judgment to ensure the accuracy and predictability of the direction of subject distance adjustment. The result is a set of advanced focusing algorithms. PFA ensures clarity of the image throughout the process of zooming and shortens focus time. The realization of PFA technology substantially improves user experience and increases product value.

### **Environmental**

Dahua cameras operate in extreme temperature environments, rated for use in temperatures from -40 °C to +70 °C (-40 °F to +158 °F) with 95% humidity. The camera complies with the IK10 Vandal Resistance impact rating making it capable of withstanding the equivalent of 55 kg (120 lbs) of force. Subjected to rigorous dust and water immersion tests and certified to the IP68 Ingress Protection rating makes it suitable for demanding outdoor applications.

# **Protection**

The camera allows for ±25% input voltage tolerance, suitable for the most unstable conditions for outdoor applications. Its 6KV lightning rating provides effective protection for both the camera and its structure against lightning.

### Interoperability

The camera conforms to the ONVIF (Open Network Video Interface Forum) and PSIA (Physical Security Interoperability Alliance) specifications, ensuring interoperability between network video products regardless of manufacturer.



Technical Specification			Video	
Camera			Compression	H.265+/H.265/H.264+/H.264
Image Sensor	1/2.8" STARVIS™ CMOS		Streaming Capability	3 Streams
Effective Pixels	1920(H) x 1080(V), 2 Megapixels		Resolution	1080P(1920×1080)/1.3M(1280×960)/720P(1280×720)/D1(704×576/704×480)/CIF(352×288/352×240)
RAM/ROM	512M/128M			Main stream: 1080P/1.3M/720P(1~50/60fps)
Scanning System	Progressive		Traine Nate	Sub stream1: D1/CIF(1 ~ 25/30fps)
Electronic Shutter Speed	1/1s~1/30,000s			Sub stream2: 1080P/1.3M/720P/D1/CIF
Minimum Illumination	Color: 0.005Lux@F1.6; B/W: 0.0005Lux@F1.6			(1~25/30fps)
S/N Ratio	More than 55dB		Bit Rate Control	CBR/VBR
IR Distance	N/A		Bit Rate	H.265/H.264: 448K ~ 8192Kbps
IR On/Off Control	N/A		Day/Night	Auto(ICR) / Color / B/W
IR LEDs	N/A		Backlight Compensation	BLC / HLC / WDR (120dB)
Lens			White Balance	Auto, ATW, Indoor, Outdoor, Manual
Focal Length	4.5mm~135mm		Gain Control	Auto / Manual
Max. Aperture	F1.6 ~ F4.4		Noise Reduction	Ultra DNR (2D/3D)
Angle of View	H: 67.8° ~ 2.4°		Motion Detection	Support
Optical Zoom	30x		Region of Interest	Support
Focus Control	Auto/Manual		Electronic Image Stabilization (EIS)	Support
Close Focus Distance	100mm~ 1000mm		Defog	Support
DORI Distance			Digital Zoom	16x
*Note: The DORI distance is a "gene			Flip	180°
pinpoint the right camera for your needs. The DORI distance is calculated based on sensor specification and lab test result according to EN 62676-4 which defines the criteria for Detect, Observe, Recognize and Identify respectively.			Privacy Masking	Up to 24 areas
Detect Observe	Recognize	Identify	Audio	
1862m(6109ft) 744m(2441ft		186m(610ft)	Compression	G.711a/G.711Mu/AAC/G.722 / G.726/MPEG2-L2
PTZ	5/2111(122011)	180111(01011)	Network	
	D 00 2500 II Tili 1	200 - 000 1 11 4000	Ethernet	RJ-45 (10Base-T/100Base-TX)
Pan/Tilt Range	Pan: 0° ~ 360° endless; Tilt: -2	•		IPv4/IPv6,HTTP,HTTPS,SSL,TCP/IP, UDP,UPnP,
Manual Control Speed	Pan: 0.1° ~300° /s; Tilt: 0.1° ~200° /s		Protocol	ICMP,IGMP,SNMP,RTSP,RTP, SMTP, NTP,DHCP, DNS,PPPOE,DDNS,FTP, IP Filter,QoS,Bonjour,802.1x
Preset Speed	Pan: 600° /s; Tilt: 500° /s		Interoperability	ONVIF, PSIA, CGI
Presets	300		Streaming Method	Unicast / Multicast
PTZ Mode	5 Pattern, 8 Tour, Auto Pan ,A		Max. User Access	20 users
Speed Setup	Human-oriented focal Length Auto restore to previous PTZ	, , ,	Edge Storage	NAS (Network Attached Storage),Local PC for instant recording, Micro SD card 128GB
Power up Action	power failure		Web Viewer	IE, Chrome, Firefox, Safari
Idle Motion	Activate Preset/ Scan/ Tour/ Pattern if there is no command in the specified period		Management Software	Smart PSS, DSS
Protocol	DH-SD, Pelco-P/D (Auto recognition)		Smart Phone	IOS, Android
Intelligence			Certifications	
Auto Tracking	Support		CE: EN55032/EN55024/EN50130-4 Certifications FCC: Part15 subpartB,ANSI C63.4- 2014 NEMA 4X: UL60950-1+CAN/CSA C22.2,No.60950-	
IVS	Tripwire, Intrusion, Abandoned/Missing, Face Detection, Heat Map			

### Interface

Video Interface	1 port(BNC, 1.0V[p-p], 75Ω)
RS485	1
Audio I/O	1/1
Alarm I/O	7/2

### Electrical

Power Supply	AC24V/3A(±25%), PoE+(802.3at)
Power Consumption	13W,20W (Heater on)

### **Environmental**

Operating Conditions	-40°C $^{\sim}$ 70°C (-40°F $^{\sim}$ +158°F) / Less than 95% RH
Ingress Protection	IP68
Vandal Resistance	IK10

### Construction

Casing	316L stainless steel
Dimensions	Ф222(mm) x 292(mm)
Net Weight	5.9kg(13.01lb)
Gross Weight	11.0Kg(24.25lb)

### **Ordering Information** Type Part Number Description 2MP 30x Anti-corrosion PTZ DH-SD60230U-HNI-SL Network Camera, WDR, PAL 2MP PTZ Camera 2MP 30x Anti-corrosion PTZ DH-SD60230UN-HNI-SL Network Camera, WDR, NTSC AC 24V/3A Power Adapter Accessories DH-PFB303W-SL Wall Mount DH-PFA120-SL Junction Box

# **Accessories**

### Included:







PFB303W-SL Wall Mount

# Optional:



PFA120-SL Junction Box

# Wall Mount PFB303W-SL+PFA120-SL

# Dimensions (mm)



