

1080p H.265 HDCVI Penta-brid DVR

32-Channel H.265 1.5U HDCVI Digital Video Recorder



- Embedded Processor
- Smart H.265+ and Smart H.264+ Dual Codec
- Dual-stream Recording
- 5 M-N (1296 x 1944) at 20 fps Maximum Recording Resolution
- 32 HDCVI, AHD, TVI, CVBS or IP Channels
- Up to 8 MP per IP Channel
- 128 Mbps Incoming Bandwidth
- Built-in Smart Search
- Spot Monitor Output on HDMI 2
- Intelligent Video System
- Four (4) SATA HDD Ports, up to 10 TB per Hard Disk Drive
- Five-year Warranty*



Functions

Smart H.265+

Smart H.265+ is the optimized implementation of the H.265 codec that uses a scene-adaptive encoding strategy, dynamic GOP, dynamic ROI, flexible multi-frame reference structure and intelligent noise reduction to deliver high-quality video without straining the network. Smart H.265+ technology reduces bit rate and storage requirements by up to 90% when compared to the H.264 video compression standard.

HDCVI/AHD/TVI/CVBS Auto-detect

The HDCVI DVR automatically recognizes the incoming signals of each attached camera without any setup, making installation easy and operation convenient.

Intelligent Video System (IVS)

With built-in IVS analytics on up to 16 channels, the HDCVI DVR delivers intelligent functions to monitor a scene for Tripwire violations, intrusion detection, and abandoned or missing objects. A device with IVS quickly and accurately responds to monitoring events in a specific area.

Face Detection

The HDCVI DVR offers Face Detection of the first analog channel. This technology detects and captures a snapshot of a human face in a defined area within a scene.

Smart Fan Design

The HDCVI DVR automatically turns on or turns off the fan according to the CPU temperature. This function reduces fan noise and helps to conserve electricity.

Smart Search

Smart Search allows an operator to specify a region in the playback video to search for a motion detection event, saving time and manpower.



System Overview

The X54A Series HDCVI DVR offers 1080p recording on each HDCVI channel and a host of advanced features and functions. The X54A takes advantage of HDCVI technology for easy integration into existing video surveillance systems while leveraging existing networks, cabling, and cameras. Penta-brid access technology seamlessly records video from HDCVI, AHD, TVI, CVBS, and IP sources simultaneously.

The X54A utilizes the Smart H.265+ Codec to significantly improve encoding efficiency and to reduce bandwidth and storage costs. This recorder is the ideal solution for actively monitoring and recording video feeds in a wide range of applications including public venues, retail stores, transportation hubs and access ways, personal property and homes, and educational institutions.

Camera Connections

Record and monitor video from analog/HDCVI camera inputs and IP camera inputs simultaneously. The X54A series supports a maximum of 32 channels, with up to 32 channels of HDCVI/AHD/TVI/CVBS/IP inputs. The flexibility of the HDCVI DVR allows all 32 channels to record input from IP cameras, or from a combination of input from analog and IP sources (not to exceed the maximum number of analog cameras allowed per recorder).

Flexible Recording

The HDCVI DVR offers a variety of configurable recording options and schedule that saves HDD space and active monitoring time. The recorder monitors incoming video and can be programmed to record if motion is detected or if an alarm is triggered. The recorder can also be programmed to record on a schedule or at different intervals. The recording options and schedules can be set for each individual camera or copied to all cameras.

Pro Series | X54A5L

Technical Sp	ecification			
System				
Main Processor		Embedded Processor		
Operating System		Embedded LINUX		
Interface				
Analog Camera I	nput	32 Channels, BNC		
Preview Ability		Channels 1 and 2: • 5 M-N (1296 x 1944) at 20 fps or • 4 M-N (1280 x 1440) at 30 fps Channels 3 to 32: • 4 M-N (1280 x 1440) at 30 fps		
HDCVI		5 MP, 4 MP, 1080p at 30 fp	os; 720p at 60 fps	
AHD		5 MP, 4 MP, 1080p at 30 fp	os; 720p at 30 fps	
TVI		5 MP, 4 MP, 1080p at 30 fp	os; 720p at 30 fps	
CVBS		NTSC		
IP Camera Input		32 Channels, each channel	up to 8 MP	
Audio		Input: Four (4) Channels, BNC Output: One (1) Channel, BNC		
Two-way Talk		Input: One (1) Microphone, BNC Output: One (1) Speaker, BNC		
Recording				
Compression		Smart H.265+, H.265, Smar	rt H.264+, H.264	
Recording Resol	ution	5 M-N (1296 x 1944), 4 M-N (1280 x 1440), 1080p, 1080N, 720p, 960H, D1, CIF		
Record Rate	Main Stream	Channel 1: • 5 M-N (1296 x 1944) at 20 fps Channels 2 to 32: • 4 M-N (1280 x 1440) at 7 fps	Channels 1 and 2: • 5 M-N (1296 x 1944) at 10 fps Channels 3 to 32: • 4 M-N (1280 x 1440) at 15 fps	
	Sub Stream	D1 or CIF at 15 fps		
Maximum Incon	ning Bandwidth	128 Mbps		
Bit Rate		32 Kbps to 6144 Kbps per Channel		
Record Mode		Manual, Schedule (Regular, Continuous), MD (Video Detection: Motion Detection, Video Loss, Tampering), Alarm, Stop		
Record Interval		1 to 60 minutes (default: 60 minutes), Pre-record: 1 s to 30 s, Post-record: 10 s to 300 s		
Audio Compress	ion	AAC (first channel only), G.711A, G.711U, PCM		
Audio Sample Ra	ate	8 KHz, 16 bits per Channel		
Audio Bit Rate		64 Kbps per Channel		
Display				
Interface		Two (2) HDMI, One (1) VGA, One (1) BNC		
Native Output	HDMI 1	3840 x 2160, 2560 x 1440, 1920 x 1080, 1280 x 1024, 1280×720		
Resolution	HDMI 2/VGA	1920 x 1080, 1280 x 1024, 1280 x 720		
Maximum Decoding		16 Channels of 4 M-N at 15 fps 8 Channels of 4 M-N at 30 fps 1 Channel of 6 MP at 30 fps		
Multi-screen Display		1/4/8/9/16/25/36		
On-screen Display		Camera Title, Time, Video Loss, Camera Lock, Motion Detection, Recording		

Network	
Interface	One (1) RJ45 (1000 Mbps) Port
Network Function	HTTP, TCP/IP, IPv4/IPv6, UPnP, RTSP, UDP, SMTP, NTP, DHCP, DNS, IP Filter, PPPoE,DDNS, FTP, Alarm Server, P2P, IP Search (Supports Dahua IP cameras, DVRs, NVS)
Maximum User Access	128 Users
Mobile Operating System	IOS, Android
Interoperability	ONVIF 16.12, CGI Conformant
Video Detection and	Alarm
Trigger Events	Recording, PTZ, Tour, Video Push, Email, FTP, Snapshot, Buzzer and Screen Tips
Video Detection	Motion Detection, MD Zones: 396 (22 × 18), Video Loss, Tampering and Diagnosis
Alarm Input	16 Channels
Relay Output	Six (6) Channels
Playback and Backup)
Playback	1/4/9/16
Search Mode	Time/Date, Alarm, MD and Exact Search (accurate to 1 second)
Playback Function	Play, Pause, Stop, Rewind, Fast Play, Slow Play, Next File, Previous File, Next Camera, Previous Camera, Full Screen, Repeat, Shuffle, Backup Selection, and Digital Zoom
Backup Mode	USB Device/Network
Storage	
Internal HDD	Four (4) SATA Ports, up to 10 TB capacity for each disk
Auxiliary Interface	
USB	One (1) USB 2.0 Port and Two (2) USB 3.0 Ports
RS232	One (1) Port for PC Communication and Keyboard
RS485	One (1) Port for PTZ Control
RS422	One (1) port for PTZ Control
Electrical	
Power Supply	100 VAC to 240 VAC, 50/60 Hz
Power Consumption	< 35 W
Construction	
Dimensions	1.5U, 440.0 mm x 417.0 mm x 76.0 mm (17.30 in. x 16.40 in. x 3.0 in.)
Net Weight	5.0 kg (11.0 lb), without HDD
Gross Weight	7.0 kg (15.43 lb)
Installation	Desktop or Rack-mount
Environmental	
Operating Conditions	-10° C to +55° C (+14° F to +131° F), 10% to 90% RH
Storage Conditions	-20° C to $+70^\circ$ C (–4° F to $+158^\circ$ F), 0% to 90% RH


The M-N resolution refers to technology that allows a 1080p HDCVI DVR to accept a video signal from a 5 MP or a 4 MP camera by sampling every other pixel on a horizontal line from the camera. The resulting recording resolutions are: 5 M-N: 1296 x 1944; 4 M-N: 1280 x 1440.

Pro Series | X54A5L

Certifications

Safety	UL 60950-1 EN 60950-1, IEC 60950-1
Electromagnetic Compatibility (EMC)	FCC Part 15 Subpart B ICES 003 Issue 6 EN 55032 EN 50130 EN 61000-3-2 EN 61000-3-3
Immunity	EN 55024 : 2010

Dimensions (mm/in.)



405.0 mm (15.94 in.)



The IVS features are operational only when the additional IP channel feature is not active. The HDCVI DVR supports only IVS or the additional IP channel inputs, both features cannot be in use simultaneously.

IVS triggers an alarm and takes a defined action for the following events:

Premium Features

Channels 1 through 16: Support Tripwire and Intrusion Detection

 $\label{eq:channels1} Channels1 and 2: Additionally support Abandoned/Missing Object \ Detection$

Tripwire			A target crosses a user-defined line.	
Intrusion			A target enters or exits a defined perimeter.	
	Abandoned/Missing Object		A target leaves an object in designated area, or a targe removes an object from the same designated area.	
Advanced Feature Available on Analog Channel 1 (feature not available if an IP camera is connected as Camera 1)		nera is connected as Camera 1)		
Face Detection		ction	Detects and captures a snapshot of a human face in a defined area within a scene.	
Ordering Information				
	Туре	Part Number	Description	

Type	Fait Nulliber	Description
Penta-brid HDCVI DVR	X54A5L	32 Analog/IP Inputs, 1080p Penta-brid, 16 Alarm Inputs, 6 Alarm Outputs, 1.5U HDCVI Digital Video Recorder

R	Rear Panel				
(1030	Ð 6	D	789	
F	0 (0 ⁻ 0 (0	0000			A
			00		5
Ľ					J
		0		112134	
	1	Microphone OUT, BNC x 1	8	VGA OUT	
	2	Microphone IN, BNC x 1	9	Power Input	
	3	Video OUT, BNC x 1	10	Video IN, BNC x 32	
	4	Audio OUT, BNC x 1	11	RS232 Port	
	5	Audio IN, BNC x 4	12	eSATA Port	
	6	Alarm I/O, RS485, RS422	13	USB 3.0 x 2	
	7	Network Port	14	HDMI 1 and HDMI 2 OUT	

