

HPS Sentinel[®]

Energy Efficient Distribution Transformers

Specifications & Accessories - Copper or Aluminum



15 to 45 kVA



75 to 150 kVA



225-1000 kVA

STANDARD SPECIFICATIONS

<p>kVA: 15-1000kVA</p> <p>UL Listed: File: E112313</p> <p>CSA Certified: File: LR3902</p> <p>Frequency: 60 Hz (optional 50/60 Hz available)</p> <p>Insulation System: 220°C (150°C rise) (optional 115°C & 80°C rise available)</p> <p>BIL Rating 10 kV (on all 3PH low voltage products)</p> <p>Enclosure Type: Heavy duty ventilated Type 3R standard (optional Type 4, 4X (stainless steel) & 12)</p> <p>Enclosure Finish: ANSI 61 Grey, UL50</p> <p>Neutral: Neutral terminal for field connection (on applicable units)</p> <p>Standard Primary Taps: Refer to wiring diagrams for details</p> <p>Optional Accessories:</p> <ul style="list-style-type: none"> • Thermal sensing & indication <ul style="list-style-type: none"> - Thermocouples - Thermometers (analog/digital) - Thermostat alarm / trip (N.O. /N.C. contacts) • Electrostatic shielding • Rated to handle current harmonics [K4] [K9] [K13] • Strip heater (space heater to prevent condensation) • Surge protection devices • Type 3R or 4X available in stainless steel • Type 3R enhanced with baffling for horizontal blowing rain and snow 	<p>Termination: Front accessible separate high and low voltage terminals; connectors suitable for aluminum and copper are provided for easy cable installation.</p> <p>Conduit Entry: Side knock-outs standard on all units; Bottom entry provision (exceptions apply)</p> <p>Impedance: Typically 3.5% to 6.5%</p> <p>Mounting: Floor or wall/ceiling mounting available. Refer to selection tables for details.</p> <p>Seismic: Seismically qualified according to the International Building Code (IBC) 2012, and the American Society of Civil Engineers ASCE 7-10 specifications, with the following design parameters: Spectral acceleration: $S_{DS} \leq 2.0$ g Importance factor: $I_p = 1.5$ Attachment/height ratio: $z/h = 1.0$" O.S.H.P.D. California Certified</p> <p>Sound Level: Meets NEMA ST-20 standards (optional low noise units available)</p> <p>Warranty: 10 years</p>
-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------	--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

HPS Sentinel Part Number Guide

Example

Family	Type	Generation	Phase	kVA				Pri. Volt.	Sec. Volt	K Rating	Winding Material/ Electrostatic Shield	Temp. Rise & Insul. Class	Enclosure
S	G	3	A	0	0	4	5	K	B	0	K	F	K

Family:

S - Sentinel

Type:

G - General
K - K Rated
H - Harmonic Mitigation

Generation:

2 - current designs
3 - current designs

Phase (Pri-Sec):

A - 3PH Delta-Wye
B - 3PH Wye-Delta
C - 3PH Delta-Delta/CT
D - 3PH Delta-Delta
Y - 3PH Wye-Wye
T - 3PH Zig Zag- 0° PH Shift
U - 3PH Zig Zag- -30°PH Shift
L- 1PH Single-Dual
N- 1PH Dual-Dual
M- 1PH Multiple-Dual

kVA:

kVA Rating

Primary Voltage:

1PH 3PH
B 208 208D, 208Y/120
D 240 240D
F 277
H 416 416D
K 480 480D, 480Y/277
L 240x480
P 600 600D, 600Y/347
X multiple

Secondary Voltage:

1PH 3PH
B 208 208D or 208Y/120
D 240 240D, 240D/120CT or
240Y/139
E 120/240
K 480 480D or 480Y/277
P 600 600D or 600Y/347
Y 380Y/220V w taps at
400Y, 416Y and 430Y

K Rating:

0 = None
4 = K4
9 = K9
3 = K13
2 = K20

Winding Material/Electrostatic Shield:

A - Aluminum
S - AL + Shield
C - Copper
K - CU + Shield

Temperature Rise at standard 220°C Insulation Class:

B - 80°C
F - 115°C
G - 130°C
H - 150°C

Enclosure:

A - Type 1
B - Type 2
C - Type 3R
D - Type 3RE
E - Type 3RX
F - Type 4
G - Type 4X (304SS)
H - Type 4X (316SS)
K - Type 12
X - None (Core & Coil)

Additional options include low sound level and special duty (marine, etc)

Support & Resources

No other transformer company can offer our service and quality in a full range of products.

Transformer Efficiency Calculator



The HPS Efficiency Calculator allows you to determine how much money and energy you can save by switching to a HPS Sentinel G3, K3, or H3 transformer. Visit the "Online Tools" area of the HPS website.

Extensive Inventory



We carry a complete inventory of Distribution Transformers throughout North America to quickly meet your needs.

Current Calculator



Calculate the Amps, Volts, or kVA of a transformer. Visit the "Online Tools" area of the HPS website.

Live Telephone Technical Support



Our inside sales team is available to quickly answer your questions. They are technically trained and able to answer most questions right over the phone.

Fast On-Site Response



On-site technicians are available to assist with any technical problems or issues that cannot be resolved over the phone.

Easy-To-Access Installation Manuals



All transformer installation manuals are conveniently located on our website so you can access them anywhere, anytime.

Selection Tables

HPS Sentinel G3
Energy Efficient General Purpose Distribution



COPPER WOUND, THREE PHASE



480 Delta Primary Volts

480Y/277 Secondary Volts

60 Hz

kVA	Catalog Number	Case Style	Approx. Dimensions (Inches)			Approx. Weight (Lbs.)	Mtg Type W - Wall F - Floor	Wiring Diagram
			Width	Depth	Height			
15	SG3A0015KKOC	DH1	21.5	20.1	22.0	210	F or W/C	SCD 19
30	SG3A0030KKOC	DH2	25.8	23.8	28.8	340	F or W/C	SCD 19
45	SG3A0045KKOC	DH2	25.8	23.8	28.8	400	F or W/C	SCD 19
75	SG3A0075KKOC	DH3	28.3	27.0	36.0	590	F (Opt W/C)	SCD 19
112.5	SG3A0112KKOC	DH3	28.3	27.0	36.0	740	F (Opt W/C)	SCD 19
150	SG3A0150KKOC	DH4	31.5	29.5	44.5	930	F	SCD 19
225	SG3A0225KKOC	DH4	31.5	29.5	44.5	1350	F	SCD 19
300	SG3A0300KKOC	DH5	37.5	34.0	52.0	1800	F	SCD 19
500	SG3A0500KKOC	DH6	49.0	41.5	64.0	3200	F	SCD 20
750	SG3A0750KKOC	DH6	49.0	41.5	64.0	4050	F	SCD 20
1000	SG3A1000KKOC	DH7	54.0	46.5	72.0	5200	F	SCD 10

W/C: Built-in Wall Ceiling Mounting Opt W/C: Wall Ceiling Mounting Kit "DW3" Available OSHPD Certified for Floor Mounting Only

600 Delta Primary Volts

208Y/120 Secondary Volts

60 Hz

kVA	Catalog Number	Case Style	Approx. Dimensions (Inches)			Approx. Weight (Lbs.)	Mtg Type W - Wall F - Floor	Wiring Diagram
			Width	Depth	Height			
15	SG3A0015PB0C	DH1	21.5	20.1	22.0	210	F or W/C	SCD 19
30	SG3A0030PB0C	DH2	25.8	23.8	28.8	340	F or W/C	SCD 19
45	SG3A0045PB0C	DH2	25.8	23.8	28.8	400	F or W/C	SCD 19
75	SG3A0075PB0C	DH3	28.3	27.0	36.0	590	F (Opt W/C)	SCD 19
112.5	SG3A0112PB0C	DH3	28.3	27.0	36.0	740	F (Opt W/C)	SCD 19
150	SG3A0150PB0C	DH4	31.5	29.5	44.5	930	F	SCD 19
225	SG3A0225PB0C	DH4	31.5	29.5	44.5	1350	F	SCD 19
300	SG3A0300PB0C	DH5	37.5	34.0	52.0	1800	F	SCD 19
500	SG3A0500PB0C	DH6	49.0	41.5	64.0	3200	F	SCD 20
750	SG3A0750PB0C	DH6	49.0	41.5	64.0	4050	F	SCD 20
1000	SG3A1000PB0C	DH7	54.0	46.5	72.0	5200	F	SCD 10

W/C: Built-in Wall Ceiling Mounting Opt W/C: Wall Ceiling Mounting Kit "DW3" Available OSHPD Certified for Floor Mounting Only

600Y Primary Volts

240 Delta Secondary Volts

60 Hz

kVA	Catalog Number	Case Style	Approx. Dimensions (Inches)			Approx. Weight (Lbs.)	Mtg Type W - Wall F - Floor	Wiring Diagram
			Width	Depth	Height			
15	SG3B0015PD0C	DH1	21.5	20.1	22.0	210	F or W/C	SCD 54
30	SG3B0030PD0C	DH2	25.8	23.8	28.8	340	F or W/C	SCD 54
45	SG3B0045PD0C	DH2	25.8	23.8	28.8	400	F or W/C	SCD 54
75	SG3B0075PD0C	DH3	28.3	27.0	36.0	590	F (Opt W/C)	SCD 54
112.5	SG3B0112PD0C	DH3	28.3	27.0	36.0	740	F (Opt W/C)	SCD 54
150	SG3B0150PD0C	DH4	31.5	29.5	44.5	930	F	SCD 54
225	SG3B0225PD0C	DH4	31.5	29.5	44.5	1350	F	SCD 54
300	SG3B0300PD0C	DH5	37.5	34.0	52.0	1800	F	SCD 54
500	SG3B0500PD0C	DH6	49.0	41.5	64.0	3200	F	SCD 58
750	SG3B0750PD0C	DH6	49.0	41.5	64.0	4050	F	SCD 58
1000	SG3B1000PD0C	DH7	54.0	46.5	72.0	5200	F	SCD 29

W/C: Built-in Wall Ceiling Mounting Opt W/C: Wall Ceiling Mounting Kit "DW3" Available OSHPD Certified for Floor Mounting Only