

# GL100PGO

Unbreakable Polycarbonate threaded globes to fit RAB and other standard size Vaporproof fixtures. Lamp base up only.

Color: opal

Weight: 0.4 lbs



## Technical Specifications

### UL Listing:

Suitable for wet locations when used with Vaporproof fixtures. Suitable for dry, damp or wet locations when used as replacement globes for listed fixtures. Fixtures must be installed with lamp base up when outdoors.

### Polycarbonate Globe:

Clear thermal shock resistant polycarbonate standard.

### Maximum Wattage:

75 watts.

### Patents:

RAB sensor and fixture designs are protected under U.S. and International Intellectual Property laws.

### Country of Origin:

Designed by RAB in New Jersey and assembled in the USA by RAB's IBEW Local 3 workers.

### Buy American Act Compliant:

This product is a COTS item manufactured in the United States, and is compliant with the Buy American Act.

### Recovery Act (ARRA) Compliant:

This product complies with the 52.225-21 "Required Use of American Iron, Steel, and Manufactured Goods-- Buy American Act-- Construction Materials (October 2010).

### Trade Agreements Act Compliant:

This product is a COTS item manufactured in the United States, and is compliant with the Trade Agreements Act.

### GSA Schedule:

Suitable in accordance with FAR Subpart 25.4.