




Cat. #		Approvals
Job	Type	

APPLICATIONS

Ideal for perimeter lighting.

SPECIFICATIONS

- Borosilicate glass refractor softens lamp image and provides uniform distribution - 4 times spacing to mounting height. Cast aluminum frame holds lens and seals to housing gasket with two stainless steel screws.
- Door assembly hinges to side on mid-size units; hinges down on large units.
- Cast aluminum housing with 1/2" conduit entries, button photocontrol can be field installed.
- WGH mid-size is 175W MH and 150W HPS, large handles 250-400W MH and HPS.
- Tri-Tap® (120, 277, 347V).
- All units have dark bronze powder paint finish, Tri-Tap® ballasts and lamps included.



LISTINGS

- cUL listed for use in wet locations.

	A	B	C
MID-SIZE	9 in.	7.25 in.	13 in.
	229 mm	184 mm	330 mm
LARGE	9 in.	13 in.	17 in.
	229 mm	330 mm	432 mm

ORDERING INFORMATION

Catalogue Number	Lamp Type / Wattage	Volts	Weight	UPC Code
Mid-Size Series				
WGH175HT	175W MH	120, 277, 347V	19.0	80503504480
WGH150ST	150W HPS	120, 277, 347V	18.0	80503504481
Large Series				
WGH250HT	250W MH	120, 277, 347V	34.0	80503504482
WGH400HT	400W MH	120, 277, 347V	37.0	80503504483
WGH250ST	250W HPS	120, 277, 347V	36.0	80503504484
WGH400ST	400W HPS	120, 277, 347V	40.0	80503504485



Hubbell Canada LP, Lighting Division

870 Brock Road South | Pickering, ON | L1W1Z8 | Tel: 905.839.1138

For more information, visit our web site: www.hubbellonline.com