



HUBBELL NextFrame Equipment Racks

Attractive Front Covers Enhance Appearance.

Channels Clip to Rack Greatly Speeding Assembly.

Gates and Spools can be Located as Needed Along Length of Channel.

FEATURES

- Sturdy, durable steel Z-frame construction.
- Universal hole pattern on rack uprights mates with other rack/channel models.
- Easy-to-use screws with dog-nose tip lead in and #3 Phillips combo head provided.

SPECIFICATIONS

- ◆ Material:
Rack: 6063-T2 aluminum.
Uprights: 1/4" web thickness.
- ◆ Finish: Durable black powder coat or mill finish.
- ◆ Weight capacity: 500 lbs. (static) when properly secured to floor.
- ◆ UL Listed - 7N69 Communications Circuit Accessory.
- ◆ EIA-310-D universal spacing tapped #12-24 front and rear.

APPROVALS/INSTALLATION

- UL 1863 Listed.
- EIA 310-D Compliant Universal Mounting.
- Mounting Holes Tapped #12-24.

APPLICATIONS

Use in data centers, the equipment room, and telecommunications room to provide racking, cable management, grounding, and power distribution for network hardware.

Superior Cable Management

Multiple tie-off points to organize cable.

Mates with most other models of racks and channels.

Hinged covers

Optional.

Gates store out of the way.



The NEXTFRAME® Equipment Rack is provided with vertical cable channels to structure and route cable efficiently. These racks are the answer to evolving requirements for handling, routing and organizing cable and optical fiber. Use in a typical cross connect/data center to house rack mount patch panels, cable organizers, hubs, routers and other network equipment.

19" Equipment Rack with 6" wide 'Z' Channels

Seven-foot cable management rack with 6" wide vertical cable management organizers in a single catalog number for ease in ordering. Use when maximum cable volume is required. Products are available in both black and clear aluminum finishes. Rack ships unassembled.

Order Information

Delivery:	1	Rack, 7'H (HPW84RR19)		
	2	Vertical Organizers (ref. VS76/VS76A - see page E11)		
Rack Height	Rack Units	Finish	Cover Style	Catalog No.
7' (2134)	45	Black	Hinged	CS1976H
7' (2134)	45	Black	Clip on	CS1976
7' (2134)	45	Aluminum	Clip on	CS1976A



CS1976A

19" Equipment Rack with 3.25" wide 'C' Channels

Seven-foot cable management rack with 3.25" wide vertical cable management organizers in a single catalog number for ease in ordering. Use when space is limited. Products are available in both black and aluminum finishes. Rack ships unassembled.

Order Information

Delivery:	1	Rack, 7'H (HPW84RR19)		
	2	Vertical organizers (VS73/VS73A - see page E11)		
	4	Covers (ref. VCC3/VCC3A - see page E12)		
Rack Height	Rack Units	Finish	Cover Style	Catalog No.
7' (2134)	45	Black	Hinged	CS1973H
7' (2134)	45	Black	Clip on	CS1973
7' (2134)	45	Aluminum	Clip on	CS1973A



CS1973A

Equipment Rack

Shipped unassembled.

Order Information

Delivery:	2	Floor angles	2	Top angles
	2	Vertical uprights	20	#12-24 x 5/8" equipment mounting screws
	1	Assembly hardware kit		

Rack Height	Rack Units	Mounting Width	Finish*	Catalog No.
48" (1219)	24	19" (483)	Black	HPW48RR19
48" (1219)	24	23" (584)	Black	HPW48RR23
68.5" (1676)	36	19" (483)	Black	HPW66RR19
84" (2134)	45	19" (483)	Black	HPW84RR19
84" (2134)	45	23" (584)	Black	HPW84RR23
89.7" (2286)	48	19" (483)	Black	HPW90RR19
89.7" (2286)	48	23" (584)	Black	HPW90RR23
96" (2438)	51	19" (483)	Black	HPW96RR19
96" (2438)	51	23" (584)	Black	HPW96RR23

* For mill finish rack, add "ML" to catalog number.



HPW84RR19



HPW84RR19ML



Hubbell Premise Wiring

HUBBELL INCORPORATED (Delaware)
 14 Lord's Hill Road • Stonington, CT 06378-0901 • (860) 535-8326 • 800-626-0005
 Fax: (860) 535-8328 • Internet site: <http://www.hubbell-premise.com>

Worldwide Locations

Hubbell Premise Wiring, Asia Pacific	852-2836-7131	Fax: 852-2836-7132	Hubbell Premise Wiring, Latin America	305-408-4501	Fax: 305-408-8201
Hubbell Canada Inc.	905-839-1138	Fax: 905-839-9108	Hubbell de Mexico, S.A. de C.V.	(5255) 9151-9999	Fax: (5255) 9151-9989
Hubbell Premise Wiring, Central America	506-309-4158	Fax: 506-260-1616	Hubbell Premise Wiring, Middle East	971-4-393-4192	Fax: 971-4-393-4194
Hubbell Premise Wiring, China	8621-6309-0119	Fax: 8621-6309-0122	Hubbell-Taian Co., Ltd., Taiwan	886-2-2522-1862	Fax: 886-2-2522-1872
Hubbell Premise Wiring, Colombia	571-245-8940	Fax: 571-340-0925	Hubbell Premise Wiring, Turkey	90-216-313-5016	Fax: 90-216-414-8148
Hubbell Premise Wiring, Europe	44-01283 500500	Fax: 44-01283 500400	Hubbell Premise Wiring, Venezuela	58-416-680-7453	Fax: 58-281-274-7900
Hubbell Int'l. Inc., Korea Branch	82-2-(0)2607-1363	Fax: 82-2-(0)2603-7386			