

- Available in Various Depth Rails
- Quick and Easy Assembly
- Universal Mounting Hole Pattern
- Minimal Packaging Reduces Construction Site Waste

FEATURES

- Stabilized top angles, excellent for ladder rack mounting
- Rugged construction
- Universal side mounting hole pattern
- Pre-threaded mounting holes, paint free
- Equipment mounting screws with tapered tip
- Rack unit identifiers
 - 2-post racks: RU numbered and divided
 - 4-post racks: rack units lined
- #12-24 tapped mounting rails (front and back)
 EIA-310-D universal pattern


SPECIFICATIONS

- Material:
 - 2-post racks: 6063-T2 aluminum
 - 4-post racks: cold rolled steel
- Finish: durable black powder coat or mill finish
- Weight capacity:
 - 2-post racks: 1,000lb when secured to floor
 - 4-post racks: 2,000lb when secured to floor
- Floor mount racks support 19" EIA-310-D rack-mount equipment
- UL Listed 7N69 Communications Circuit Accessory

REXTERAME

Equipment Racks





Rack unit identifiers simplify equipment installation

Compatible with Hubbell XXL and VS Series cable organizers

4-Post RackRecommended for mounting servers

NEXTFRAME Equipment Racks are available in 2- and 4-post. 2-post versions are available with depths of 3" and 6". **NEXTFRAME** racks provide an efficient method and structure for a variety of cross connect configurations. These racks are used in typical cross connect and data center applications to house patch panels, cable organizers, switches, and other network equipment. When used in conjunction with **NEXTFRAME** cable management accessories, these racks provide a solution for handling, routing, and organizing cable and optical fiber.

STANDARDS

- UL Listed 1863
- EIA-310-D Compliant

APPLICATIONS

Use in data centers, equipment rooms and telecommunication rooms to provide racking, cable management, grounding and power distribution for network hardware.



2-POST RACKS

Rack ships unassembled.

Contents:

2 floor angles 2 top angles

20 #12-24 x 5/8" equipment mounting screws 2 vertical uprights

1 assembly hardware kit

	,					
Rack Units	Overall Height Inches (mm)	Overall Width Inches (mm)	Post Depth Inches (mm)	Hole Type	Color	Catalog No.
24	48" (1219)	20.2" (518)	3" (76)	#12-24 Threaded	Black	HPW48RR19
36	68.5" (1676)	20.2" (518)	3" (76)	#12-24 Threaded	Black	HPW66RR19
45	84" (2134)	20.2" (518)	3" (76)	#12-24 Threaded	Black	HPW84RR19
48	89.7" (2286)	20.2" (518)	3" (76)	#12-24 Threaded	Black	HPW90RR19
51	96" (2438)	20.2" (518)	3" (76)	#12-24 Threaded	Black	HPW96RR19
24	48" (1219)	24.2" (615)	3" (76)	#12-24 Threaded	Black	HPW48RR23
45	84" (2134)	24.2" (615)	3" (76)	#12-24 Threaded	Black	HPW84RR23
48	89.7" (2286)	24.2" (615)	3" (76)	#12-24 Threaded	Black	HPW90RR23
51	96" 2438)	24.2" (615)	3" (76)	#12-24 Threaded	Black	HPW96RR23
45	84" (2134)	20.2" (518)	6" (152)	#12-24 Threaded	Black	HPW84RR19D



Note: For mill (aluminum) finish rack, add "ML" to the end of catalog number.

SERVER FRAME 4-POST RACKS


Rack ships unassembled.

Contents:

4 cross members 50 mounting screws 4 depth members 1 assembly hardware kit

4 vertical posts

		Usable					
Rack	Overall Height	Height	Overall Width	Depth			
Units	Inches (mm)	Inches (mm)	Inches (mm)	Inches (mm)	Hole Type	Color	Catalog No.
45	84" (2134)	79" (2007)	20.2" (513)	24" (610)	#12-24 Threaded	Black	SF841924T
45	84" (2134)	79" (2007)	20.2" (513)	29.23" (742)	#12-24 Threaded	Black	SF841929T
45	84" (2134)	79" (2007)	20.2" (513)	36" (914)	#12-24 Threaded	Black	SF841936T
45	84" (2134)	79" (2007)	20.2" (513)	24" (610)	M6 Square	Black	SF841924
45	84" (2134)	79" (2007)	20.2" (513)	29.23" (742)	M6 Square	Black	SF841929
45	84" (2134)	79" (2007)	20.2" (513)	36" (914)	M6 Square	Black	SF841936



19" EQUIPMENT RACK WITH 6" WIDE Z-CHANNELS

Seven-foot cable management rack with 6" wide vertical cable management organizers in a single catalog number for ease in ordering. Use when maximum cable volume is required. Products are available in both black and clear aluminum finishes. Rack ships unassembled.

Contents:

1 rack, 7'H (HPW84RR19)

2 vertical organizers (VS76/VS76A)

Rack Units	Rack Height, In. (mm)	Cover Style	Finish	Catalog No.
45	7" (2134)	Hinged	Black	CS1976H
45	7" (2134)	Clip on	Black	CS1976
45	7" (2134)	Clip on	Aluminum	CS1976A



19" EQUIPMENT RACK WITH 3.25" WIDE C-CHANNELS

Seven-foot cable management rack with 3.25" wide vertical cable management organizers in a single catalog number for ease in ordering. Use when space is limited. Products are available in both black and aluminum finishes. Rack ships unassembled.

Contents:

1 rack, 7'H (HPW84RR19) 4 covers (VCC3/VCC3A)

2 vertical organizers (VS73/VS73A)

Rack Units	Rack Height, In. (mm)	Finish	Cover Style	Catalog No.
45	7" (2134)	Black	Hinged	CS1973H
45	7" (2134)	Black	Clip on	CS1973
45	7" (2134)	Aluminum	Clip on	CS1973A





www.hubbell-premise.com

