



HUBBELL OptiChannel Patch Cords

50/125MM Laser Optimized
Fiber Cords Available for
10GbE Applications.

100% Insertion Loss Tested for
Optical Performance.



FEATURES

- SC, ST-style, LC and MT-RJ versions available.
- High quality zirconia ferrules for high performance and superior durability.
- Low mated pair insertion loss - minimum impact on signal budget.
- Wide temperature operating range for environmental stability.
- Precision engineered plastic SC housings for consistent repeatable mating.

SPECIFICATIONS

- ◆ Mated pair insertion loss:
MM: <0.35 dB (0.15dB typical).
SM: <0.35 dB (0.15dB typical).
- ◆ Typical SM mated pair return loss: <-55 dB.
- ◆ Operating/Storage Temperature: 0°C to +75°C.

STANDARDS/LISTINGS/VERIFICATIONS

- Mating Durability: 500 matings per FOTP-21.
- Cable Retention: >10 lbs. per FOTP-6.
- Optical, mechanical and environmental performance: Meets TIA/EIA-568-B.3 specifications.

Fiber patch cords provide connections from the work area to the wall outlet, or from active equipment to the patch panel. These applications include connecting to network interface cards (NIC), or to a fiber hub, router or switch.

Cords are available as duplex or simplex 62.5/125, 50/125 MM, 50/125 Laser Optimized or SM fibers. We offer ST-style, SC, MT-RJ or LC connectors. All patch cords are factory polished and 100% optically tested for superior performance.

APPLICATIONS SUPPORTED

- ▲ Intra-building Backbone LAN cross connects.
- ▲ 10Gigabit fiber links (300m 10GbE 50mm fiber).
- ▲ Local and Wide Area Networks.
- ▲ Data transmission.
- ▲ Video systems.
- ▲ Remote optical communications.
- ▲ Process control.

Fiber Patch Cords

Order Information



SC Duplex to SC Duplex MM

SC to SC Patch Cords

Replace 'X' with standard lengths of **1, 2, 3, 5** or **10** meters

| Duplex/Multimode | Catalog No. | Duplex/Singlemode | Catalog No. |
|-------------------------|----------------------|---------------------|---------------------|
| SC to SC, 62.5/125 | DFPCSCSCXMM | SC to SC Singlemode | DFPCSCSCSXSM |
| SC to SC, 50/125 | DFPCSCSCDXMM | | |
| SC to SC, 50/125, 10GbE | DFPCSCSCEXMM* | | |

* 10GbE cords are not available in 10m lengths.

ST-style to ST-style Patch Cords

Replace 'X' with standard lengths of **1, 2, 3, 5** or **10** meters.

| Duplex/Multimode | Catalog No. | Duplex/Singlemode | Catalog No. |
|--------------------------|---------------------|---------------------------|---------------------|
| ST to ST-style, 62.5/125 | DFPCSTSTCXMM | ST to ST-style Singlemode | DFPCSTSTXSMM |
| ST to ST-style, 50/125 | DFPCSTSTDMM | | |

ST-style to SC Patch Cords

Replace 'X' with standard lengths of **1, 2, 3, 5** or **10** meters.

| Duplex/Multimode | Catalog No. | Duplex/Singlemode | Catalog No. |
|--------------------------|---------------------|----------------------------|---------------------|
| ST-style to SC, 62.5/125 | DFPCSTSCXMM | ST-style to SC, Singlemode | DFPCSTSCSXSM |
| ST-style to SC, 50/125 | DFPCSTSCDXMM | | |

MT-RJ Patch Cords


Replace 'X' with standard lengths of **1, 2, 3** or **5** meters.

| Duplex/Multimode | Catalog No. | Duplex/Singlemode | Catalog No. |
|-----------------------------|---------------------|-------------------|-------------|
| MT-RJ to MT-RJ, 62.5/125 | DFPCRJRJCXMM | | |
| MT-RJ to ST-style, 62.5/125 | DFPCRJSTCXMM | | |
| MT-RJ to SC 62.5/125 | DFPCRJSCXMM | | |

LC Patch Cords

Replace 'X' with standard lengths of **1, 2, 3** or **5** meters.

| Duplex/Multimode | Catalog No. | Duplex/Singlemode | Catalog No. |
|--------------------------|---------------------|----------------------------|---------------------|
| LC to LC, 62.5/125 | DFPCLCLCCXMM | LC to LC, Singlemode | DFPCLCLCCXSM |
| LC to ST-style, 62.5/125 | DFPCLCSTCXMM | LC to ST-style, Singlemode | DFPCLCSTCXSM |
| LC to SC, 62.5/125 | DFPCLCSCCXMM | LC to SC, Singlemode | DFPCLCSCCXSM |
| LC to LC, 50/125, 10GbE | DFPCLCLCEXMM | | |
| LC to SC, 50/125, 10GbE | DFPCLCSCEXMM | | |



ST to ST-style Duplex MM

SC Duplex to ST-style Duplex MM



MT-RJ Duplex to SC Duplex MM



LC Duplex to LC Duplex MM



Hubbell Premise Wiring

HUBBELL INCORPORATED (Delaware)
 14 Lord's Hill Road • Stonington, CT 06378-0901 • (860) 535-8326 • 800-626-0005
 Fax: (860) 535-8328 • Internet site: <http://www.hubbell-premise.com>

Worldwide Locations

Hubbell Premise Wiring, Asia Pacific
 Hubbell Canada Inc.
 Hubbell Premise Wiring, Central America
 Hubbell Premise Wiring, China
 Hubbell Premise Wiring, Colombia
 Hubbell Premise Wiring, Europe
 Hubbell Int'l. Inc., Korea Branch

852-2836-7131 Fax: 852-2836-7132
 905-839-1138 Fax: 905-839-9108
 506-309-4158 Fax: 506-260-1616
 8621-6309-0119 Fax: 8621-6309-0122
 571-245-8940 Fax: 571-340-0925
 44-01283 500500 Fax: 44-01283 500400
 82-2-(0)2607-1363 Fax: 82-2-(0)2603-7386

Hubbell Premise Wiring, Latin America
 Hubbell de Mexico, S.A. de C.V.
 Hubbell Premise Wiring, Middle East
 Hubbell-Taian Co., Ltd., Taiwan
 Hubbell Premise Wiring, Turkey
 Hubbell Premise Wiring, Venezuela

305-408-4501 Fax: 305-408-8201
 (5255) 9151-9999 Fax: (5255) 9151-9989
 971-4-393-4192 Fax: 971-4-393-4194
 886-2-2522-1862 Fax: 886-2-2522-1872
 90-216-313-5016 Fax: 90-216-414-8148
 58-416-680-7453 Fax: 58-281-274-7900