


# Voice & Datacom ID



## DATA CENTRE EQUIPMENT, BAY, RACK & FRAME LABELS

Durable materials with permanent adhesive. Available in a variety of sizes and colours for marking racks, bays, frames, slots, and other voice/data hardware.

Diagram	Order Reference	Colour	Label Width A (mm)	Label Height B (mm)	Label Length B (m)	Labels per Roll	Additional Features
<b>B-422</b>							
⊙	MC-1000-422	Black on White	25.40	-	7.62 m	1	For smooth or textured surfaces
▲	M-7-422	Black on White	12.70	12.70		280	For smooth or textured surfaces
▲	M-17-422	Black on White	25.40	12.70		360	For smooth or textured surfaces
▲	M-19-422	Black on White	25.40	25.40		200	For smooth or textured surfaces
▲	M-29-422	Black on White	38.10	12.70		360	For smooth or textured surfaces
▲	M-30-422	Black on White	38.10	19.05		200	For smooth or textured surfaces
<b>B-483</b>							
▲	M-61-483	Black on White	12.70	50.80		80	For smooth or textured surfaces
▲	M-17-483	Black on White	25.40	12.70		360	For smooth or textured surfaces
▲	M-20-483	Black on White	25.40	50.80		80	For smooth or textured surfaces
<b>B-595</b>							
⊙	MC-500-595-YL-BK	Black on Yellow	12.70	-	7.62 m	1	Indoor/Outdoor Vinyl
⊙	MC-1000-595-YL-BK	Black on Yellow	25.40	-	7.62 m	1	Indoor/Outdoor Vinyl
⊙	MC-1500-595-YL-BK	Black on Yellow	38.10	-	7.62 m	1	Indoor/Outdoor Vinyl



## SELF-LAMINATING CABLE MARKERS

Features a clear, non-printable area that wraps around the cable and serves as an overlaminate to the printed text. Offers superior resistance to abrasion, dirt, oils, solvents, and water.

Diagram	Order Reference	Colour	Label Width A (mm)	Label Height B (mm)	Printable Area Width PW (mm)	Printable Area Height PH (mm)	Labels per Roll	For Data Cables Sized to Fit
<b>B-427</b>								
⊐	M-19-427	Black on White/Transparent	25.40	25.40	25.40	9.53	200	2 pair Fibre/Coaxial, Single/Multi-Mode
⊐	M-21-427	Black on White/Transparent	25.40	63.50	25.40	19.05	80	25 pair Copper, 4-12 pair Fibre, Coaxial
⊐	M-23-427	Black on White/Transparent	25.40	101.60	25.40	25.40	70	50 pair Copper, 24 pair Fibre, Backbone
⊐	M-102-427	Black on White/Transparent	12.70	31.75	12.70	9.53	200	CAT-6, 4 pair UTP Copper
⊐	M-103-427	Black on White/Transparent	25.40	31.75	25.40	12.70	200	CAT-6, 4 pair UTP Copper, Fibre, Coaxial
■	M-29-427	Black on White/Transparent	38.10	12.70	12.70	12.70	360	CAT-6, 4 pair UTP Copper
■	M-30-427	Black on White/Transparent	38.10	19.05	12.70	19.05	200	CAT-6, 4 pair UTP Copper
■	M-31-427	Black on White/Transparent	38.10	25.40	12.70	25.40	200	CAT-6, 4 pair UTP Copper, Fibre, Coaxial
■	M-115-427	Black on White/Transparent	38.10	31.75	12.70	31.75	200	CAT-6, 4 pair UTP Copper
■	M-32-427	Black on White/Transparent	38.10	38.10	12.70	38.10	180	CAT-6, 4 pair UTP Copper, Fibre, Coaxial
■	M-116-427	Black on White/Transparent	38.10	63.50	19.05	63.50	80	25 pair Copper, 4-12 pair Fibre, Coaxial
⊐	M-33-427	Black on White/Transparent	38.10	101.60	38.10	25.40	70	50 pair Copper, 24 pair Fibre, Backbone
⊐	M-34-427	Black on White/Transparent	38.10	152.40	38.10	38.10	40	100 pair Copper, 36 pair Fibre, Backbone
⊐	M-21-427-YL	Black on Yellow/Transparent	25.40	63.50	25.40	19.05	80	25 pair Copper, 4-12 pair Fibre, Coaxial
⊐	M-23-427-YL	Black on Yellow/Transparent	25.40	101.60	25.40	25.40	70	50 pair Copper, 24 pair Fibre, Backbone
■	M-31-427-YL	Black on Yellow/Transparent	38.10	25.40	12.70	25.40	200	CAT-6, 4 pair UTP Copper, Fibre, Coaxial