



# METAL

## POWER DISTRIBUTION

Hubbell has developed a family of high performance power distribution units (PDUs) for use in data centers, telecommunication rooms and remote equipment enclosures. Hubbell's PDUs are provided in a wide variety of horizontal and vertical configurations such as: metered and unmetered, with or without surge protection, power load, receptacle count and receptacle configurations. Each PDU is 100% tested and inspected to assure reliable and clean conditioned power to the active electronics.





# POWER DISTRIBUTION

<b>PRODUCT</b>	<b>PAGE</b>
VERTICAL POWER STRIPS . . . . .	03
HORIZONTAL POWER STRIPS, RACK MOUNT . . . . .	05
INTELLIGENT POWER STRIPS . . . . .	07



**Equipment Safeguard**

Added surge protection provides the reliability needed to protect the mission critical equipment investment.



**Configurability**

Available in single phase and 3-phase options specifying IEC or standard NEMA plugs.



**Flexibility**

Customize each power strip circuit with 15, 20, 30, 40 and 50A receptacles.



**Administration**

Environmental and power consumption monitoring assuring 24/7 uptime.

**HUBBELL  
Advantage**


- Constructed with Hubbell Premium Receptacles
- Multiple Bracket Options to Suit Every Application
- Steady, Reliable Uninterrupted Conditioned Power
- Environmental and Power Consumption Monitoring

**Specifications**

- Housing material: cold-rolled steel
- Housing finish: black powder coat
- AC voltage: 120V or 250V
- Current rating: 15, 20, 30 or 60A
- Outlets: NEMA 5-15R or 5-20R or IEC C-13 or C-19
- Input plug cord: 10' cable with NEMA plug, IEC 320 C-20 inlet, or 60A IEC 309 plug
- Surge protection:
  - Protection modes: L-N, L-G, N-G
  - Joule rating: 720



PR20620



Full length  
mounting bracket



PR10420

**Power Strips, Vertical Mount**

Contents: 1 strip, 1 kit mounting hardware, universal mounting brackets

Electrical Specification	Receptacle Type	Outlets Front	Plug Type	No. of Circuits	Surge Protected	Switch	Current Monitor	Catalog No.
15A-120V	NEMA 5-15R	10	NEMA 5-15P	1	No	No	No	<b>PR104</b>
20A-120V	NEMA 5-20R	10	NEMA 5-20P	1	No	No	No	<b>PR10420</b>
15A-120V	NEMA 5-15R	20	NEMA 5-15P	1	No	No	No	<b>PR206</b>
20A-120V	NEMA 5-20R	20	NEMA 5-20P	1	No	No	No	<b>PR20620</b>
20A-120V	NEMA 5-20R	20	NEMA 5-20P	1	No	No	No	<b>PR20620TL****</b>
20A-120V	NEMA 5-20R	20	NEMA 5-20P	1	No	Yes	Yes	<b>PR20820DRTL*</b>
30A-120V	NEMA 5-20R	20	NEMA L5-30P	1	No	No	No	<b>PR20830</b>
20/16A/circuit 120V	NEMA 5-20R	20	NEMA 5-20P	2	No	No	No	<b>PR20820A**</b>
20/16A-120/250V	IEC 320C-13	20	IEC 320 C20	1	No	No	No	<b>PR20820I***</b>
30/24A-250V	IEC 320C-13	24	NEMA L6-30P	1	No	No	No	<b>PR24</b>

\*PR20820DRTL features a digital current meter and a 20A Twist-Lock® plug.

\*\*PR20820A features (2) 20A circuits each fed by 10' cable with NEMA 5-20 plug.

\*\*\*PR20820I includes an IEC 320 (C-20) inlet for power input.

\*\*\*\*PR20620TL includes a Twist-Lock® plug.

**Mounting Brackets for Vertical Power Strips**

Description	Catalog No.
L-brackets: turned "in" for rack/rail mounting; turned "out" extend mounting options an additional 8 inches	<b>PRSLB4</b>
For left, right, front or back rail mounting; may be installed in conjunction with other equipment mounted in the same "U" space	<b>PREZB</b>



PREZB



PRSLB4





### Configurations

Available standard 15A and 20A front and rear mounting options.



### Reliability

Standard horizontal front mounting 10-20A IEC320-C13 receptacles for active equipment in cabinet rear.



### Flexibility

Transformer spaced power strip, recessed 8-15A receptacles, 4 on front and 4 on rear.

### Equipment Safeguard

Added surge protection provides the reliability needed to protect the mission critical equipment investment.

## HUBBELL Advantage

- Manufactured Premium Hubbell Receptacles
- Easy to Install with Multiple Bracket Options
- Surge Protection
- Environmental and Power Consumption Monitoring

### Specifications

- Housing material: cold-rolled steel
- Housing finish: black powder coat
- AC voltage: 120V or 250V
- Current rating: 15, 20, 30 or 60A
- Outlets: NEMA 5-15R or 5-20R or IEC C-13 or C-19
- Input plug cord: 10' cable with NEMA plug, IEC 320 C-20 inlet, or 60A IEC 309 plug
- Surge protection:
  - Protection modes: L-N, L-G, N-G
  - Joule rating: 720



# HORIZONTAL POWER STRIPS, RACK MOUNT



MCCPSS19TS



HPWPWR



PRPMB



PR10720



PRAMB



PREZB



PRSLB4

## Power Strips, Horizontal

Delivery: 1 strip, 1 kit mounting hardware

Electrical Specification	Receptacle Type	Outlets		Mounting Style	Surge Protected	Transformer Spaced	Switch	Current Monitor	Catalog No.
		Front	Rear						
15A-120V	NEMA 5-15R	0	10	Flush	No	No	Yes	No	<b>HPWPWR</b>
15A-120V	NEMA 5-15R	0	10	Flush	Yes	No	Yes	No	<b>MCCPSS19</b>
15A-120V	NEMA 5-15R	4	4	Recess	Yes	Yes	No	No	<b>MCCPSS19TS</b>
20A-120V	NEMA 5-20R	0	10	Flush	No	No	No	No	<b>PR10120</b>
20/16A, 120/250V	IEC 320C-13	10	0	Flush	No	No	No	No	<b>PR10720*</b>
15A-120V	NEMA 5-15R	0	6	Flush	No	No	No	No	<b>PR0615</b>
20A-120V	NEMA 5-20R	0	10	Flush	No	No	Yes	Yes	<b>PR1020</b>
60A-250V	IEC 320C-19	0	3	Adjustable	No	N/A	CB/Switch	No	<b>PR0360**</b>

\*PR10720 includes an IEC 320 (C-20) inlet for power input. Vertical mount brackets are also included.

\*\*PR0360 features 10' cable with IEC 60A 2P/3W plug.

## Mounting Brackets for Horizontal Power Strips

Description	Catalog No.
Adjustable mount brackets; allows numerous recess or flush mount options.	<b>PRAMB</b>
Panel mount brackets; ideal for zero 'U' mounting applications by effectively allowing the unit to be hung from a cross beam or flat surface.	<b>PRPMB</b>

Type	Catalog No.	Integral Fixed Brackets	Pre-Assembled Brackets Included	Optional Brackets Available
<b>19" Rack Mount</b>	HPWPWR MCCPSS19 PR10120 PR0615 PR1020	Flush Mount	N/A	N/A
	MCCPSS19TS	N/A	Recess Mount	PRAMB PRPMB
	PR10720	N/A	Flush Mount and PRSLB4	PREZB
	PR0360	N/A	PRAMB	PRPMB



**60, 80, 120A/250V Solutions**

for the most demanding data center applications.

**Power**

for those most demanding, multiple blade server applications.

**Remote Monitoring**

to maximize uptime and life span of active equipment.

**User-Defined**

current thresholds.

**Local**

current meter.

**Application Support**

for applications with a mix of power receptacles — NEMA and IEC.

**Numerous**

power cord types.

**Vertical Mounting Arrangements**

ideally suited for data center and cabinet applications.

**HUBBELL  
Advantage**

- **Advanced Monitoring and Alert Capabilities to Help Ensure the Maximum Life Span for Active Equipment**
- **3-Phase WYE Configurations Support Multiple Voltage (120/208) Applications and Minimize Input Cabling**
- **Support for the Simple to the Most Advanced Data Center Applications**
- **Local and Remote Monitoring Optimize Power Consumption**

**Specifications**

- Housing material: cold-rolled steel
- Housing finish: durable, black powder coat
- FCC Part 15, Class A conformance
- Web based GUI
- SNMP v1
- AC voltage: 125, 250, 120/208
- Current rating: 20, 30, 60, 80, 120A
- Phase: single, 3~ WYE, 3~ DELTA
- Frequency: 50/60Hz
- Input plug type: various, NEMA, straight blade, TWIST-LOCK®, Pin and Sleeve, none – conduit connection access provided
- Receptacles: various NEMA and IEC

**Standards**

- UL and cUL Listed 60950



**Metal PLUGTRAK® 5ft Base and Cover**

Amp	Circuits	# Single Receptacles	Receptacle Spacing Inches (mm)	Catalog No.
15	Single	10	6 (15)	<b>HBL20GB506xx</b>
15	Single	5	12 (31)	<b>HBL20GB512xx</b>
15	Two	5	12 (31)	<b>HBL20GBA512xx</b>
15	IG/Single	5	12 (31)	<b>HBL20IG512xx</b>
20	Single	10	6 (15)	<b>HBL24GB506xx</b>
20	Single	5	12 (31)	<b>HBL24GB512xx</b>
20	Two	5	12 (31)	<b>HBL24GBA512xx</b>

xx = Color: **IV** (Ivory) and **GY** (Gray).

**Metal PLUGTRAK® 6ft Base and Cover**

Amp	Circuits	# Single Receptacles	Receptacle Spacing Inches (mm)	Catalog No.
15	Single	12	6 (15)	<b>HBL20GB606xx</b>
15	Single	8	9 (23)	<b>HBL20GB609xx</b>
15	Single	6	12 (31)	<b>HBL20GB612xx</b>
15	Single	4	18 (46)	<b>HBL20GB618xx</b>
15	Two	8	9 (23)	<b>HBL20GBA609xx</b>
15	Two	6	12 (31)	<b>HBL20GBA612xx</b>
15	Two	4	18 (46)	<b>HBL20GBA618xx</b>
15	IG/Single	12	6 (15)	<b>HBL20IG606xx</b>
20	Single	12	6 (15)	<b>HBL24GB606xx</b>
20	Single	6	12 (31)	<b>HBL24GB612xx</b>
20	Single	4	18 (46)	<b>HBL24GB618xx</b>
20	Two	6	12 (31)	<b>HBL24GBA612xx</b>
20	Two	4	18 (46)	<b>HBL24GBA618xx</b>

xx = Color: **IV** (Ivory) and **GY** (Gray).

**Boxes and Fittings**

Description	Catalog No.
One-gang device box	<b>HBL2048xx</b>
Two-gang device box	<b>HBL20482xx</b>
Internal corner coupling	<b>HBL2017TC*</b>
External elbow	<b>HBL2018Cxx</b>
Flat elbow	<b>HBL2011xx</b>
Tee	<b>HBL2015xx</b>
Entrance end fitting	<b>HBL2010A2xx</b>
Large entrance end fitting	<b>HBL2010A3xx</b>
Blank end fitting	<b>HBL2010Bxx</b>
Cover clip	<b>HBL2006xx</b>
Supporting clip	<b>HBL2003SC*</b>
Coupling	<b>HBL2001C*</b>

xx = Color: **IV** (Ivory) and **GY** (Gray).

\*Finish: galvanized steel.

**Portable Metal PLUGTRAK®**

Amp	Circuits	# Single Receptacles	Length Inches (mm)	Cord Length Feet (mm)	Catalog No.
15	Single	6	40" (1016)	6' (1829)	<b>HBL20C215xx</b>
15	Single	8	64" (1626)	6' (1829)	<b>HBL20C315xx</b>

xx = Color: **IV** (Ivory) and **GY** (Gray).

Note: Hubbell Metal PlugTrak is supplied with two HBL2010BIV (Ivory) or HBL2010BGY (Gray) Blank End Fittings and one HBL2001C. Outlets match raceway color. "IG" Isolated receptacles are Orange.