



TLS 2200®/TLS PC Link™ Labels

TLS 2200®/TLS PC Link™ Label Index By Size (Continued)

TLS 2200®/TLS PC Link™ Label Index By Size

Diagram	Catalog Number	Labels Per Roll	Material	Color	B-Number	Label Width Inch (mm) A	Label Height Inch (mm) B	Write-On Height Inch (mm) C	Wire Gauge
1.000" (Continued)									
Fig. 8	PTL-42-439-BK	Continuous	Vinyl	Black	B-439	1.000 (25.4)	50 ft. (15.2 m)	–	–
Fig. 8	PTL-42-439-BL	Continuous	Vinyl	Blue	B-439	1.000 (25.4)	50 ft. (15.2 m)	–	–
Fig. 8	PTL-42-439-GR	Continuous	Vinyl	Green	B-439	1.000 (25.4)	50 ft. (15.2 m)	–	–
Fig. 8	PTL-42-439-OR	Continuous	Vinyl	Orange	B-439	1.000 (25.4)	50 ft. (15.2 m)	–	–
Fig. 8	PTL-42-439-RD	Continuous	Vinyl	Red	B-439	1.000 (25.4)	50 ft. (15.2 m)	–	–
Fig. 8	PTL-42-439-YL	Continuous	Vinyl	Yellow	B-439	1.000 (25.4)	50 ft. (15.2 m)	–	–
Fig. 8	PTL-42-483	Continuous	Polyester	White	B-483	1.000 (25.4)	50 ft. (15.2 m)	–	–
Fig. 8	PTL-42-489	Continuous	Polyester	White	B-489	1.000 (25.4)	50 ft. (15.2 m)	–	–
1.015"									
Fig. 20	PSPT-094-1-WT	100	Polyolefin	White	B-342	1.015 (25.8)	0.182 (4.6)	–	28 to 18
Fig. 20	BPSPT-094-1-WT	2500	Polyolefin	White	B-342	1.015 (25.8)	0.182 (4.6)	–	28 to 18
Fig. 20	PSPT-094-1-YL	100	Polyolefin	Yellow	B-342	1.015 (25.8)	0.182 (4.6)	–	28 to 18
Fig. 20	BPSPT-094-1-WT	2,500	Polyolefin	White	B-342	1.015 (25.8)	0.182 (4.6)	–	–
Fig. 20	PSPT-094-1-BK	100	Polyolefin	Black	B-342	1.015 (25.8)	0.182 (4.6)	–	–
Fig. 20	PSPT-094-1-BL	100	Polyolefin	Blue	B-342	1.015 (25.8)	0.182 (4.6)	–	–
Fig. 20	PSPT-094-1-BR	100	Polyolefin	Brown	B-342	1.015 (25.8)	0.182 (4.6)	–	–
Fig. 20	PSPT-094-1-GR	100	Polyolefin	Green	B-342	1.015 (25.8)	0.182 (4.6)	–	–
Fig. 20	PSPT-094-1-GY	100	Polyolefin	Grey	B-342	1.015 (25.8)	0.182 (4.6)	–	–
Fig. 20	PSPT-094-1-OR	100	Polyolefin	Orange	B-342	1.015 (25.8)	0.182 (4.6)	–	–
Fig. 20	PSPT-094-1-PK	100	Polyolefin	Pink	B-342	1.015 (25.8)	0.182 (4.6)	–	–
Fig. 20	PSPT-094-1-RD	100	Polyolefin	Red	B-342	1.015 (25.8)	0.182 (4.6)	–	–
Fig. 20	PSPT-094-1-VT	100	Polyolefin	Violet	B-342	1.015 (25.8)	0.182 (4.6)	–	–
Fig. 20	PSPT-094-1-WT	100	Polyolefin	White	B-342	1.015 (25.8)	0.182 (4.6)	–	–
Fig. 20	PSPT-094-1-YL	100	Polyolefin	Yellow	B-342	1.015 (25.8)	0.182 (4.6)	–	–
Fig. 20	PSPT-125-1-WT	100	Polyolefin	White	B-342	1.015 (25.8)	0.235 (6.0)	–	22 to 16
Fig. 20	BPSPT-125-1-WT	1000	Polyolefin	White	B-342	1.015 (25.8)	0.235 (6.0)	–	22 to 16
Fig. 20	PSPT-125-1-YL	100	Polyolefin	Yellow	B-342	1.015 (25.8)	0.235 (6.0)	–	22 to 16
Fig. 20	BPSPT-125-1-WT	1,000	Polyolefin	White	B-342	1.015 (25.8)	0.235 (6.0)	–	–
Fig. 20	PSPT-125-1-BK	100	Polyolefin	Black	B-342	1.015 (25.8)	0.235 (6.0)	–	–
Fig. 20	PSPT-125-1-BL	100	Polyolefin	Blue	B-342	1.015 (25.8)	0.235 (6.0)	–	–
Fig. 20	PSPT-125-1-BR	100	Polyolefin	Brown	B-342	1.015 (25.8)	0.235 (6.0)	–	–
Fig. 20	PSPT-125-1-GR	100	Polyolefin	Green	B-342	1.015 (25.8)	0.235 (6.0)	–	–
Fig. 20	PSPT-125-1-GY	100	Polyolefin	Grey	B-342	1.015 (25.8)	0.235 (6.0)	–	–
Fig. 20	PSPT-125-1-OR	100	Polyolefin	Orange	B-342	1.015 (25.8)	0.235 (6.0)	–	–
Fig. 20	PSPT-125-1-PK	100	Polyolefin	Pink	B-342	1.015 (25.8)	0.235 (6.0)	–	–
Fig. 20	PSPT-125-1-RD	100	Polyolefin	Red	B-342	1.015 (25.8)	0.235 (6.0)	–	–
Fig. 20	PSPT-125-1-VT	100	Polyolefin	Violet	B-342	1.015 (25.8)	0.235 (6.0)	–	–
Fig. 20	PSPT-125-1-WT	100	Polyolefin	White	B-342	1.015 (25.8)	0.235 (6.0)	–	–

Figure 8




Figure 20

