

# HC22R Series



## 200 AMP MAINS - 200 AMP / POSITION c/w Blank Compartment

CATALOGUE #	DESCRIPTION	METER POSITIONS	ENCLOSURE SIZE A X B X C	WEIGHT
HC22R	2 gang, 200 Amp main, 200 per position	2	15 <sup>1</sup> / <sub>8</sub> " x 5 <sup>3</sup> / <sub>8</sub> " x 26 <sup>1</sup> / <sub>2</sub> "	42 lbs.
HC23R	3 gang, 200 Amp main, 200 per position	3	15 <sup>1</sup> / <sub>8</sub> " x 5 <sup>3</sup> / <sub>8</sub> " x 35 <sup>1</sup> / <sub>4</sub> "	58 lbs.
HC24R	4 gang, 200 Amp main, 200 per position	4	15 <sup>1</sup> / <sub>8</sub> " x 5 <sup>3</sup> / <sub>8</sub> " x 44"	74 lbs.

- Blank compartment on left side for underground
- Factory Bussed - 200 Amp Mains
- 4 Jaw meter socket
- 200 Amp - 600 Volts per position
- CSA enclosure 3
- Approved conductor range:  
Line 6-250 MCM AWG CU/AL  
Load No. 6-250 MCM AWG
- Combination OH/UG
- Used primarily in Cambridge, Ontario

- Order "SXC" hubs separate
- Approved for overhead or underground use
- Use SXC503 for 5th jaw at 9 O'clock

KNOCKOUT CODE	CONDUIT SIZE
G	1 <sup>1</sup> / <sub>4</sub> ", 1 <sup>1</sup> / <sub>2</sub> ", 2", 2 <sup>1</sup> / <sub>2</sub> "
AA	1 <sup>1</sup> / <sub>2</sub> "
F	1 <sup>1</sup> / <sub>4</sub> ", 1 <sup>1</sup> / <sub>2</sub> ", 2", 2 <sup>1</sup> / <sub>2</sub> ", 3"

