

Commercial Enclosures



CONTINUOUS BUSBAR TROUGHS CUSTOM MADE NEMA 1



Application

General purpose enclosure designed for indoor distribution. Plenty of wiring space and connection flexibility. Constructed of 12 gauge

- Padlockable cover, Hinged cover
- Available with aluminum or copper bus bars

How to Order:

Example - BBT800AL6F3W

BBT - Bus bar trough

800 - Current rating

AL - Aluminum / CU - Copper

6F - Length of trough in feet

3W - 3 wire / 4W - 4 wire

- All lug requirements must be specified, add suffix "L" to part number if required

MAINS CAPACITY AMP	TROUGH DIMENSIONS			
	3 WIRE		4 WIRE	
	H	D	H	D
225	19	7	19	7
400	19	7	21	7
600	19	7	21	7
800	19	7	23	8
1000	23	8	27	8
1200	23	8	27	8
1600	23	8	27	8
2000	25	10	30	10
2500	25	10	30	10

Technical Readout

CATALOGUE AMPERAGE	WIDTH INCHES	DEPTH INCHES	LENGTH (X) IN FEET									
			3	4	5	6	7	8	9	10	11	12
			WEIGHT IN LBS.									
225-3	13	5	36	46	57	66	76	117	131	—	—	—
400-3	19	7	63	102	124	142	164	192	214	242	—	—
600-3	19	7	74	120	147	167	193	226	252	285	306	332
800-3	19	7	74	120	147	167	193	226	252	285	306	332
1000-3	23	8	—	—	188	211	247	288	324	365	389	424
1200-3	23	8	—	—	188	211	247	288	324	365	389	424
1600-3	23	8	—	—	—	235	277	324	365	413	436	423
2000-3	25	10	—	—	—	313	332	389	439	501	522	572
2500-3	25	10	—	—	—	398	472	468	536	598	626	686
225-4	16	5	44	54	66	79	90	108	120	—	—	—
400-4	19	7	73	120	145	171	192	234	264	291	—	—
600-4	21	7	93	150	184	217	242	282	315	348	373	406
800-4	23	8	93	150	184	217	242	282	315	348	373	406
1000-4	27	8	—	—	234	277	305	237	402	453	481	525
1200-4	27	8	—	—	234	277	305	237	402	453	481	525
1600-4	27	8	—	—	—	317	345	406	457	517	445	597
2000-4	30	10	—	—	—	438	477	557	622	708	748	819
2500-4	30	10	—	—	—	524	569	662	748	842	887	974