



TLS 2200®/TLS PC Link™ Label Index By Size (Continued)

Diagram	Catalog Number	Labels Per Roll	Material	Color	B-Number	Label Width Inch (mm) A	Label Height Inch (mm) B	Write-On Height Inch (mm) C	Wire Gauge
1.015" (Continued)									
Fig. 20	PSPT-125-1-YL	100	Polyolefin	Yellow	B-342	1.015 (25.8)	0.235 (6.0)	–	–
Fig. 20	PSPT-187-1-WT	100	Polyolefin	White	B-342	1.015 (25.8)	0.335 (8.5)	–	18 to 12
Fig. 20	BPSPT-187-1-WT	1000	Polyolefin	White	B-342	1.015 (25.8)	0.335 (8.5)	–	18 to 12
Fig. 20	PSPT-187-1-YL	100	Polyolefin	Yellow	B-342	1.015 (25.8)	0.335 (8.5)	–	18 to 12
Fig. 20	BPSPT-187-1-WT	1,000	Polyolefin	White	B-342	1.015 (25.8)	0.335 (8.5)	–	–
Fig. 20	PSPT-187-1-BK	100	Polyolefin	Black	B-342	1.015 (25.8)	0.335 (8.5)	–	–
Fig. 20	PSPT-187-1-BL	100	Polyolefin	Blue	B-342	1.015 (25.8)	0.335 (8.5)	–	–
Fig. 20	PSPT-187-1-BR	100	Polyolefin	Brown	B-342	1.015 (25.8)	0.335 (8.5)	–	–
Fig. 20	PSPT-187-1-GR	100	Polyolefin	Green	B-342	1.015 (25.8)	0.335 (8.5)	–	–
Fig. 20	PSPT-187-1-GY	100	Polyolefin	Grey	B-342	1.015 (25.8)	0.335 (8.5)	–	–
Fig. 20	PSPT-187-1-OR	100	Polyolefin	Orange	B-342	1.015 (25.8)	0.335 (8.5)	–	–
Fig. 20	PSPT-187-1-PK	100	Polyolefin	Pink	B-342	1.015 (25.8)	0.335 (8.5)	–	–
Fig. 20	PSPT-187-1-RD	100	Polyolefin	Red	B-342	1.015 (25.8)	0.335 (8.5)	–	–
Fig. 20	PSPT-187-1-VT	100	Polyolefin	Violet	B-342	1.015 (25.8)	0.335 (8.5)	–	–
Fig. 20	PSPT-187-1-WT	100	Polyolefin	White	B-342	1.015 (25.8)	0.335 (8.5)	–	–
Fig. 20	PSPT-187-1-YL	100	Polyolefin	Yellow	B-342	1.015 (25.8)	0.335 (8.5)	–	–
Fig. 20	PSPT-250-1-WT	100	Polyolefin	White	B-342	1.015 (25.8)	0.439 (11.2)	–	16 to 10
Fig. 20	BPSPT-250-1-WT	1000	Polyolefin	White	B-342	1.015 (25.8)	0.439 (11.2)	–	16 to 10
Fig. 20	PSPT-250-1-YL	100	Polyolefin	Yellow	B-342	1.015 (25.8)	0.439 (11.2)	–	16 to 10
Fig. 20	BPSPT-250-1-WT	1,000	Polyolefin	White	B-342	1.015 (25.8)	0.439 (11.2)	–	–
Fig. 20	PSPT-250-1-BK	100	Polyolefin	Black	B-342	1.015 (25.8)	0.439 (11.2)	–	–
Fig. 20	PSPT-250-1-BL	100	Polyolefin	Blue	B-342	1.015 (25.8)	0.439 (11.2)	–	–
Fig. 20	PSPT-250-1-BR	100	Polyolefin	Brown	B-342	1.015 (25.8)	0.439 (11.2)	–	–
Fig. 20	PSPT-250-1-GR	100	Polyolefin	Green	B-342	1.015 (25.8)	0.439 (11.2)	–	–
Fig. 20	PSPT-250-1-GY	100	Polyolefin	Grey	B-342	1.015 (25.8)	0.439 (11.2)	–	–
Fig. 20	PSPT-250-1-OR	100	Polyolefin	Orange	B-342	1.015 (25.8)	0.439 (11.2)	–	–
Fig. 20	PSPT-250-1-PK	100	Polyolefin	Pink	B-342	1.015 (25.8)	0.439 (11.2)	–	–
Fig. 20	PSPT-250-1-RD	100	Polyolefin	Red	B-342	1.015 (25.8)	0.439 (11.2)	–	–
Fig. 20	PSPT-250-1-VT	100	Polyolefin	Violet	B-342	1.015 (25.8)	0.439 (11.2)	–	–
Fig. 20	PSPT-250-1-WT	100	Polyolefin	White	B-342	1.015 (25.8)	0.439 (11.2)	–	–
Fig. 20	PSPT-250-1-YL	100	Polyolefin	Yellow	B-342	1.015 (25.8)	0.439 (11.2)	–	–
Fig. 20	PSPT-375-1-WT	100	Polyolefin	White	B-342	1.015 (25.8)	0.645 (16.4)	–	12 to 6
Fig. 20	BPSPT-375-1-WT	1000	Polyolefin	White	B-342	1.015 (25.8)	0.645 (16.4)	–	12 to 6
Fig. 20	PSPT-375-1-YL	100	Polyolefin	Yellow	B-342	1.015 (25.8)	0.645 (16.4)	–	12 to 6
Fig. 20	BPSPT-375-1-WT	1,000	Polyolefin	White	B-342	1.015 (25.8)	0.645 (16.4)	–	–
Fig. 20	PSPT-375-1-BK	100	Polyolefin	Black	B-342	1.015 (25.8)	0.645 (16.4)	–	–
Fig. 20	PSPT-375-1-BL	100	Polyolefin	Blue	B-342	1.015 (25.8)	0.645 (16.4)	–	–

