

# DWR Series Wall Cabinet

## Dimensions

12 RU - 28" h x 24.34" w x (17, 22, 26, 32)" d  
 18 RU - 38.6" h x 24.34" w x (17, 22, 26, 32)" d  
 24 RU - 49" h x 24.34" w x (17, 22, 26, 32)" d

## Construction

Welded Steel

## Finish

durable black textured powder coat

## Weight Capacity

**12 RU - 200 lbs.**

**18 RU - 250 lbs.**

**24 RU - 300 lbs.**

**UL Listed in  
US and Canada  
to 300 lbs.**

Seismic certified to the following codes and standards: 2007 & 2010 CBC; 2006, 2009 & 2012 IBC; ASCE 7-05 (2005 Edition) & ASCE 7-10 (2010 Edition) and the 2006 & 2009 editions of NFPA 5000 for use in areas of high seismicity – Zone 4 or Seismic Design Category (SDC) "D". These are designed for Mission Critical and/or High-Importance Installations in locations with the highest level of seismicity and top floor or rooftop installations including those within UBC and CBC Essential facilities or IBC, ASCE 7, and NFPA 5000 Seismic Use Group III facilities. For all codes, the Importance factor (Ip) is 1.5. Seismic Certified load capacity of 140 lbs. when used with DWRSR-ZL Latch.



**Includes 50 rack screws 10-32**

**UNIQUE DUAL-PIVOT! allows reversal of center section opening without removing equipment**

**DWR-18-22**



US PATENT #7,278,183

EIA/TIA Compliant



Spec. #  
**96-045**  
for full  
product  
info.



## CABINET WITH PLEXIGLASS DOOR

17" Deep Part # (15" Useable)	22" Deep Part # (20" Useable)	26" Deep Part # (24" Useable)	Description
DWR-12-17PD	DWR-12-22PD	DWR-12-26PD	2 ft. wall cabinet (28.06" overall height); 12 RU (21" useable height)
DWR-18-17PD	DWR-18-22PD	DWR-18-26PD	3 ft. wall cabinet (38.56" overall height); 18 RU (31.5" useable height)
DWR-24-17PD	DWR-24-22PD	DWR-24-26PD	4 ft. wall cabinet (49.06" overall height); 24 RU (42" useable height)

## CABINET ONLY

17" Deep Part # (15" Useable)	22" Deep Part # (20" Useable)	26" Deep Part # (24" Useable)	32" Deep Part # (30" Useable)	Description
DWR-12-17	DWR-12-22	DWR-12-26	DWR-12-32	2 ft. wall cabinet (28.06" overall height); 12 RU (21" useable height)
DWR-18-17	DWR-18-22	DWR-18-26	DWR-18-32	3 ft. wall cabinet (38.56" overall height); 18 RU (31.5" useable height)
DWR-24-17	DWR-24-22	DWR-24-26	DWR-24-32	4 ft. wall cabinet (49.06" overall height); 24 RU (42" useable height)

## ENCLOSURE OPTIONS

Accessory Type	12 RU Part #	18 RU Part #	24 RU Part #	Description
front doors	FD-12	FD-18	FD-24	solid front door
	VFD-12	VFD-18	VFD-24	perforated front door
	PFD-12	PFD-18	PFD-24	smoked plexi-glass front door
rackrail	DWR-RR12	DWR-RR18	DWR-RR24	additional set of #10-32 mounting rails

## FAN KITS

17" Deep Part # (15" Useable)	22" Deep Part # (20" Useable)	26" Deep Part # (24" Useable)	32" Deep Part # (30" Useable)	Description
DWR-FK17	DWR-FK22	DWR-FK26	DWR-FK32	fan kits include (2) 4-1/2" fans, (4) guards, and vent blockers to optimize airflow

## RECOMMENDED ACCESSORIES

Accessory Type	Part #	Description
power strip	PD-815SC-NS	18" power strip with (8) 5-15R outlets and 10 ft. cord with 5-15P plug
	PD-915R	1 RU rackmount power distribution unit (9) outlet, 15 Amp, 9 ft. cord
shelving	VSA-1626*	< 1 RU 4-point mounting shelf adjustable 16-26 deep, 400 lbs. weight capacity
	U2V	2 RU front mount shelf 14.5" deep 50 lb. weight capacity - vented
hardware	HP	100 pieces additional mounting screws

\*requires rear rackrail

