

ACTUATOR-/INDICATOR COMPONENT LAMP HOLDER
BA 9S WITHOUT LAMP SCREW TERMINAL RATED
VOLTAGE ACC.TO LAMP



Contact block/ lampholder:

Product designation		lampholder
Number of NC contacts / for auxiliary contacts		0
Number of NO contacts / for auxiliary contacts		0
Number of changeover contacts / for auxiliary contacts		0
Product function / positive opening		No
Number of lampholders		1
Execution of the mounting		BA 9s
Design of the electrical connection		screw-type terminals

General technical data:

Degree of pollution		class 3
Voltage type / of operating voltage		AC/DC
Reference code <ul style="list-style-type: none"> • according to DIN EN 61346-2 • according to DIN 40719 extended according to IEC 204-2 / according to IEC 750 		P H
Ambient temperature <ul style="list-style-type: none"> • during operating • during storage 	°C °C	-25 ... +60 -25 ... +80
protection type IP		

<ul style="list-style-type: none"> • of the terminal • of the enclosure 		IP20 IP40
Operating voltage		
<ul style="list-style-type: none"> • at 50 Hz / at AC / rated value 	V	6 ... 230
<ul style="list-style-type: none"> • at 60 Hz / at AC / rated value 	V	6 ... 230
<ul style="list-style-type: none"> • for DC • rated value 	V	6 ... 230
Suitability for integration		
<ul style="list-style-type: none"> • pressure selection button 		Yes
<ul style="list-style-type: none"> • front element 		Yes
<ul style="list-style-type: none"> • suspension switch 		Yes
<ul style="list-style-type: none"> • suspension pushbutton 		Yes
Insulation voltage / rated value	V	250
Impulse voltage resistance / rated value	kV	4
Tightening torque / for auxiliary contacts / with screw-type terminals	N·m	0.8
Product component		
<ul style="list-style-type: none"> • fluorescent materials 		No
<ul style="list-style-type: none"> • diode 		No
<ul style="list-style-type: none"> • lamp transformer 		No
<ul style="list-style-type: none"> • series resistance 		No
Mounting type		front mounting
Width	mm	10
Height	mm	36.5
Depth	mm	20

Connections/ terminals:

Type of the connectable conductor cross-section

- for auxiliary contacts / solid
- for auxiliary contacts / solid / with conductor end processing
- for auxiliary contacts / finely stranded / with conductor end processing
- for AWG conductors / for auxiliary contacts

2x (1.0 ... 1.5 mm²)
2x (0.5 ... 0.75 mm²)
2x (0.5 ... 1.5 mm²)
2x (18 ... 14)

Certificates/ approvals:

General Product Approval

Declaration of Conformity

other



[Confirmation](#)

[Environmental Confirmations](#)

Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrial-controls/mall>

Cax online generator


<http://www.siemens.com/cax>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3SB3400-1A/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3SB3400-1A



last change:

Apr 21, 2014