

ARMADILLO ALUMINUM FLEXIBLE CONDUIT CSA

AFCSA
Heavy wall (CSA)

Made from high strength aluminum alloy

- Exceptional strength and appearance
- 1/3 of the weight of steel
- For use in dry locations
- CSA # LL63215



Made in Canada



Armadillo-Aluminum Flex

Part #	Trade Sizes (Inches)	Inside Diameter (Inches)	Outside Diameter (Inches)		Weight Per Coil CSA	Bend Diameter (Inches)	Standard Coils (Meters)	Standard Reels (Meters)
		Min.	Min.	Max.				
AFCSA031	10 (5/16")	7.92 (.312)	11.94(.470)	12.95 (.510)	6 kg	76.2 (3)	150	
AFCSA038	12 (3/8")	9.52 (.375)	14.23(.560)	15.49 (.610)	8 kg	101.6 (4)	75	150/300
AFCSA044	14 (7/16")	11.1 (.437)	N/A	17.15 (.675)	8 kg	101.6 (4)	75	150/300
AFCSA050	16 (1/2")	15.88 (.625)	21.85 (.860)	23.37 (.920)	8 kg	152.4 (6)	30	150/300
AFCSA075	21 (3/4")	20.62 (.812)	26.55 (1.045)	28.07 (1.105)	10 kg	203.2 (8)	30	150
AFCSA100	27 (1")	25.40 (1.000)	33.02 (1.300)	35.05 (1.380)	17 kg	254 (10)	30	120
AFCSA125	35 (1 1/4")	31.75 (1.250)	39.37 (1.550)	41.40 (1.630)	10 kg	305 (12)	15	75
AFCSA150	41 (1 1/2")	38.10 (1.500)	46.99 (1.850)	49.53 (1.950)	12 kg	381 (15)	15	45
AFCSA200	51 (2")	50.80 (2.000)	59.69 (2.350)	62.23 (2.450)	15 kg	508 (20)	15	30
AFCSA250	63 (2 1/2")	63.50 (2.500)	72.65 (2.860)	77.72 (3.060)	20 kg	635 (25)	15	
AFCSA300	78 (3")	76.20 (3.000)	85.35 (3.360)	90.42 (3.560)	21 kg	762 (30)	15	
AFCSA350	91 (3 1/2")	88.90 (3.500)	98.05 (3.860)	103.12 (4.060)	26 kg	889 (35)	15	
AFCSA400	103 (4")	101.60 (4.000)	110.75 (4.360)	115.82 (4.560)	32 kg	1016 (40)	15	

Custom lengths available upon request. Longer reel lengths are available—reel deposit depending on length. Please contact our office for more details.

A company as flexible as its product...

SUPERIOR FLEXIBLE CONDUITS INC.