



# HIGH POWER CORDLESS LED FLOODLIGHTS

The original LED work-light



IP65

Lithium-Ion Battery  
**LED**

listed in  
**LUCKINS**  
DATABASE



The FLOOD-IT range comes with  
**2 years warranty** as standard



# ESSENTIAL

Sharing all the same high quality build and components of our professional range the FLOOD-IT ESSENTIAL is perfect for the DIY enthusiast and home owner.

Up to 400 Lumens




The compact size means its easily stowed away and very portable, great for reading the metre, home plumbing or keeping in the car as part of a breakdown and emergency kit.

You'll be amazed how convenient it is to have a floodlight available at any time.

The ESSENTIAL has a 3 hour working time and a 3 hour charge time.

- Up to 400lm/5watt
- Perfect for home use
- DIY
- Use as part of a breakdown kit
- Camping

Lithium-Ion Battery  
**LED**



**ESSENTIAL**  
FLEB CW

The FLOOD-IT range comes with  
2 years warranty as standard

LED Total Power	5W
Light Source	1 x 5W integrated LED
Unit dimension	115 x 82 x 185 mm
LED luminous Flux	400lm
Input Voltage	12V DC / 24V DC
Colour Temperature	Cool white 5,500k - 6,000k
Colour rendering index	Ra>70
Housing material	Aluminum & Iron
Adaptor	Input 100-240V AC 50/60Hz Output 12V DC 10000mA
Working Temperature	-25° to 50°C
Charging Temperature	0° to 45°C
Beam Angle	120°
Battery type	7.4V, 4.4Ah Lithium-ion
Charging time	3 hours
Working time	Over 3 hours
Certificates	IP65, CE, ROHS
Life Span	50,000 hrs
Warranty	2 years or 500 full charges



# THE PRO RANGE

The FLOOD-IT **PRO** is the ultimate work light. Specifically designed to be transported from job to job. This will literally change the way you work.

900 Lumens

**PRO**  
FL10 CW

**PRO6**  
FL10 CW6

- 900lm/10watt
- Tool box essential
- 4 hours working time
- Extended 6 hour battery upgrade available
- Mains and car charger included

The **PRO** range is a portable light that works with high quality lithium-ion batteries and LED chips giving clear bright light for up to 6 hours on one charge, meaning you can push on and get the job done.

Available in 5 colours to suit your need.

The **PRO** comes with mains and in-car charger so you can charge the battery on the go.



The **PRO** also has a range of accessories:

- **Magnetic feet** gives you the ability to secure the light from a height from any metal surface
- **Tripod**, Up to 3 of the **PRO** units can be secured to the tripod which is lightweight and easily transported
- **Solar Panel** can be used to power and charge the **PRO** if mains electricity is not available

**10W** **4/6hr** **120°**  
POWER SOURCE    RUNNING TIME    BEAM ANGLE

LED Total Power	10W
Light Source	1 x 10W integrated LED
Unit dimension	145 x 160 x 240 mm
LED luminous Flux	900lm
Input Voltage	12V DC / 24V DC
Colour Temperature	Cool white 5,500k - 6,000k
Colour rendering index	Ra>70
Housing material	Aluminum & Iron
Adaptor	Input 100-240V AC 50/60Hz
	Output 12V DC 10000mA
Working Temperature	-25° to 50°C
Charging Temperature	0° to 45°C
Beam Angle	120°
Battery type	7.4V, 4.4Ah Lithium-ion
Charging time	<b>PRO:</b> 5 hours <b>PRO6:</b> 8 hours
Working time	<b>PRO:</b> Up to 4 hrs <b>PRO6:</b> Over 6 hrs
Certificates	IP65, CE, ROHS
Life Span	50,000 hrs
Warranty	2 years or 500 full charges

Telephone: 01291 622 388

# THE PRIME RANGE

The **PRIME** & **PRIME8**.

**THE** working tool for serious illumination on the go.

1800 Lumens

## PRIME

FL20CW

- Ideal for lighting a scene
- No trailing leads
- No generators
- Mains and car charger included



The high power LED light that offers a robust and reliable solution to portable lighting in tough situations.

Used by railway maintenance, the coast guard and the Emergency Services; No trailing leads No generator just safe portable lighting.

The top of the range **PRIME8** is equipped with a dimmer switch enabling the battery life to be extended as the lumen level is lowered.

20W

POWER SOURCE

over 3hr

RUNNING TIME

120°

BEAM ANGLE

## PRIME8

FL20GCW8D

- 30 hours from 1 charge
- Standard working time, over **9 hours**
- Mains and car charger included

LED Total Power	20W
Light Source	1 x 20W integrated LED
Unit dimension	215 x 185 x 285 mm
LED luminous Flux	1800lm
Input Voltage	12V DC / 24V DC
Colour Temperature	Cool white 5,500k - 6,000k
Colour rendering index	Ra>70
Housing material	Aluminum & Iron
Adaptor	Input 100-240V AC 50/60Hz Output 12V DC 10000mA
Working Temperature	-25° to 50°C
Charging Temperature	0° to 45°C
Beam Angle	120°
Battery type	7.4V, 4.4Ah Lithium battery
Charging time	<b>PRIME:</b> 5 hours <b>PRIME8:</b> 10 hours
Working time	<b>PRIME:</b> Over 3 hours <b>PRIME8:</b> Over 9-30 hrs (with dimmer)
Certificates	IP65, CE, ROHS
Life Span	50,000 hrs
Warranty	2 years or 500 full charges



IP65

20W

POWER SOURCE

over 9hr

RUNNING TIME

up to 30hr

USING DIMMER



# THE RGB RANGE

THE colour changing light available as **PRO** and **PRIME**.



With the use of a remote control the lighting effects can be set to colour change or can be left on a consistent colour.

An amazingly versatile light. From wedding venues to festivals, the RGB creates no hassle ambience easily enhancing any event cost effectively.

Even offshore oil companies and the Emergency Services have found uses for these lights, colour coding hazardous and safe areas ensuring the right working conditions for their staff.

- Colour rotation
- Continuous colour selection
- Remote control
- Great for events
- Colour coding working areas to safety standards
- Mains and car charger included



Lithium-Ion Battery  
**LED**

## PRORGB

FL10B RGB

<b>10W</b>	<b>4hr</b>	<b>120°</b>
<b>POWER SOURCE</b>	<b>RUNNING TIME</b>	<b>BEAM ANGLE</b>

**900 Lumens**



## PRIMERGB

FL20B RGB

**1800 Lumens**

<b>20W</b>	<b>3hr</b>
<b>POWER SOURCE</b>	<b>RUNNING TIME</b>
<b>120°</b>	
<b>BEAM ANGLE</b>	



LED Total Power	<b>PRO: 10W PRIME: 20W</b>
Light Source	<b>PRO: 1 x 10W integrated LED</b> <b>PRIME: 1 x 20W integrated LED</b>
Unit dimension	<b>PRO: 145 x 160 x 240</b> <b>PRIME: 215 x 185 x 285 mm</b>
LED luminous Flux	<b>PRO: 900lm PRIME: 1800lm</b>
Input Voltage	12V DC / 24V DC
Colour Temperature	RGB
Colour rendering index	Ra>70
Housing material	Aluminum & Iron
Adaptor	Input 100-240V AC 50/60Hz Output 12V DC 1,000 mA
Working Temperature	-25° to 50°C
Charging Temperature	0° to 45°C
Beam Angle	120°
Battery type	<b>PRO: 7.4V, 4.4Ah Lithium-ion</b> <b>PRIME: 7.4V, 8.8Ah Lithium-ion</b>
Charging time	<b>PRO: 5 hours PRIME: 5 hours</b>
Working time	<b>PRO: Up to 4 hours</b> <b>PRIME: Over 3 hours</b>
Certificates	IP65, CE, ROHS
Life Span	50,000 hours
Warranty	2 years or 500 full charges

**Telephone: 01291 622 388**

# THE PIR RANGE

Using FLOOD-IT LED and battery technology combined with advances in high performance solar, the PIR range is ideal for stand alone set ups and applications.

900/1800 Lumens



## PROPIR

FL10 PIR

## PRO6PIR

FL10 PIR6

## PRIMEPIR

FL20 PIR

The sensor on the base makes this perfect for off grid security or movement sensitive lighting.

Hooked up to our solar panel for complete independence from the electricity grid. The solar panel can be used with both the PRO and PRIME units without the sensor for a continuous-charge from day light.

Solar Panel sold separately

- PIR available in:
  - PRO 4hr
  - PRO 6hr
  - PRIME
- Off grid lighting
- self sufficient security lighting

LED Total Power	10W/20W
Light Source	<b>PRO/PRO6:</b> 1 x 10W integrated LED <b>PRIME PIR:</b> 1 x 20W integrated LED
Unit dimension	<b>PRO/PRO6:</b> 115 x 117 x 195 mm <b>PRIME PIR:</b> 215 x 185 x 285 mm
LED Luminous Flux	<b>PRO/PRO6:</b> 900lm <b>PRIME PIR:</b> 1800lm
Input Voltage	12V DC / 24V DC
Colour Temperature	Cool white 5,500k - 6,000k
Colour rendering index	Ra>70
Housing material	Aluminum & Iron
Adaptor	Input 100-240V AC 50/60Hz Output 12V DC 1,000mA
Working Temperature	-25° to 50°C
Charging Temperature	0° to 45°C
Beam Angle	120°
Battery type	<b>PRO:</b> 7.4V, 4.4Ah Lithium battery <b>PRO6 PIR:</b> 7.4V, 6.4Ah Lithium battery <b>PRIME PIR:</b> 7.4V, 6.4Ah Lithium battery
Charging time	<b>PRO PIR:</b> 5 hours <b>PRO6 PIR:</b> 8 hours <b>PRIME PIR:</b> 10 hours
Working time	<b>PRO PIR:</b> Up to 4 hrs <b>PRO6 PIR:</b> Over 6 hrs <b>PRIME PIR:</b> Over 3 hrs
Certificates	IP65, CE, ROHS
Life Span	50,000 hrs
Warranty	2 years or 500 full charges

Lithium-Ion Battery

**LED**



POWER SOURCE



RUNNING TIME



BEAM ANGLE



# ACCESSORIES

FLOOD-IT accessories have been designed to enhance the range providing even more lighting solutions.



## SOLAR PANEL

Charge your FLOOD-IT with the power of daylight. The FLOOD-IT solar panel can be used with any of our models in the range. Using it with a PIR means you have the added benefit of a sensor, making it perfect for security lighting.

## TRIPOD

Our tripod will hold 3 PRO FLOOD-IT's and/or 2 PRIME's. Sturdy and easy to put up/take down. Great for site use.

## MAGNETIC FEET

Detachable, strong and easy to apply. For attaching your FLOOD-IT to any metal surface.

## FOOD SAFETY

We have specifically designed this food safe lens to be used within catering conditions where regulations insist upon it.



- Many other options and extras available, see our website for full details



The range features all the benefits of the rechargeable FLOOD-IT, fully IP65 rated which mean these statics are suitable for hard hitting weather, a chip life of up to 50,000 hours and an extended cable, no more fiddly installations!

900 Lumens

10W/PIR

Power	10W
LED	Epistar
Input Voltage	between AC100 - 240V
Luminous flux	900LM
Power factor	>0.95
Material	Alu+toughened glass
CCT	Only CW
CRI	≥70
Lifespan	≥50,000 Hrs
IP	IP65
Beam angle	45/90/120/160
Working temp	-30°C ~ 60°C
Net weight	0.72kg

1 Metre  
EXTENDED  
CABLE

10W

POWER  
SOURCE

120°

BEAM  
ANGLE



**FLOOD-IT**  
BUILT TO LAST

**THE STATIC RANGE**

NEW to the range FLOOD-IT statics.

[www.broadnetsolutionsltd.co.uk](http://www.broadnetsolutionsltd.co.uk)



# Premium Quality Static Floodlights



20W  
POWER  
SOURCE

120°  
BEAM  
ANGLE

IP65

1800 Lumens

## 20W/PIR

Power	20W
LED	Epistar
Input Voltage	between AC100 - 240V
Luminous flux	1800LM
Power factor	>0.95
Material	Alu+toughened glass
CCT	Only CW
CRI	≥70
Lifespan	≥50,000 Hrs
IP	IP65
Beam angle	45/90/120/160
Working temp	-30°C ~ 60°C
Net weight	1.04kg



The FLOOD-IT range comes with  
**2 years warranty** as standard

Telephone: 01291 622 388

IP65



2700 Lumens

30W

POWER SOURCE

120°

BEAM ANGLE

## 30W/PIR

Power	30W
LED	Epistar
Input Voltage	between AC100 - 240V
Luminous flux	2700LM
Power factor	>0.95
Material	Alu+toughened glass
CCT	Only CW
CRI	≥70
Lifespan	≥50,000 Hrs
IP	IP65
Beam angle	45/90/120/160
Working temp	-30°C - 60°C
Net weight	1.4kg



# THE STATIC RANGE