SIEMENS

Product data sheet 3RV1021-0JA10



CIRCUIT-BREAKER SIZE S0, FOR MOTOR PROTECTION, CLASS 10, A-REL. 0.7 ...1A, N-REL. 13A, SCREW TERMINAL, STANDARD SWITCHING CAPACITY

General technical data:		
product brand name		SIRIUS
Product designation		circuit breaker
Size of the circuit-breaker		S0
Number of poles / for main current circuit		3
Product function		
 removable terminal for auxiliary and control circuit 		No
overload protection		Yes
phase disturbance recognition		Yes
short-circuit to earth recognition		No
Product component		
auxiliary switch		No
undervoltage release mechanism		No
trip indicator		No
Product extension		
auxiliary switch		Yes
optional / motor drive		No
Impulse voltage resistance / rated value	V	6,000
Protection class IP / on the front		IP20
Protection against electrical shock		finger-safe

m	2,000
	25g / 11 ms
°C	-50 + 80
°C	-50 + 80
°C	-20 +70
W	6
	°C °C

Main circuit:		
Operating voltage / rated value	V	690
Type of voltage		AC/DC
Service power / at AC-3 / at 400 V / rated value	kW	0.25
Operating current / at AC-3 / at 400 V / rated value	Α	1
Mechanical operating cycles as operating time / of the main contacts / typical		100,000
Frequency of operation / with AC-3 / maximum	1/h	15

Auxiliary circuit:	
Number of changeover contacts / for auxiliary contacts	0

Protection function:		
Trip class		CLASS 10
Adjustable response current / of the current-dependent overload release	Α	0.7 1
Breaking capacity limit short-circuit current (Icu)		
• at 400 V / rated value	kA	100
• at 500 V / rated value	kA	100
• at 690 V / rated value	kA	100

Installation/mounting/dimensions:		
Mounting type		screw and snap-on mounting onto 35 mm standard mounting rail according to DIN EN 50022
mounting position		any
Depth	mm	96
Height	mm	97
Width	mm	45

Connections:	
Arrangement of electrical connectors / for main current circuit	front side
Design of the electrical connection	
for main current circuit	screw-type terminals
 for auxiliary and control current circuit 	screw-type terminals
Type of the connectable conductor cross-section	

• for main contacts

• solid

• finely stranded

• with conductor end processing

stranded

• for AWG conductors / for main contacts

2x (1 ... 2.5 mm²), 2x (2.5 ... 6 mm²)

2x (1 ... 2.5 mm²), 2x (2.5 ... 6 mm²)

2x (1 ... 2.5 mm²), 2x (2.5 ... 6 mm²)

2x (14 ... 10)

Certificates/approvals:

General Product Approval











Special Test Certificate

Test Certificates

Shipping Approval







other

Confirmation

Declaration of Conformity

other

Environmental Confirmations

Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)

http://www.siemens.com/industrial-controls/catalogs

Industry Mall (Online ordering system)

http://www.siemens.com/industrial-controls/mall

Cax online generator:


http://www.siemens.com/cax


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

http://support.automation.siemens.com/WW/view/en/3RV1021-0JA10/all

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3RV1021-0JA10





last change: Mar 17, 2014