

Splice Cap Crimp Connectors

- Designed for making fast, permanent, pressure-type connections
- Solid copper sleeves require less crimping pressure
- Resist corrosion in harsh environments
- Tin-plated steel sleeves also available
- UL 486C Listed and CSA C22.2 #188 Certified; comply with Federal Specification W-S-61D




Description	Wire Combination Range (Inches)	Quantity / Package	Cat. No.
Copper Crimp Connector	600V* 18 to 10 AWG Min. 2 #18 Max. 4 #12	100 / Box	2006S
		1,000 / Bag	2006SB
Copper Crimp Connector	600V* 14 to 4 AWG Min. 2 #10 Max. 2 #6	50 / Box	2011S
		500 / Bag	2011SB

*1,000V maximum in fixtures and signs



Splice Cap Insulators

- Convenient, safe and fast installation
- Snap-on nylon construction
- Rated at 105°C (221°F) – 600V (1,000V maximum in fixtures and signs)



For Connector Model	Quantity / Package	Cat. No.
2006S	100 / Box	2007
	1,000 / Bag	2007B
2011S	50 / Box	2014
	500 / Bag	2014B

Termend® Lugs

- Convenient, safe and fast installation
- One size fits 16 AWG through 8 AWG solid or stranded wire
- Available in ring, spade and locking spade



Tongue Type	Stud Size	Quantity / Package	Cat. No.
Ring	10	50 / Box	16-8-10
Ring	1/4	50 / Box	16-8-1/4
Spade	10	50 / Box	16-8-10S
Locking Spade	10	50 / Box	16-8-10L

Four-Way Crimp Tool

- Patented design ensures even compression and reliable connectors
- Spring-loaded, cam-actuated plungers
- Fingertip adjustment for different connector sizes



Description	Cat. No.
Four-Way Crimp Tool	C-24

NM Cable Connectors

- Unique snap-in detents hold fitting firmly in place – eliminates the need for screws, lock nuts or clamps
- UL Listed and CSA Certified for 14/2, 14/3, 12/2, 12/3, 10/2, 10/3 and for double-runs of 14/2 and 12/2 NM sheathed cable



Description	Quantity	Cat. No.
12 in. NM Cable Connector	100	1050