

# Plug Fuses

## Plug Fuses: G/GP/TD/GW/GTL/GT/GSL

Mersen Plug Fuses are for industrial and residential applications. Standard non-time delay fuses are for receptacle and lighting circuits. Standard time delay fuses are for motor loads. For Canadian requirements, a type “P” fuse is used for non-motor loads and type “D” fuses are used for electric heating and cycling loads circuits. Both fuses have low melting-point temperature elements. Low-Temp time delay plug fuses have thermal sensitivity are also for cycling loads and motor circuits. Type “S” plug fuses are time delay and tamper-resistant.

## Catalog Numbers (amps)

| Catalog Number    |                    |               |                             |                        |                         |                          |
|-------------------|--------------------|---------------|-----------------------------|------------------------|-------------------------|--------------------------|
| Edison Base       |                    |               |                             |                        |                         | Type S                   |
| Non-Time Delay UL | Non-Time Delay CSA | Time-delay UL | “P” Type Non-time Delay CSA | Low-Temp Time-delay UL | “D” Type Time-delay CSA | Rejection* Time-delay UL |
| GW3               | G3                 | -             | -                           | -                      | -                       | -                        |
| GW6               | G6                 | -             | -                           | -                      | -                       | -                        |
| GW10              | G10                | -             | -                           | -                      | -                       | -                        |
| GW15              | -                  | GTL15         | GP15                        | GT15                   | TD15                    | GSL15                    |
| GW20              | -                  | GTL20         | GP20                        | GT20                   | TD20                    | GSL20                    |
| GW25              | -                  | GTL25         | GP25                        | GT25                   | TD25                    | GSL25                    |
| GW30              | -                  | GTL30         | GP30                        | GT30                   | TD30                    | GSL30                    |

FR15 Rejector Rings available

FRW Rejection removal tool available to remove FR15

\*Must be used with an SAG adaptor to fit an Edison base fuse holder.

## Type S Plug Fuse Adaptors

| Cat.No./Rating | Fuse Range - Amps |
|----------------|-------------------|
| SAG3-2/10      | 1-8/10 - 3-2/10   |
| SAG6-1/4       | 3-1/2 - 6-1/4     |
| SAG15          | 7 - 15            |
| SAG20          | 20                |
| SAG30          | 25 - 30           |

Type S adaptors screw into the Edison base and allow Type S fuses to be installed. Type S adaptors prevent the wrong ampere size fuse from being used.



## Ratings:

Volts : 125VAC  
 Amps : 3 to 30A  
 IR : 10kA I.R. AC

Choice of Edison Base, Types “P”, “D”, or “S”

## Approvals:

- UL Listed Guide JEFV, File E76208
- CSA Certified Class 142301, File 15525

