

### 3. Select Front

Select a front of the correct height (see Step 1). For additional front options, see Section 9 of the BuyLog® Catalog (GEP-1100).



Door within Door



Standard



Front Hinged to Box

| Front Height | Standard (20" wide) |                      |                     | Door Within Door (20" wide) |                      |                     | Front Hinged To Box (20" wide) |                      |                     | Standard (30" Wide) |                      |                     |
|--------------|---------------------|----------------------|---------------------|-----------------------------|----------------------|---------------------|--------------------------------|----------------------|---------------------|---------------------|----------------------|---------------------|
|              | Flush <sup>①</sup>  | Surface <sup>①</sup> | List Price, GO-134B | Flush <sup>①</sup>          | Surface <sup>①</sup> | List Price, GO-134B | Flush <sup>①</sup>             | Surface <sup>①</sup> | List Price, GO-134B | Flush <sup>①</sup>  | Surface <sup>①</sup> | List Price, GO-134B |
| 31.5"        | AF31F               | AF31S                | \$174.00            | AF31FP                      | AF31SP               | \$412.00            | AF31FD                         | AF31SD               | \$284.00            | AF31FW              | AF31SW               | \$424.00            |
| 37.5"        | AF37F               | AF37S                | 191.00              | AF37FP                      | AF37SP               | 429.00              | AF37FD                         | AF37SD               | 301.00              | AF37FW              | AF37SW               | 441.00              |
| 43.5"        | AF43F               | AF43S                | 218.00              | AF43FP                      | AF43SP               | 456.00              | AF43FD                         | AF43SD               | 328.00              | AF43FW              | AF43SW               | 468.00              |
| 49.5"        | AF49F               | AF49S                | 257.00              | AF49FP                      | AF49SP               | 495.00              | AF49FD                         | AF49SD               | 367.00              | AF49FW              | AF49SW               | 507.00              |
| 64.5"        | AF64F               | AF64S                | 326.00              | AF64FP                      | AF64SP               | 564.00              | AF64FD                         | AF64SD               | 436.00              | AF64FW              | AF64SW               | 576.00              |
| 76.5"        | AF76F               | AF76S                | 367.00              | AF76FP                      | AF76SP               | 605.00              | AF76FD                         | AF76SD               | 477.00              | AF76FW              | AF76SW               | 617.00              |

① For CSA label, add "A" suffix to catalog number.

### 4. Select Main and/or Sub-feed Breaker Kit

Select a main breaker kit appropriate for your interior type (see Step 1), amp rating and kAIC rating. If a sub-feed breaker is required, repeat this selection process.

**Circuit breakers are only included in kits ending in "WB". "WB" kits include a breaker, mounting kit and load-side lugs; rating plugs sold separately.**

| Interior Type                       | Cat. No.                     | List Price, GO-101P | Panel Amps | No. of Poles    | Breaker Rating (kAIC) |                  |           |                       |                           |      |      |  |
|-------------------------------------|------------------------------|---------------------|------------|-----------------|-----------------------|------------------|-----------|-----------------------|---------------------------|------|------|--|
|                                     |                              |                     |            |                 | 10                    | 14               | 22        | 25                    | 65                        | 100  | 200  |  |
| AQU1:<br>240 VAC,<br>1 Phase        | MB612                        | \$35.00             | 100        | 2               | THQB                  |                  | THHQB     |                       |                           |      |      |  |
|                                     | MB614                        | 80.00               | 100        | 4               | (2) THQB              |                  | (2) THHQB |                       |                           |      |      |  |
|                                     | MB512                        | 118.00              | 225        | 2               | TQD                   |                  | THQD      |                       |                           |      |      |  |
|                                     | <b>MB335WB</b>               | 3800.00             | 400        | 2               |                       |                  |           |                       | SGDA+Kit                  |      |      |  |
|                                     | MB332                        | 145.00              | 400        | 2               |                       |                  |           |                       | SGHA                      | SGLA | SGPA |  |
|                                     | MB332                        | 145.00              | 600        | 2               |                       |                  |           |                       | SGHA                      | SGLA | SGPA |  |
| AQU3:<br>208/120<br>VAC,<br>3 Phase | <b>MB332WB</b>               | 4225.00             | 600        | 2               |                       |                  |           |                       | SGHA+Kit                  |      |      |  |
|                                     | MB613                        | 35.00               | 100        | 3               | THQB                  |                  | THHQB     |                       |                           |      |      |  |
|                                     | MB616                        | 90.00               | 100        | 6 <sup>⑤</sup>  | (2) THQB              |                  | (2) THHQB |                       |                           |      |      |  |
|                                     | MB513                        | 92.00               | 225        | 3               | TQD                   |                  | THQD      |                       |                           |      |      |  |
|                                     | MB516                        | 210.00              | 400        | 6 <sup>⑤</sup>  | (2) TQD               |                  | (2) THQD  |                       |                           |      |      |  |
|                                     | MB233                        | 125.00              | 225        | 3               |                       |                  |           |                       | SFHA                      | SFLA | SFPA |  |
|                                     | <b>MB233WB</b>               | 1325.00             | 225        | 3               |                       |                  |           |                       | SFHA+Kit                  |      |      |  |
|                                     | MB2332 <sup>④</sup>          | 125.00              | 400        | 6 <sup>④⑤</sup> |                       |                  |           |                       | 2nd SFHA                  |      |      |  |
|                                     | <b>MB2332WB</b> <sup>④</sup> | 1500.00             | 400        | 6 <sup>④⑤</sup> |                       |                  |           |                       | 2nd SFHA+Kit              |      |      |  |
|                                     | <b>MB331WB</b>               | 4600.00             | 400        | 3               |                       |                  |           |                       | SGDA+Kit                  |      |      |  |
| AEU3:<br>480/277<br>Vac,<br>3 Phase | MB333                        | 160.00              | 400        | 3               |                       |                  |           |                       | SGHA                      | SGLA | SGPA |  |
|                                     | MB333                        | 160.00              | 600        | 3               |                       |                  |           |                       | SGHA                      | SGLA | SGPA |  |
|                                     | <b>MB333WB</b>               | 5100.00             | 600        | 3               |                       |                  |           |                       | SGHA+Kit                  |      |      |  |
|                                     | MB423                        | 35.00               | 100        | 3               |                       | TEY              |           |                       |                           |      |      |  |
|                                     | MB426                        | 90.00               | 100        | 6 <sup>⑤</sup>  |                       | (2) TEY          |           |                       |                           |      |      |  |
|                                     | MB133                        | 52.00               | 150        | 3               |                       | TED <sup>①</sup> |           |                       | THED                      |      |      |  |
|                                     | MB133                        | 52.00               | 150        | 3               |                       |                  |           |                       | SEHA                      | SELA | SEPA |  |
|                                     | <b>MB133WB</b>               | 1000.00             | 150        | 3               |                       |                  |           |                       | SEHA+Kit                  |      |      |  |
|                                     | MB233                        | 125.00              | 225        | 3               |                       |                  |           |                       | SFHA <sup>③</sup>         | SFLA | SFPA |  |
|                                     | <b>MB233WB</b>               | 1325.00             | 225        | 3               |                       |                  |           |                       | SFHA+Kit <sup>③</sup>     |      |      |  |
|                                     | MB2332 <sup>④</sup>          | 125.00              | 400        | 6 <sup>④⑤</sup> |                       |                  |           |                       | 2nd SFHA <sup>③</sup>     |      |      |  |
|                                     | <b>MB2332WB</b> <sup>④</sup> | 1500.00             | 400        | 6 <sup>④⑤</sup> |                       |                  |           |                       | 2nd SFHA+Kit <sup>③</sup> |      |      |  |
| <b>MB334WB</b>                      | 4600.00                      | 400                 | 3          |                 |                       |                  |           | SGHA+Kit              |                           |      |      |  |
| MB333                               | 160.00                       | 400                 | 3          |                 |                       |                  |           | SGHA <sup>③</sup>     | SGLA                      | SGPA |      |  |
| MB333                               | 160.00                       | 600                 | 3          |                 |                       |                  |           | SGHA <sup>③</sup>     | SGLA                      | SGPA |      |  |
| <b>MB333WB</b>                      | 5100.00                      | 600                 | 3          |                 |                       |                  |           | SGHA+Kit <sup>③</sup> |                           |      |      |  |


① Actual breaker rating is 18kAIC.

② Actual breaker rating is 30kAIC.


③ Actual breaker rating is 35kAIC.

④ To achieve 6 poles of subfeed, the MB233WB or MB233 kit is also required.


⑤ 6 poles of subfeed applies only to 400A and 600A interiors.



**MB513**  
Breaker Kit



**MB516**  
6-pole Breaker Kit



**MB233WB**  
"WB" Breaker Kit