

Residential Load Centers

PowerMark Gold Load Centers

Product Features - Generator Panels

- Suitable for use in accordance with Article 702 of the National Electrical Code, ANSI/NFPA 70
- Single-phase, 2 interlock 60A or 30A main breakers, 8 circuits max.
- Safety and convenience when using a generator - 14,000 peak wattage, 11,520 continuous load, 48 amps at 240 volts.
- Maintains power to such critical circuits as those for furnace, pump, refrigerator, lights.
- Connected dual breaker mechanism ensures that only one source is active at a time.



TL412R250GF/TM830FCUGEN

PowerMark Gold Load Centers Single-Phase, Three-Wire, 120/240 Vac, Two Interlocked Main Breakers Factory Installed Indoor (NEMA 1) Enclosure

Main Ampere Rating	1 Pole, 1" Spaces	2 Pole, 1" Spaces	1 Pole, 1/2" Spaces	2 Pole, 1/2" Spaces	Total 1-pole Spaces	Front Type	Feed Type	Box Number	Main Wire Size (AWG/kcmil) Cu-Al	Equipment Ground Kit	Product Number	List Price GO-137D
30	4	2	8	4	8	Flush Front	Top Bottom	3A	6-1	TGK12 included	TM830FCUGEN	\$570.00
30	4	2	8	4	8	Surface Front	Top Bottom	3A	6-1	TGK12 included	TM830SCUGEN	\$570.00
60	4	2	8	4	8	Flush Front	Top Bottom	3A	6-1	TGK12 included	TM860FCUGEN	\$570.00
60	4	2	8	4	8	Surface Front	Top Bottom	3A	6-1	TGK12 included	TM860SCUGEN	\$570.00

PowerMark Gold Load Centers Single-Phase, Three-Wire, 120/240 Vac, Two Interlocked Main Breakers Factory Installed Outdoor (NEMA 3R) Enclosure

Main Ampere Rating	1 Pole, 1" Spaces	2 Pole, 1" Spaces	1 Pole, 1/2" Spaces	2 Pole, 1/2" Spaces	Total 1-pole Spaces	Feed Type	Box Number	Main Wire Size (AWG/kcmil) Cu-Al	Equipment Ground Kit	Product Number	List Price GO-137D
30	4	2	8	4	8	Top	R2A	6-1	TGK12 included	TM830RCUGEN	\$635.00
60	4	2	8	4	8	Top	R2A	6-1	TGK12 included	TM860RCUGEN	\$635.00

PowerMark Gold Load Centers Single-Phase, Three-Wire, 120/240 Vac, Riser Panel Indoor (NEMA 1) Enclosure

Main Ampere Rating	1 Pole, 1" Spaces	2 Pole, 1" Spaces	1 Pole, 1/2" Spaces	2 Pole, 1/2" Spaces	Total 1-pole Spaces	Load Center Type	Feed Type	Box Number	Main Wire Size (AWG/kcmil) Cu-Al	Equipment Ground Kit	Product Number	List Price GO-137A
125	20	10	40	20	40	Combination Flush/Surface Front	Top	9A	6-2/0	TGK12 (order separately)	TLM2012CCURP	\$380.00
125	12	6	24	10	24	Combination Flush/Surface Front	Top	4A	6-2/0	TGK12 (order separately)	TLM1212CCURP	\$300.00

Tap kits required, order separately. See page 1-29.
Auxiliary gutters available. See page 1-29.

PowerMark Gold Load Centers Single-Phase, Three-Wire 120/240 Vac, Spa Panel Outdoor (NEMA 3R) Enclosure

Main Ampere Rating	1 Pole, 1" Spaces	2 Pole, 1" Spaces	1 Pole, 1/2" Spaces	2 Pole, 1/2" Spaces	Total 1-pole Spaces	Load Center Type	Feed Type	Box Number	Main Wire Size (AWG/kcmil) Cu-Al	Equipment Ground Kit	Product Number	List Price GO-137A
125	4	2	8	4	8	Factory Included 50A GFCI	Top Bottom		1-2/0	TGL1 installed	TL412R250GF	\$925.00
125	4	2	8	4	8	Factory Included 60A GFCI	Top Bottom		1-2/0	TGL1 installed	TL412R260GF	\$925.00

Twist Lock Power Inlets

Receptacles	Amps	Volts	UL	Product Number	List Price GO-137G
L14-20	20	120/240	Canada, US	T020N	\$115.00
L14-30	30	120/240	Canada, US	T030N	\$125.00
CS637	50	120/240	Canada, US	T050N	\$200.00



Publications and Reference: See Section 22 for a complete list of additional product-related publications