

# GE Meter Centres

## TMPC Residential Meter Stack Modules - 5 Jaw Design

- Stacks with 1-phase horizontal bus are rated 240/120V, 1-phase, 3-wire. Stacks with 3-phase horizontal bus are rated 208Y/120V, 3-phase, 4-wire but can be used on 240/120V, 3-phase, 4-wire delta systems.
- All 3-phase horizontal bus modules have 4-wire, 800A cross bus and all stacks are factory balanced for ease of installation.
- Short circuit ratings up to 100,000A RMS symmetrical depending upon Ale rating of installed main tenant circuit breakers and main device.
- Lay-in Lug is attached to back of every cell. Removal of K/O allows ground cable to run from cell to cell.
- Main tenant feeders can exit top or bottom. Knockouts are available at all exit locations.
- Type 3R enclosure. If being used in outdoor application and exiting the top, mount Myer type hubs on rainproof cap.
- Provision for 2-pole breaker. Plug-on type for 125A Meters and bolt-on type for 200A Meters. Circuit breakers not included..
- Available in three and six Meter socket configuration, 5 jaw standard.

Amperes per Meter Socket	Number of Meter Sockets	Bus Ampacity	Enclosure Type	1-Phase Horizontal Bus (3 Horizontal Bus Bars - A, B and Neutral)	3-Phase Horizontal Bus (4 Horizontal Bus Bars - A, B, C and Neutral)	Main Tenant Breaker Type  For Specific Catalogue Number refer to page 9
				Catalogue Number	Catalogue Number	
125	3	800	Indoor & Outdoor	-	TMPC8312R <sup>(1)</sup>	Plug on Type TMQRL TMQRHL TMQL
	6		Indoor & Outdoor	TMPC612 <sup>(1)</sup>	TMPC8612R <sup>(1)</sup>	
200	3	800	Indoor & Outdoor	TMPC612R <sup>(1)</sup>	TMPC8320R <sup>(1)</sup>	Bolt-on Type TMQRD TMQ TMQRHD

### Wire Sizes: Neutral and Ground Lugs

- Each stack includes a neutral and ground bar.
  - If an extra ground bar is needed order 1 MMGBK
- 1) Fifth jaw at 9 o'clock position included as standard.  
Can be field adjusted to the 3, or 6, or 12 o'clock position.


LUG IN METER SOCKET MODULES	WIRE SIZE, AI/CU
Branch Neutral	#6-2/0
125A socket module	
Branch Neutral	#1/0-300 kcmil
200A socket module	
Equipment Ground Bar	#14-#2
125A socket module	
Equipment Ground Bar	#14-2/0
200A socket module	
Optional Ground Bar (1 MMGBK)	#6-2/0




imagination at work

# GE Meter Centres

## TMPC, 125A - 5 Jaw Design




TMPC8312R




TMPC612R / TMPC8612R

## TMPC, 200A - 5 Jaw Design




TMPC320R / TMPC8320R

## TMPC, 100A & 200A - 7 Jaw Design



TMPC312420R / TMPC312410R



TMPC312120R



imagination at work

[www.ge-ed.ca](http://www.ge-ed.ca)  
[www.geindustrial.com](http://www.geindustrial.com)  
 1-800-GE-1STOP