

## MASONRY DRILLING

### HAMMER DRILL BITS

#### FASTER DRILLING


- Unique flute geometry provides efficient dust and debris removal

#### STARTS ON CONTACT

- Patented self-centering carbide tip maintains hole placement

#### NO SPIN

- 3-Flat shank holds bit secure in drill chuck



Size	Part Number	Useable Length	Overall Length	Pack Qty	Size	Part Number	Useable Length	Overall Length	Pack Qty
1/8"	48-20-8800	1-1/2"	3"	2	3/4"	48-20-8845	4"	6"	1
5/32"	48-20-8801	4"	6"	2	3/4"	48-20-8846	10"	12"	1
3/16"	48-20-8805	2"	4"	2	7/8"	48-20-8847	4"	6"	1
3/16"	48-20-8806	4"	6"	2	7/8"	48-20-8848	10"	12"	1
1/4"	48-20-8810	2"	4"	1	1"	48-20-8849	4"	6"	1
1/4"	48-20-8811	4"	6"	1	1"	48-20-8854	10"	12"	1
1/4"	48-20-8812	10"	12"	1	3/16"	48-20-8957	4"	6"	5
5/16"	48-20-8816	4"	6"	1	1/4"	48-20-8961	2"	4"	5
5/16"	48-20-8817	10"	12"	1	1/4"	48-20-8962	4"	6"	5
3/8"	48-20-8821	4"	6"	1	1/8"	48-20-8900	1-1/2"	3"	25
3/8"	48-20-8822	10"	12"	1	5/32"	48-20-8901	4"	6"	25
3/8"	48-20-8823	16"	18"	1	3/16"	48-20-8905	2"	4"	25
7/16"	48-20-8825	4"	6"	1	3/16"	48-20-8906	4"	6"	25
1/2"	48-20-8830	4"	6"	1	1/4"	48-20-8910	2"	4"	25
1/2"	48-20-8831	10"	12"	1	1/4"	48-20-8911	4"	6"	25
1/2"	48-20-8832	16"	18"	1	5/16"	48-20-8916	4"	6"	25
9/16"	48-20-8835	4"	6"	1	3/8"	48-20-8921	4"	6"	20
5/8"	48-20-8840	4"	6"	1	7/16"	48-20-8925	4"	6"	20
5/8"	48-20-8841	10"	12"	1	1/2"	48-20-8930	4"	6"	15
5/8"	48-20-8842	16"	18"	1	5/8"	48-20-8940	4"	6"	10

### HAMMER DRILL BIT SETS

3 Pc 3-Flat SECURE-GRIP™ Hammer Drill Bit Set 48-20-8850	5 Pc 3-Flat SECURE-GRIP™ Hammer Drill Bit Set 48-20-8851
<b>Includes:</b> <ul style="list-style-type: none"> <li>■ 5/32" x 6"</li> <li>■ 3/16" x 6"</li> <li>■ 1/4" x 6"</li> </ul>	<b>Includes:</b> <ul style="list-style-type: none"> <li>■ 5/32" x 6"</li> <li>■ 3/16" x 6"</li> <li>■ 1/4" x 6"</li> <li>■ 5/16" x 6"</li> <li>■ 3/8" x 6"</li> </ul>
6 Pc 3-Flat SECURE-GRIP™ Hammer Drill Bit Set 48-20-8856	7 Pc 3-Flat SECURE-GRIP™ Hammer Drill Bit Set 48-20-8852
<b>Includes:</b> <ul style="list-style-type: none"> <li>■ (2) 1/4" x 6"</li> <li>■ 5/32" x 6"</li> <li>■ 3/16" x 6"</li> <li>■ 5/16" x 6"</li> <li>■ 3/8" x 6"</li> </ul>	<b>Includes:</b> <ul style="list-style-type: none"> <li>■ (2) 3/16" x 6"</li> <li>■ (2) 1/4" x 6"</li> <li>■ 5/32" x 6"</li> <li>■ 5/16" x 6"</li> <li>■ 3/8" x 6"</li> </ul>

### SDS+ ROTARY HAMMER BITS

#### 4-CUTTER PREMIUM MX4 SDS+ CARBIDE BITS

##### LONG LIFE

- 4-Cutter solid carbide tip for up to 3X life in rebar



##### ACCURATE HOLES

- Centering tip and 4-Cutter design drills more accurate holes for anchoring applications

Size	Useable Length	Overall Length	Individual Part Number	Bulk Part Number	Bulk Qty
3/16"	2"	4"	48-20-7310	-	-
3/16"	4"	6"	48-20-7311	48-20-7911	15
3/16"	6"	8"	48-20-7312	-	-
3/16"	8"	10"	48-20-7313	-	-
3/16"	10"	12"	48-20-7314	-	-
1/4"	2"	4"	48-20-7330	-	-
1/4"	4"	6"	48-20-7331	48-20-7931	15
1/4"	6"	8"	48-20-7332	-	-
1/4"	8"	10"	48-20-7334	-	-
1/4"	10"	12"	48-20-7335	-	-
5/16"	4"	6"	48-20-7341	-	-
3/8"	4"	6"	48-20-7351	48-20-7951	10
3/8"	10"	12"	48-20-7354	-	-
3/8"	16"	18"	48-20-7357	-	-
1/2"	4"	6"	48-20-7371	48-20-7971	10
1/2"	10"	12"	48-20-7374	-	-
1/2"	16"	18"	48-20-7377	-	-

#### 4-CUTTER SDS+ BITS

##### DURABLE

- 4-Cutter design lasts longer when encountering small diameter rebar and mesh

##### ACCURATE STARTS

- Centering point ensures correct hole placement

##### FASTER DRILLING

- Unique face design directs dust through the 4 fluted spiral for faster drilling

Size	Part Number	Useable Length	Overall Length
5/8"	48-20-7200	6"	8"
5/8"	48-20-7203	10"	12"
5/8"	48-20-7206	16"	18"
3/4"	48-20-7210	6"	8"
3/4"	48-20-7215	10"	12"
3/4"	48-20-7220	16"	18"
7/8"	48-20-7225	6"	8"
7/8"	48-20-7230	10"	12"
7/8"	48-20-7236	16"	18"
1"	48-20-7240	8"	10"
1"	48-20-7246	16"	18"
1-1/8"	48-20-7250	8"	10"
1-1/8"	48-20-7256	16"	18"