

Safety Switches

Double-Throw Switches

Section 4

Spec-Setter™ Safety Switches

Type TC, Type TDT

240, 480, 600 Volts AC

250 Volts DC

Three-pole, 240 Volts AC, 250 Volts DC, No Fuse

Ampere Rating	Enclosure Type	HP, 240 Vac, NEC Std, 3-ph	HP, 480 Vac, NEC Std, 3-ph	HP, 600 Vac, NEC Std, 3-ph	Lug Wire Size, AWG/kcmil, Cu Only	Product Number
30A	NEMA Type 1	2	–	–	14-8	TC35321
60A	NEMA Type 1	3	–	–	14-4	TC35322
100A	NEMA Type 1	7 1/2	–	–	14-1/0	TC35323
200A	NEMA Type 1	15	–	–	6-250	TC35324
400A	NEMA Type 1	30	–	–	(2)1/0-250 or #2-600	TC35325
600A	NEMA Type 1	50	–	–	(2)3/0-350 or #2-600	TC35326 ²

Three-pole, 240 Volts AC, 250 Volts DC, No Fuse

Ampere Rating	Enclosure Type	HP, 240 Vac, NEC Std, 3-ph	HP, 480 Vac, NEC Std, 3-ph	HP, 600 Vac, NEC Std, 3-ph	Lug Wire Size, AWG/kcmil, Cu Only	Product Number
30A	NEMA Type 3R	2	–	–	14-8	TC35321R
60A	NEMA Type 3R	3	–	–	14-4	TC35322R
100A	NEMA Type 3R	7.5	–	–	14-1/0	TC35323R
200A	NEMA Type 3R	15	–	–	6-250	TC35324R
400A	NEMA Type 3R	30	–	–	(2) 1/0-250 or #2-600	TC35325R

Three-pole, 600 Volts AC, 250 Volts DC, No Fuse

Ampere Rating	Enclosure Type	HP, 240 Vac, NEC Std, 3-ph	HP, 480 Vac, NEC Std, 3-ph	HP, 600 Vac, NEC Std, 3-ph	Lug Wire Size, AWG/kcmil, Cu Only	Product Number
30A	NEMA Type 1	10	10	10	14-4	Use 60A
60A	NEMA Type 1	10	10	10	14-4	TC35362
100A	NEMA Type 1	15	15	15	14-1/0	TC35363
200A	NEMA Type 1	30	30	30	6-250	TC35364
400A	NEMA Type 1	–	–	–	(2)1/0-250 or #2-600	TC35365 ^{1,2,5}
600A	NEMA Type 1	–	–	–	(2)3/0-350 or #2-600	TC35366 ^{1,2}

Three-pole, 600 Volts AC, 250 Volts DC, No Fuse

Ampere Rating	Enclosure Type	HP, 240 Vac, NEC Std, 3-ph	HP, 480 Vac, NEC Std, 3-ph	HP, 600 Vac, NEC Std, 3-ph	Lug Wire Size, AWG/kcmil, Cu Only	Product Number
30A	NEMA Type 3R	10	10	10	14.4	Use 60A
60A	NEMA Type 3R	10	10	10	14-4	TC35362R
100A	NEMA Type 3R	15	15	15	14-1/0	TC35363R
200A	NEMA Type 3R	30	30	30	6-250	TC35364R

240 Volts AC, Fusible

Ampere Rating	Enclosure Type	HP, 240 Vac, Time Delay, 1-ph	HP, 480 Vac, Time Delay, 1-ph	HP, 600 Vac, Time Delay, 1-ph	HP, 240 Vac, Time Delay, 3-ph	HP, 480 Vac, Time Delay, 3-ph	HP, 600 Vac, Time Delay, 3-ph	HP, DC @ 250V	Product Number
30A	NEMA Type 1	3	–	–	7 1/2	–	–	5	TDT3321
60A	NEMA Type 1	10	–	–	15	–	–	10	TDT3322
100A	NEMA Type 1	15	–	–	30	–	–	20	TDT3323
200A	NEMA Type 1	15	–	–	60	–	–	40	TDT3324 ³
400A	NEMA Type 1	–	–	–	125	–	–	50	TDT3325
600A	NEMA Type 1	–	–	–	50	–	–	50	TDT3326 ⁴
30A	NEMA Type 3R	3	7 1/2	10	7 1/2	15	20	5	TDT3321R
60A	NEMA Type 3R	10	20	25	15	30	50	10	TDT3322R
100A	NEMA Type 3R	15	30	40	30	60	75	20	TDT3323R
200A	NEMA Type 3R	15	50	50	60	125	150	40	TDT3324R ³

600 Volts AC, Fusible

Ampere Rating	Enclosure Type	HP, 240 Vac, Time Delay, 1-ph	HP, 480 Vac, Time Delay, 1-ph	HP, 600 Vac, Time Delay, 1-ph	HP, 240 Vac, Time Delay, 3-ph	HP, 480 Vac, Time Delay, 3-ph	HP, 600 Vac, Time Delay, 3-ph	HP, DC @ 250V	Product Number
30A	NEMA Type 1	3	7 1/2	10	7 1/2	15	20	–	TDT3361
60A	NEMA Type 1	10	20	25	15	30	50	–	TDT3362
100A	NEMA Type 1	15	30	40	30	60	75	–	TDT3363
200A	NEMA Type 1	15	50	50	60	125	150	40	TDT3364 ³
400A	NEMA Type 1	–	–	–	125	250	350	50	TDT3365
100A	NEMA Type 3R	15	30	40	30	60	75	20	TDT3363R
200A	NEMA Type 3R	15	50	50	60	125	150	40	TDT3364R ³

¹Not UL Listed.

²Not suitable for use as service equipment per NEC Article 702.

³200 Amp switches move load base for Class J fuses.

⁴600 Amp switch available with Class T fuse provision only.

⁵No provision for auxiliary contact kit.

