



# HEAVY-DUTY CARBIDE CIRCULAR SAW BLADES

## HEAVY-DUTY ENDURANCE® BLADES

### CONSTRUCTION AND FINISHING ENDURANCE BLADES

CATALOG NUMBER	NUMBER OF TEETH	MAX RPM	TOOTH MATERIAL	DESCRIPTION	KERF THICKNESS
<b>5-3/8" BLADE-LEFT</b>					
48-40-4100 <sup>†</sup>	18	7000	Carbide	Framing/Ripping	.063"
48-40-4104 <sup>†</sup>	36	7000	Carbide	Trim/Finish	.063"
<b>6-1/2" BLADE-LEFT</b>					
48-40-4108*	24	7000	Carbide	Framing/Ripping	.063"
48-40-4112*	40	7000	Carbide	Trim/Finish	.063"
<b>7-1/4" BLADE-LEFT</b>					
48-40-4115 <sup>◇</sup>	16	7000	Carbide	Framing/Ripping	.071"
48-40-4119 <sup>◇</sup>	24	7000	Carbide	Rip/Crosscut	.071"
48-40-4125 <sup>◇</sup>	40	7000	Carbide	Trim/Finish	.071"
<b>7-1/4" BLADE-RIGHT</b>					
48-40-4116 <sup>◇</sup>	16	7000	Carbide	Framing/Ripping	.071"
48-40-4120 <sup>◇</sup>	24	7000	Carbide	Rip/Crosscut	.071"
48-40-4126 <sup>◇</sup>	40	7000	Carbide	Trim/Finish	.071"
48-40-4128 <sup>◇</sup>	24	7000	Carbide	Rip/Crosscut	.106"
48-40-4130 <sup>◇</sup>	40	7000	Carbide	Trim/Finish	.106"
48-40-4132 <sup>◇</sup>	48	7000	Carbide	Non-Ferrous Metal Cut	.106"
48-40-4134	26	7000	Steel	Rip/Crosscut	.106"
48-40-4136	40	7000	Steel	Rip/Crosscut	.106"
48-40-4138	140	7000	Steel	Plywood/Paneling	.106"
48-40-4140 <sup>◇</sup>	-	7000	Steel	Ferrous Metal Cut	.106"
<b>8-1/4" BLADE-RIGHT</b>					
48-40-4148 <sup>◇</sup>	18	7000	Carbide	Framing/Ripping	.071"
48-40-4150 <sup>◇</sup>	24	7000	Carbide	Rip/Crosscut	.071"
48-40-4152 <sup>◇</sup>	40	7000	Carbide	Trim/Finish	.071"
48-40-4154 <sup>◇</sup>	24	7000	Carbide	Rip/Crosscut	.122"
48-40-4156 <sup>◇</sup>	40	7000	Carbide	Trim/Finish	.122"
48-40-4158	60	7000	Carbide	Trim/Finish	.122"
<b>10" BLADE-RIGHT</b>					
48-40-4160	24	6000	Carbide	Framing/Ripping	.122"
48-40-4162	40	6000	Carbide	Trim/Finish	.122"
48-40-4164	60	6000	Carbide	Trim/Finish	.122"
48-40-4166	80	6000	Carbide	Trim/Finish	.122"
48-40-4168	80	6000	Carbide	Non-Ferrous Metal Cut	.122"
<b>10-1/4" BLADE-RIGHT</b>					
48-40-4170	28	6000	Carbide	Rip/Crosscut	.122"
48-40-4172	40	6000	Carbide	Trim/Finish	.122"



- Extra Long Life
- Fast Cutting
- Straight Accurate Cuts
- Regular Or Thin Kerf
- Resists Bending And Twisting



**25-PACK OF ENDURANCE BLADES**  
**48-40-4123** 7-1/4", 24 Carbide Teeth, 7000 max. r.p.m.  
 For rip/crosscut applications.

◇ Includes diamond knockout  
 † 10mm arbor hole. All others have 5/8" arbor holes.  
 \* Alternate Top Bevel (ATB) produces a high quality finish cut.