

Residential Load Centers

PowerMark Gold and Plus Load Centers

Product Number Guides

Section 1

Product Number Guide for Load Centers

(Product number for illustrative purposes only)

T	M	42	4	20	C	CU	B
GE Identification						Insert for Specials	
Type						G or T = Factory installed ground bar B = Bottom feed main breaker FL = Factory installed feed-through lugs D = Optional door for 6-8 circuit panel. (Doors standard on all units 12 circuits or greater)	
M = Main breaker						Insert for PowerMark Gold	
L = Main lug						CU = Copper Bus	
LM = Convertible						42 = Copper Bus Full 42 circuit panel	
PL = Main lug (Thermoplastic)							
Maximum Number 1" Spaces						Enclosure Type	
2, 4, 6...42						C = Combination surface/flush	
						F = Flush	
						S = Surface	
						R = Outdoor	
Insert for 3-Phase 4-Wire Load Centers							
						Bus Ampere Rating	
						40 = 40 Amps 20 = 200 Amps	
						70 = 70 Amps 22 = 225 Amps	
						10 = 100 Amps 30 = 300 Amps	
						12 = 125 Amps 40 = 400 Amps	
						15 = 150 Amps 60 = 600 Amps	

Product Number Guide for Q-Line Plug-in Circuit Breakers

(Product number for illustrative purposes only)

T	H	QL	1	1*	15		
GE Identification						Ground Fault/Arc Fault Circuit Interrupter	
Interrupting Rating						GF = 1-pole Ground Fault Circuit Interrupter-5 mA	
H = 10kAIC						GF1= 2-pole Ground Fault Circuit Interrupter-5 mA	
HH = 22kAIC						AF = 1- & 2-pole Arc Fault Circuit Interrupter	
X = 65kAIC						GFEP = 1- & 2-pole Ground Fault Circuit Interrupter-30 mA	
Type						Ampere Rating	
QL = 1" plug-in							
QP = 1/2" plug-in							
QB = 1" bolt-on							
Poles (1, 2, 3)						Voltage	
						1 = 120/240V	
						2 = 240V	

*Omit character for THQP breakers, which are all 120/240V.

