

HACK SAW BLADES

Bi-Metal Blades

- Lasts up to 3X longer than conventional blades

Part Number	Length	TPI	Set	Pkg Qty
48-43-0600	12"	14	Raker	10
48-43-0610	12"	18	Raker	10
48-43-0620	12"	24	Wavy	10
48-43-0630	12"	32	Wavy	10

Carbide Grit Blades

- Cuts cast iron, ceramic tile, fiberglass, slate, brick and marble

Part Number	Length	TPI	Set	Pkg Qty	Description
48-43-0200	12"	Carbide Grit	Med	1	Hack Saw
48-43-0250	12"	Carbide Grit	N/A	1	Rod Saw

DRY CUT METAL CIRCULAR SAW BLADES

LONG LIFE

- Micro ground carbide teeth stay sharper longer

ACCURATE CUTS

- Fully hardened, tensioned steel plate prevents warping

FAST CUTTING

- Extra thin kerf for faster, cleaner cuts



Diameter	Part Number	# of Teeth	Tooth Material	Arbor	Max RPM	Pkg Qty	Materials
6-1/2"	48-40-4005	60	Carbide	5/8"	4,200	1	Non-Ferrous
6-1/2"	48-40-4015	48	Carbide	5/8"	4,200	1	Ferrous
6-7/8"	48-40-4006	52	Carbide	20mm	4,200	1	Non-Ferrous
6-7/8"	48-40-4016	36	Carbide	20mm	4,200	1	Ferrous
8"	48-40-4515	42	Cermet	5/8"	5,000	1	Ferrous
8"	48-40-4520	50	Cermet	5/8"	5,000	1	Ferrous
8"	48-40-4530	60	Carbide	5/8"	5,000	1	Non-Ferrous
8"	48-40-4540	60	Carbide	5/8"	5,000	1	Non-Ferrous
14"	48-40-4505	72	Carbide	1"	1,800	1	Ferrous
14"	48-40-4510	90	Carbide	1"	1,800	1	Ferrous

CONSTRUCTION CIRCULAR SAW BLADES

Diameter	Part Number	# of Teeth	Tooth Material	Arbor	Max RPM	Pkg Qty	Materials
6-1/2"	48-40-4108	24	Carbide	5/8"	7,000	1	Framing
6-1/2"	48-40-4112	40	Carbide	5/8"	7,000	1	Trim
7-1/4"	48-40-4116	16	Carbide	5/8"	7,000	1	Framing
7-1/4"	48-40-4120	24	Carbide	5/8"	7,000	1	Ripping
7-1/4"	48-40-4123	24	Carbide	5/8"	7,000	25	Ripping
7-1/4"	48-40-4126	40	Carbide	5/8"	7,000	1	Trim
7-1/4"	48-40-4132	48	Carbide	5/8"	7,000	1	Non-Ferrous
7-1/4"	48-40-4138	140	Steel	5/8"	7,000	1	Plywood
7-1/4"	48-40-4140	-	Steel	5/8"	7,000	1	Ferrous
8-1/4"	48-40-4148	18	Carbide	5/8"	7,000	1	Framing
8-1/4"	48-40-4150	24	Carbide	5/8"	7,000	1	Ripping
8-1/4"	48-40-4152	40	Carbide	5/8"	7,000	1	Trim
10"	48-40-4160	24	Carbide	5/8"	6,000	1	Framing
10"	48-40-4162	40	Carbide	5/8"	6,000	1	Trim
10"	48-40-4164	60	Carbide	5/8"	6,000	1	Trim
10"	48-40-4166	80	Carbide	5/8"	6,000	1	Trim
10"	48-40-4168	80	Carbide	5/8"	6,000	1	Non-Ferrous
10-1/4"	48-40-4170	28	Carbide	5/8"	6,000	1	Ripping
10-1/4"	48-40-4172	40	Carbide	5/8"	6,000	1	Trim