












SAWZALL® BLADES



SPECIALTY SAWZALL® BLADES



Description	TPI	Length	Height	Width	1 Pack	3 Pack	5 Pack	50 Pack	Bulk (100)
 DUCTWORK	30	3.33"	0.75"	0.050"	—	—	48-00-1630	—	—
 DRYWALL ACCESS	—	2.5"	0.75"	0.062"	48-00-1640	—	—	—	—
 FLUSH CUT	5	12"	2-1/8"	0.062"	48-00-1600	—	—	—	—
 ROUGH-IN	5	7-3/8"	1/2"	0.062"	—	—	48-00-1610	—	—
 THE TORCH™ DIAMOND GRIT	GRIT	6"	1"	0.042"	48-00-1440	—	—	—	—
	GRIT	9"	1"	0.042"	48-00-1450	—	—	—	—
 CARBIDE GRIT	GRIT	6"	3/4"	0.032"	48-00-1421	48-00-1420	—	48-01-6420	—
	GRIT	9"	3/4"	0.032"	48-00-1431	48-00-1430	—	48-01-6430	—
 PRUNING	5	9"	3/4"	0.049"	48-00-1304	—	48-00-1301	—	—
	5	12"	3/4"	0.049"	48-00-1305	—	48-00-1303	—	—
 CLEAN WOOD	6	6"	3/4"	0.050"	—	—	48-00-5015	—	48-01-7015
	6	9"	3/4"	0.050"	—	—	48-00-5016	—	48-01-7016
	6	12"	3/4"	0.050"	—	—	48-00-5017	—	—
 PLASTER	6	5"	3/4"	0.050"	—	—	48-00-5052	—	—
 METAL SCROLLING	10	3-5/8"	5/16"	0.035"	—	—	48-00-5161	—	—
	14	3-5/8"	5/16"	0.035"	—	—	48-00-5162	—	—
	18	3-5/8"	5/16"	0.035"	—	—	48-00-5163	—	—
 WOOD SCROLLING	4/6	6"	1/2"	0.050"	—	—	48-00-5041	—	—

DIAMOND GRIT THE TORCH™
48-00-1440 and 48-00-1450




IDEAL FOR CAST IRON

SCRAPER BLADES
49-00-5455, 49-00-5456 and 49-00-5463

IDEAL FOR MATERIAL REMOVAL

SAWZALL® / HACKZALL™ UTILITY BLADES

	Description GROUT REMOVAL TOOL	1 Pack 49-00-5450		Description 5" SCRAPER BLADE	1 Pack 49-00-5455		Description 3" SCRAPER BLADE	1 Pack 49-00-5456	Bulk (5) 49-01-5456
	Description 1-1/2" SCRAPER BLADE	1 Pack 49-00-5463						Bulk (5) 49-01-5463	

SAWZALL® BLADE SETS



Product No.	49-22-5403	49-22-0240	49-22-1145	49-22-0220
Description	3 PC MATERIAL REMOVAL SET	8 PC THIN KERF SAWZALL® BLADE SET	9 PC THIN KERF SAWZALL® BLADE SET	10 PC M12™ HACKZALL™ BLADE SET
Contents	(1) 1-1/2" scraper blade (1) 3" scraper blade (1) grout removal tool	(2) 6" 5TPI Thin Kerf wood blades (2) 9" 5TPI Thin Kerf wood blades (2) 6" 14TPI Thin Kerf Ice Hardened™ metal blades (2) 6" 18TPI Thin Kerf Ice Hardened™ metal blades	(3) 6" 24TPI Thin Kerf metal blades (3) 6" 14TPI Thin Kerf metal blades (2) 6" 5TPI Thin Kerf wood blades (1) 9" 5TPI Thin Kerf wood blade	(2) wood blades (3) EMT blades (2) duct blades (3) PVC blades