


Raychem JBM-100 MULTIPLE-ENTRY POWER/SPLICE/TEE CONNECTION WITH JUNCTION BOX





PRODUCT OVERVIEW

The JBM-100 kit serves as a power connection, splice, or tee for up to three Raychem brand BTV, QTVR, XTV, KTV, or VPL heating cables. It is approved by FM, CSA, PTB and IEx for use in hazardous locations.

The JBM-100 integrates the functions of connection kits and insulation entries. The rugged stand protects the heating cable and allows for up to four inches (100 mm) of thermal insulation.

The cold-applied core sealer does not require a heat gun or torch for installation, so no hot work permit is necessary. The silicone-free, noncuring sealant allows easy installation and re-entry for maintenance.

Innovative spring clamp terminals provide fast installation and safe, reliable, maintenance-free operation.

Compared with other systems, this connection kit significantly reduces installation time. The kit is offered in three versions, customized for local installation practices. All kits are also available with a plug-in LED light (-L) that indicates when power is supplied to the heating cable circuit.

The kit contains all the necessary materials for a complete installation except for the pipe straps, which must be ordered separately.

JBM-100-A, A6 JBM-100-L-A*

JBM-100-E JBM-100-L-E*

JBM-100-EP JBM-100-L-EP*

*Not for use with 480 V VPL

DESCRIPTION

This kit has a junction box This kit has a junction box This kit has a junction box with one through hole. The with two M25 threaded kit includes one stopping

entries, one stopping plug entries, an earthing plate and one plastic power cable gland.

with two M25 threaded and an external earthing stud. It is designed for use with armored power cables.

KIT CONTENTS

Note: Order appropriate pipe straps separately (two straps per kit)

- 1 junction box with terminals
- 1 stand assembly
- 3 core sealers
- 3 green/yellow tubes
- 1 3/4 in stopping plug assembly
- 1 light module (for -L only) 2 grommet plugs
- 1 junction box with terminals
 - 1 stand assembly
 - 3 core sealers
 - 3 green/yellow tubes
 - 1 M25 gland for power cable 8-17 mm in diameter
 - 2 M25 stopping plugs
 - 1 light module (for -L only) 2 grommet plugs
- 1 junction box with terminals, earth continuity plate, and
- 1 stand assembly
- 3 core sealers
- 3 green/yellow tubes
- 2 M25 stopping plugs
- 1 light module (for -L only)
- 2 grommet plugs

APPROVALS

*Not for use with 480 V VPL

Hazardous Locations



Class I, Div. 2, Groups A, B, C, D^[2]
Class II, Div. 2, Groups E, F, G^[2]
Class III^[2]



II 2G II 2D $\langle E_{X} \rangle$ Ex e II Ex tD A21 IP66

Ex e II T^[2]

PTB 09 ATEX 1056U IECEx PTB 09.0027U



II 2G Ex emb II II 2D Ex tD mbD A21 IP66

PTB 09 ATEX 1056U IECEx PTB 09.0027U





09-IEx-0004X Ex em IIC T* Gb



Ex e II T^[2] Ex em II T^[2] (for -L only)



09-IEx-0004X Ex e IIC T* Gb Ex em IIC T* Gb Ex e IIC T* Gb Ex em IIC T* Gb


IECEX JBM-100-A is IECEx certified for use with: BTV-CR/BTV-CT: IECEx BAS 06.0043X QTVR-CT: IECEx BAS 06.0045X

XTV-CT: IECEx BAS 06.0044X IECEX BAS 06.0046X IECEX BAS 06.0048X VPL-CT:


[1] Except VPL

[2] For T-rating, see heating cable or design documentation


DIMENSIONS



JBM-100-E



JBM-100-EP



	JBM-100-A, A6	JBM-100-E	JBM-100-EP
PRODUCT SPECIFICATIONS			
Heating cable capability	BTV-CR, BTV-CT, QTVR-CT, XTV-CT, KTV-CT and VPL-CT		
Ingress protection	NEMA 4X	IP66	IP66
Entries	1 x 0.75 in (1 x 1 in for A6)	2 x M25	2 x M25
Minimum installation temperature	-40°F (-40°C)	-40°F (-40°C)	-40°F (-40°C)
Minimum ambient temperature	-75°F (-60°C)*	-60°F (-50°C)*	-60°F (-50°C)*
Maximum ambient temperature	132°F (56°C)*	132°F (56°C)*	132°F (56°C)*
	* For –L lighted kits, the ambient temperature range is –40°F (–40°C) to 104°F (40°C). For non-lighted kits, use a power wire with continuous temperature rating of > 194°F (90°C). For –E and –EP kits use a metallic power cable gland.		
Maximum pipe temperature	500°F (260°C)	500°F (260°C)	500°F (260°C)
Terminals	Spring clamp Ex e 4 line, 2 ground	Spring clamp Ex e 2 phase, 2 neutral, 2 earth	Spring clamp Ex e 2 phase, 2 neutral, 2 earth
Maximum conductor size	8 AWG (A6 to 6 AWG)	10 mm ²	10 mm ²
Maximum operating voltage	480 Vac	480 Vac	480 Vac
Maximum circuit breaker rating	50 A	40 A	40 A
MATERIALS			
Enclosure	Electrostatic charge- resistant glass-filled engineered polymer, black	Electrostatic charge- resistant glass-filled engineered polymer, black	Electrostatic charge- resistant glass-filled engineered polymer, black
Lid screws	Stainless steel	Stainless steel	Stainless steel
Lid gasket	Silicone rubber	Silicone rubber	Silicone rubber
Earth continuity plate	n/a	n/a	Steel, zinc-plated and yellow-chromated
OPTIONAL LED INDICATOR LIGHT			
Color	Red	Green	Green
Voltage rating	100-277 Vac	100-277 Vac	100-277 Vac
Power consumption	< 1 W	< 1 W	< 1 W
ORDERING DETAILS			
Multiple-entry power/splice/tee conn	ection		
Catalog number	JBM-100-A / JBM-100-A6	JBM-100-E	JBM-100-EP
Part number	179955-000 / P000001376	831519-000	986415-000
Weight	4.3 lb (1.95 kg)	1.9 kg (4.2 lb)	2.1 kg (4.6 lb)
Multiple-entry power/splice/tee conn	ection with light		
Catalog number	JBM-100-L-A	JBM-100-L-E	JBM-100-L-EP
Part number	656081-000	395855-000	300273-000
Weight	5.3 lb (2.4 kg)	2.3 kg (5.1 lb)	2.5 kg (5.5 lb)



WWW.PENTAIRTHERMAL.COM

NORTH AMERICA

Tel: +1.800.545.6258 Fax: +1.800.527.5703 Tel: +1.650.216.1526 Fax: +1.650.474.7711 thermal.info@pentair.com **EUROPE, MIDDLE EAST, AFRICA**

Tel: +32.16.213.511 Fax: +32.16.213.603 thermal.info@pentair.com ASIA PACIFIC

Tel: +86.21.2412.1688 Fax: +86.21.5426.2917 cn.thermal.info@pentair.com **LATIN AMERICA**

Tel: +1.713.868.4800 Fax: +1.713.868.2333 thermal.info@pentair.com

Pentair, JBM, BTV, QTVR, XTV, KTV, and VPL are owned by Pentair or its global affiliates. All other trademarks are the property of their respective owners. Pentair reserves the right to change specifications without prior notice.

© 2001-2013 Pentair.