

ARCHITECTURAL BASEBOARD

ALUMINUM - ALUX3 SERIES



THE ARCHITECTS' CHOICE

When it comes to aesthetics, the ALUX3 is the heating unit of choice. The ALUX3 features a winning combination of style and functionality with its extruded aluminum finish and its choice of watt densities. The ALUX3 is practically indestructible due to the quality of construction of its aluminum front panel with a thickness equivalent to 10 gauge. What's more, it offers the option of adding blank sections for a seamless, uniform look. Offices, large windows and schools can all benefit from the special features of this baseboard heater.



EXTRUDED ALUMINUM FRONT COVER WITH A UNIQUE AND LUXURIOUS DESIGN

EXTREMELY SOLID, IMPACT AND RUST RESISTANT

THREE WATT DENSITIES OFFERED

NEW STYLISH WHITE SATIN FINISH

PERSONALIZED INSTALLATION

BLANK SECTIONS, PEDESTALS AND CLEAN BACKS AVAILABLE

IDEAL FOR:

OFFICES, BUSINESSES, HOTELS, LOBBIES, LARGE WINDOWS, SCHOOLS, HOSPITALS

COLOURS

- standard: white, silica white
- luxurious finish: clear anodized (see price list)
- optional: almond, black, textured charcoal, silver, nickel, champagne, light bronze, dark brown (10% surcharge)

FINISH

epoxy-polyester powdercoat or clear anodized finish

MANUFACTURING

- 3 in. x 4 in. compact profile
- solid 20-gauge steel cabinet
- extremely resistant extruded aluminum front cover with a thickness equivalent to 10 gauge
- thermal protection with automatic reset
- full-length wireway
- pencil-proof openings less than 1/4 in. (6.7 mm) prevent foreign objects from entering the unit

ELEMENT

single tubular, stainless steel sheathed element with boxed aluminum fins for improved heat dissipation; the element is securely fastened at its center, floating in nylon sleeves at each end, eliminating expansion and contraction noises

CONTROL

- wall thermostat (not included) - the use of an electronic thermostat is strongly recommended
- built-in tamper-proof thermostat accessible without removing front grille, installed in the left junction box only (optional)
- low voltage relay kit installed in the left junction box only (optional)

INSTALLATION

- surface mounted
- wall or floor mounted with or without pedestal kit (optional)
- wiring compartments at both ends of unit
- for a continuous effect, custom blank sections with a simple attach system are available (optional)

ACCESSORIES

PRODUCT	DESCRIPTION
ALUX3T12*	built-in tamper-proof single pole thermostat
ALUX3T22*	built-in tamper-proof double pole thermostat
ALUX3RE153*	built-in electronic low voltage relay [15 A @ 120V-347 V]
ALUX3RE156*	built-in electronic low voltage relay [6 A @ 600 V]
ALUX3RE153T*	built-in electronic low voltage relay c/w transformer 24 V [15 A @ 208 V-347 V]
ALUX3R841C1151*	built-in mechanical low voltage relay c/w transformer 24 V [6000 W @ 600 V]
PK5*	pedestal kit - single (kit of two)
PK5CAP	clear anodized (paint) pedestal kit - single (kit of two)
PK5D*	pedestal kit - double (kit of two)
PK5DCAP	clear anodized (paint) pedestal kit - double (kit of two)
ALUX3JS*	joiner strip (2 in. - 51 mm)
ALUX3JSCAP	clear anodized (paint) joiner strip (2 in. - 51 mm)
ALUX3IC90*	inside corner (back measures 6 1/2 in. - 165 mm long on each side)
ALUX3IC90CA	clear anodized (finish) inside corner (back measures 6 1/2 in. - 165 mm long on each side)
ALUX3OC90*	outside corner (back measures 6 1/2 in. - 165 mm long on each side)
ALUX3OC90CA	clear anodized (finish) outside corner (back measures 6 1/2 in. - 165 mm long on each side)
ALUX3CB**	clean back (fully finished, no mounting holes or knockouts)
ALUX3SA*	full width flush fit stand height of 2 to 12 in - 51 mm to 305 mm
ALUX3SR*	full width recessed stand (39/64 in. - 16 mm) - Height of 2 inches - 51 mm

Electronic relays can receive a PWM (pulsed width modulation) or digital (on/off) signal

* Add W for white or SW for silica white

* Factory installed