

## ORDERING INFORMATION

Order code: 10912  
 Description: F25T8/35K/8/RS/G13/STD ESV  
 UPC: 69549109124  
 Case quantity: 25




Nominal length : 36 in. (915 mm) Dia. : 1 in. (26 mm)

## PERFORMANCE DATA


Shape: T8  
 Base: G13 (Med Bipin)  
 Starting method: Rapid Start (RS)  
 Wattage (W): 25  
 Colour temperature (K): 3 500  
 CRI: 85  
 Rated life on IS<sup>1</sup> ballast:  
     Based on a 3 hour start 24 000  
     Based on a 12 hour start 30 000  
 Rated life on PS/PRS<sup>1</sup> ballast:  
     Based on a 3 hour start 30 000  
     Based on a 12 hour start 36 000  
 Initial lumens (lm): 2 150  
 Mean lumens (lm): 2 040  
 Nominal efficiency (lm/W): 86  
 TCLP compliant: Yes  
 Phosphor composition: Triphosphor  
 Nominal lamp operating frequency (Hz): 60  
<sup>2</sup> Minimum starting temperature (°C): -10

## DIMENSIONS



A Max	B Min / B Max	C Max
Base face to base face	Base face to end of opposite face pin	End of base pin to the end of opposite end
35.22 in.	35.40 in./35.50 in.	35.78 in.
894.6 mm	899.2 mm/901.7 mm	908.8 mm

## SPECTRAL DISTRIBUTION



<sup>1</sup> The life rating indicated is based on 3 hour burning cycles under specified conditions and with ballast meeting ANSI specifications.

<sup>2</sup> The minimum starting temperature is a function of the ballast. The minimum starting temperature is based on a STANDARD brand T8 800 series ballast.

