

## WH SERIES CONDUIT HUBS



### WH Series Watertight Conduit Hubs


WH Series Watertight Conduit Hubs features unique angled serrations that provide a larger & tighter surface plus a reliable watertight seal even with a rough or oversized knock-out. Used to connect rigid metal conduit or IMC to a threadless opening in electrical enclosures, these Watertight Conduit Hubs are rated NEMA 2, 3, 3R, 4, 4X, 5, 12, & 13 and may be used in either wet or dry applications.

Designed with a simple two-piece construction, these hubs offer positive grounding, protective insulated throats that prevent wire abrasion and an embedded O-Ring to ensure a watertight seal. Made of zinc die cast, WH Watertight Hubs features sizes from 1/2" to 4" and are also available in a grounded style.

## STRAIGHT, EXTERNAL CONDUIT THREAD

### PART NUMBERS

Hub Size	Zinc Die Cast	Grounded	A	B	Mtg. Hole (minimum)
1/2"	WH-1	WH-1-G	1.54	1.31	0.84
3/4"	WH-2	WH-2-G	1.73	1.37	1.05
1"	WH-3	WH-3-G	2.04	1.59	1.31
1 1/4"	WH-4	WH-4-G	2.42	1.59	1.66
1 1/2"	WH-5	WH-5-G	2.79	1.59	1.90
2"	WH-6	WH-6-G	3.30	1.59	2.37
2 1/2"	WH-7	WH-7-G	3.70	2.47	2.88
3"	WH-8	WH-8-G	4.39	2.47	3.50
3 1/2"	WH-9	WH-9-G	4.81	2.69	4.11
4"	WH-10	WH-10-G	5.38	2.69	4.63



- Certified for use in hazardous locations, Class II Groups E, F, G and Class III
- throat insulator & sealing ring
- 105°C rated