

## Ground Clamps

### Waterpipe Ground Clamps

Grounding



Cat. No.	Ground Wire Size	Water Pipe Size
<b>2-TB</b>	#6, #4, #2	1/2", 3/4", 1" or rebar 4-10
<b>3-TB</b>	#6, #4, #2	1-1/4", 1-1/2" or 2"
<b>4</b>	#6, #4, #2	2-1/2", 3" or 3-1/2"
<b>5-TB</b>	#6, #4, #2	4", 4-1/2" or 5"
<b>6</b>	#6, #4, #2	6"

*Malleable iron crossbar, steel U-Bolt c/w copper cable clamp with serrations.*



Cat. No.	Wire Range	Water Pipe Size
<b>3902</b>	#4-4/0 AWG	1/2"-1"
<b>3903</b>	#4-4/0 AWG	1-1/4"-2"
<b>3904</b>	#4-4/0 AWG	2-1/2"-3-1/2"
<b>3905-TB</b>	#4-4/0 AWG	4"-5"
<b>3906-TB</b>	#4-4/0 AWG	6"
<b>3907</b>	#4-4/0 AWG	8"
<b>3908</b>	#4-4/0 AWG	10"
<b>3909-TB</b>	#4-4/0 AWG	12"

*Material: Steel U-bolt and nut c/w bronzed aluminum cap and crossbar cadmium plated plus gold chromate finish.*



Cat. No.	Wire Range	Water Pipe Size
<b>3902BU*</b>	#4-4/0 AWG	1/2"-1"
<b>3903BU*</b>	#4-4/0 AWG	1-1/4"-2"
<b>3904BU*</b>	#4-4/0 AWG	2-1/2"-3-1/2"
<b>3905BU*</b>	#4-4/0 AWG	4"-5"
<b>3906BU*</b>	#4-4/0 AWG	6"
<b>3907BU*</b>	#4-4/0 AWG	8"
<b>3908BU*</b>	#4-4/0 AWG	10"
<b>3909BU*</b>	#4-4/0 AWG	12"

*Material: Bronze U-bolt and nut c/w bronzed aluminum cap and crossbar with a brite dip finish.  
\*UL Listed for Direct Burial*

## Ground Clamps




3849



3826



3840



3844

For armored and unarmored wire

### Ground Clamp



Cat. No.	Material	Water Pipe, Copper Tubing Size	Grd. Rod Size
3826*	M.I.	1/2", 3/4"	1/2"-1"
3846*	Bronze	1/2", 3/4"	1/2"-1"
3849**	Brass	1/2"-1"	-
3840-TB•	M.I.	1/2", 3/4" or 1"	-

\* For unarmored copper wire #6, #4.

\*\* For copper and aluminum conductors; for 14 thru 2 unarmored copper wire for corrosive and outdoor use. UL approved for direct burial.

• #8 thru #4 AWG. Not CSA Certified

### Ground Clamps for K&L Grade Copper Tubing Only



Cat. No.	Ground Wire Size	Water Pipe, Copper Tubing Size
3844*	#8-#4	1/2"-1"
3888**	#8-#4	1/2"-1" also rebar 4-10

\* With Steel Screws

\*\* UL approved for direct burial. silicon Bronze Screws.

## Ground Clamp Accessories



Cat. No.	Description	For use with
10102-TB	1-1/4 to 1-1/2" cables	#8-#2 Ground wire
10103-TB	2 to 4" cables	#4-4/0 Ground wire

Material: Malleable iron, zinc plating

