



# Bolts

## MACHINE BOLTS

### Square Head Machine Bolts complete with Nuts

Bolts 6" and longer made with buffer points. C.S.A. Standard Drawing No. B-3.

Minimum breaking strength at thread root:

3/8" diameter – 4,650 lbs.


1/2" diameter – 8,500 lbs.

5/8" diameter – 13,500 lbs.

3/4" diameter – 20,000 lbs.

| Cat. No.   | L     | T     | Std.Pkg. | Wt.-lbs./ C |
|--|-------|-------|----------|-------------|
| <b>3/8" Diameter Bolts complete with Hexagon Nuts:</b> |       |       |          |             |
| 1538M  | 1.1/2 | 1     | 100      | 10          |
| 238M   | 2     | 1     | 100      | 11          |
| 2538M  | 2.1/2 | 1     | 100      | 12          |
| 338M   | 3     | 1     | 100      | 13          |
| 438M   | 4     | 1     | 50       | 15          |
| 538M   | 5     | 1     | 50       | 19          |
| 638M   | 6     | 1     | 50       | 22          |
| <b>1/2" Diameter Bolts complete with Square Nuts:</b>  |       |       |          |             |
| 1512M  | 1 1/2 | 1 1/4 | 50       | 18          |
| 212M   | 2     | 1 1/4 | 50       | 21          |
| 312M   | 3     | 1 1/4 | 50       | 28          |
| 412M   | 4     | 1 1/4 | 25       | 35          |
| 512M   | 5     | 1 1/4 | 25       | 40          |
| 612M   | 6     | 1 1/4 | 25       | 45          |
| 712M   | 7     | 1 1/4 | 25       | 50          |
| 812M   | 8     | 4     | 50       | 56          |
| 1012M  | 10    | 4     | 50       | 67          |
| 1212M  | 12    | 6     | 50       | 76          |
| 1412M  | 14    | 6     | 50       | 85          |
| 1612M  | 16    | 6     | 50       | 94          |

Other sizes available upon request.



1258M



### Square Head Machine Bolts complete with Square Nuts *Cont'd*

| Cat.No.                     | L  | T     | Std. Pkg. | Wt.-lbs./ C |
|-----------------------------|----|-------|-----------|-------------|
| <b>5/8" Diameter Bolts:</b> |    |       |           |             |
| 258M                        | 2  | 1 1/2 | 25        | 38          |
| 358M                        | 3  | 1 1/2 | 25        | 45          |
| 458M                        | 4  | 1 1/2 | 25        | 54          |
| 558M                        | 5  | 1 1/2 | 25        | 62          |
| 658M                        | 6  | 1 1/2 | 50        | 70          |
| 858M                        | 8  | 4     | 50        | 86          |
| 1058M                       | 10 | 4     | 50        | 102         |
| 1058M-8                     | 10 | 8     | 50        | 102         |
| 1258M                       | 12 | 6     | 50        | 115         |
| 1458M                       | 14 | 6     | 50        | 130         |
| 1658M                       | 16 | 6     | 50        | 145         |
| 1858M                       | 18 | 6     | 25        | 160         |
| 2058M                       | 20 | 6     | 25        | 175         |
| 2258M                       | 22 | 6     | 25        | 190         |
| 2458M                       | 24 | 6     | 25        | 208         |
| 2658M                       | 26 | 6     | 25        | 226         |
| 2858M                       | 28 | 6     | 25        | 235         |
| <b>3/4" Diameter Bolts:</b> |    |       |           |             |
| 634M                        | 6  | 1 3/4 | 50        | 102         |
| 834M                        | 8  | 4     | 50        | 130         |
| 1034M                       | 10 | 4     | 50        | 150         |
| 1234M                       | 12 | 6     | 50        | 175         |
| 1434M                       | 14 | 6     | 25        | 200         |
| 1634M                       | 16 | 6     | 25        | 225         |
| 1834M                       | 18 | 6     | 25        | 245         |
| 2034M                       | 20 | 6     | 25        | 270         |
| 2234M                       | 22 | 6     | 25        | 300         |
| 2434M                       | 24 | 6     | 25        | 320         |
| 2634M                       | 26 | 6     | 25        | 340         |

Other sizes available upon request.

