



LP SERIES

All-Plastic Pictogram Exit Sign
Commercial-grade,
universal-mount and snap-fit

Type: _____
 Project/Location: _____
 Contractor: _____
 Prepared By: _____
 Date: _____
 Model No.: _____

FEATURES

The Lumacell® LP Series is a compact pictogram Exit Sign with an all-in-one, snap-fit design. Easy to install and affordable, the LP Series Exit Sign is ideally suited for commercial applications, especially those in which large numbers of Exit Signs are required.

- Durable, factory white, thermoplastic housing
- Universal mounting: wall, end, or ceiling mount
- Long-life white LED light source
- Certified CSA 22.2 No.141-10 for pictogram safety signs
- Two-wire universal AC input: 120 to 347VAC; two-wire standard DC input: 6 to 24VDC
- Energy efficient – consumes less than 2.5W in AC mode and only 1W in DC-remote
- Self-Powered model delivers standard two hours of back-up lighting
- Optional vandal-proof shield and tamper-proof screws

TYPICAL SPECIFICATIONS


Supply and install the Lumacell® LP pictogram Exit Sign. The equipment shall operate with universal 2-wire AC input voltage of 120 to 347VAC at less than 2.5W and universal 2-wire DC input voltage from 6 to 24VDC at 1W consumption for single and double face signs. The sign shall come standard with a canopy and shall be suitable for wall, end, or ceiling mounting. The frame, faceplates, back plate and canopy shall each be constructed of a one-piece UV-stabilized thermoplastic material colored factory white. The light source shall be white light-emitting diodes (LED) and shall provide even illumination in normal and emergency operation. The equipment in a Self-Powered configuration shall use a sealed Nickel-Cadmium battery of 2.4V nominal voltage. The equipment shall recharge the battery in 24 hours and stay illuminated at least two hours upon AC failure. The pictogram Exit Sign shall be listed to the CSA 22.2 No.141-10 standard.

Equipment is Lumacell® Model: _____



DIMENSIONS

Dimensions are approximate and subject to change.



POWER CONSUMPTION AND UNIT RATING

MODEL	AC SPECS		DC SPECS	
AC only	120 to 347VAC	Less than 2.5W	-	-
AC/DC standard	120 to 347VAC	Less than 2.5W	6 to 24VDC	Less than 1.5W
AC/Special DC	120 to 347VAC	Less than 2.5W	36, 48, 120VDC	Less than 2.5W
Two-wire 120V AC/DC	120Vac	Less than 2.5W	120VDC	Less than 2.5W
Self-Powered	120 to 347VAC	Less than 3W	Nickel-Cadmium Battery	Min. 2 hours

ORDERING INFORMATION

SERIES	FACES/MOUNTING	ENCLOSURE COLOUR	VOLTAGE	OPTIONS
LP= plastic pictogram	1= single face, universal mounting 2= double face, universal mounting 3= universal face, universal mounting	B= black W= factory white	S= 120 to 347VAC; self-powered U= universal 120 to 347VAC; 6 to 24VDC U00= 120 to 347VAC only U36= 120 to 347VAC 36VDC U48= 120 to 347VAC; 48VDC U120= 120 to 347VAC; 120VDC 24= 2-wire 6 to 24VDC 2120= 2-wire 120VAC/VDC	TP= tamper-proof screws* VR= vandal resistant shield with tamper-proof screws* *990.0119-L= Tamper-proof bit (sold separately) * Option VR not available with universal face

EXAMPLE: LP1WUVR