

## TOWER LIGHTS HEAVY-DUTY

### BD-1000MH HEAVY-DUTY 1000W POWER TOWER

Powerful enough to light up large construction sites, and yet collapsible to fit in a truck or SUV. The BD1000MH utilizes intense, high efficiency, metal halide bulbs that are rated for 10,000 hours and can light up to 109,000 FT<sup>2</sup>. Built to withstand the rigors of a jobsite, the stable design features a rugged aluminum fixture with a tempered glass lens. Sets up or collapses in only a couple of minutes. Removable and adjustable mast allows the light to be positioned from 19" to 12 1/2' from the ground.

The base includes all-terrain pneumatic rubber tires. Can accommodate any standard generator on its base, or run directly from a power outlet (see power requirements below).

**APPROVAL:** cETLus Certified

**BULB:** Single 1000W metal halide bulb

**LIGHT OUTPUT:** 110,000 lumens

**WEIGHT:** 125 lbs

**CONSTRUCTION:** Aluminum light fixture, tempered glass lens, steel mast and base

**POWER REQUIREMENT:** 120V 8.4A, NEMA 5-15 plug

**REPLACEMENT BULB:** P/N P100817



### BD-2000MH HEAVY-DUTY 2000W POWER TOWER

Twice the light, no compromises. With the same base and mast as the BD1000MH, the BD2000MH doubles down with two 1000W metal halide bulbs. This unit gives off an amazing amount of light and can illuminate up to 218,000 FT<sup>2</sup>.

**APPROVAL:** cETLus Certified

**BULB:** Double 1000W metal halide bulb

**LIGHT OUTPUT:** 220,000 lumens

**WEIGHT:** 200 lbs

**CONSTRUCTION:** Aluminum light fixture, tempered glass lens, steel mast and base

**POWER REQUIREMENT:** 120V 16.7A, NEMA L5-30 plug

**REPLACEMENT BULB:** P/N P100817



# INDUSTRIAL LIGHTING

## FLOOD & DOCK LIGHTS

### DOCK LIGHTS HEAVY-DUTY

#### L61 LED DOCK LIGHT

Bright, energy efficient LED technology comes to the dock light. Our L61 LED dock light shines a bright beam designed to light up the longest of trailers with no wasted light. The LEDs last over 50,000 hours (over 5 years of 24/7 use) and give off almost no heat, meaning a safer light with much less maintenance. Comes with a flexible arm, which helps to cushion the light against impact and allows for unlimited positioning.

**APPROVAL:** cULus Certified



**BULB:** 16W LED

**LIGHT OUTPUT:** 1,300 lumens

**WEIGHT:** 12 lbs

**CONSTRUCTION:** Housing made from strong polycarbonate polymer. Flexible arm allows for unlimited positioning. No glass parts, so able to be used in food processing areas.



**\$ SAVE up to \$150.00 per year in energy savings vs. traditional dock lights**

#### L41 HEAVY-DUTY HALOGEN DOCK LIGHT

Our heavy-duty docklight has what it takes to light up entire trailers so that you can get your job done no matter what time of day and no matter what weather conditions. Suitable for even wet areas, the L41 has a 40" extension arm and five pivot points to provide easy positioning. Two adjustment knobs allow fixture to pivot up and down. Safety yellow fixture, arm, and grounded 6' cord with plug. Includes 2 bulbs (1 spare).

**APPROVAL:** cULus Certified



**BULB:** 500W, 2,000 hour quartz halogen lamp included

**LIGHT OUTPUT:** 10,500 lumens

**WEIGHT:** 11 lbs

**CONSTRUCTION:** Aluminum fixture, tubular steel arm, tempered glass lens, and wire guard



**REPLACEMENT BULB:** P/N **LE86-P35**