

Pipe Straps, Pipe Clamps and Hangers

SECTION 5


Conduit and Cable Clamps

Quick Clamp II




Design Load 1 has a safety factor of 4. Design Loads 2 and 3 have a safety factor of 1.

Ordering information



Cat. No.	Dimension A EMT in. (mm)	Dimension A Rigid Conduit in. (mm)	Quantity per Box	Wt./C lb
TBQC050	1-5/16 (33.5)	1-1/4 (31.5)	100	10
TBQC075	1-3/4 (44.5)	1-11/16 (43)	100	12
TBQC100	1-13/16 (46)	1-3/4 (44.5)	100	13
TBQC125	2-1/8 (54)	2 (51)	50	15
TBQC150	2-3/8 (60.5)	2-3/16 (55.5)	50	16
TBQC200	2-5/8 (66.5)	2-1/2 (63.5)	50	19
TBQC250	3-1/16 (78)	3-1/16 (78)	25	29
TBQC300	3-11/16 (93.5)	3-11/16 (93.5)	25	34
TBQC350	4-3/16 (106.5)	4-3/16 (106.5)	25	38
TBQC400	4-11/16 (119)	4-11/16 (119)	25	42

Loading Data



Design Load 1 Static Load Limit lb (kg)	Design Load 2 lb (kg)	Design Load 3 lb (kg)
200 (90)	50 (23)	50 (23)
200 (90)	50 (23)	50 (23)
200 (90)	50 (23)	50 (23)
200 (90)	50 (23)	50 (23)
200 (90)	50 (23)	50 (23)
200 (90)	50 (23)	50 (23)
350 (158)	50 (23)	50 (23)
350 (158)	50 (23)	50 (23)
350 (158)	50 (23)	50 (23)

Cobra



Standard material is commercial-grade, bright electrogalvanized steel. Stainless steel 316L is also available; add the suffix "SS6" to catalogue no. (i.e.: CPC050SS6). Stainless steel bolt head is hexagonal and slotted only. Not available in aluminum.


Ordering information

Cat. N°	EMT Trade Size	Rigid Con. Trade Size	Cable O.D. Range (in.)	Static Load Limit (lb) Safety Factor = 4	Qty per Box	Wt./C lb
CPC050	1/2	1/2	0.650 - 0.890	200	100	10
CPC075	3/4	3/4	0.860 - 1.110	200	100	12
CPC100	1	1	1.100 - 1.400	200	100	14
CPC125	1 1/4	1 1/4	1.400 - 1.725	200	50	16
CPC150	1 1/2	1 1/2	1.690 - 1.980	200	50	18
CPC200	2	2	1.980 - 2.576	200	50	24
CPC250	2 1/2	2 1/2	2.576 - 3.060	350	25	36
CPC300	3	3	3.060 - 3.626	350	25	42
CPC350	3 1/2	3 1/2	3.626 - 4.126	350	25	46
CPC400	4	4	4.126 - 4.626	350	25	50

King Cobra




Ordering information



Cat. N°	EMT Trade Size	Rigid Con. Trade Size	Cable O.D. Range (in.)	Qty per Box	Wt./C lb
KCPC050	1/2	1/2	0.650 - 0.890	100	15
KCPC075	3/4	3/4	0.860 - 1.110	100	16
KCPC100	1	1	1.100 - 1.400	50	19
KCPC125	1 1/4	1 1/4	1.400 - 1.725	50	23
KCPC150	1 1/2	1 1/2	1.690 - 1.980	50	27
KCPC200	2	2	1.980 - 2.576	50	38
KCPC250	2 1/2	2 1/2	2.576 - 3.060	25	44
KCPC300	3	3	3.060 - 3.626	25	53
KCPC350	3 1/2	3 1/2	3.626 - 4.126	25	58
KCPC400	4	4	4.126 - 4.626	25	66

Loading Data



Design Load 1 Static Load Limit lb (kg)	Design Load 2 lb (kg)	Design Load 3 lb (kg)
350 (159)	50 (23)	50 (23)
350 (159)	50 (23)	50 (23)
350 (159)	50 (23)	50 (23)
350 (159)	50 (23)	50 (23)
350 (159)	50 (23)	50 (23)
350 (159)	50 (23)	50 (23)
350 (159)	50 (23)	50 (23)
450 (204)	50 (23)	50 (23)
450 (204)	50 (23)	50 (23)
450 (204)	50 (23)	50 (23)