
# WPLED20W RCL

Ultra-high efficiency 20 Watt wallpack. Patent Pending thermal management system. 100,000 hour L70 lifespan. 5 Year Warranty.

**LED Info Driver Info** 

Watts: 20W Type: **Constant Current** 120V: Color Temp: 5000K (Cool) 0.19A Color Accuracy: 70 208V: 0.12A L70 Lifespan: 100000 240V: 0.10A LM79 Lumens: 1,401 277\/· 0.08A Efficacy: 65 LPW Input Watts: 22W Efficiency: 93%



# **Technical Specifications**

#### **cUL Listina:**

Suitable for wet locations. Suitable for mounting within 1.2m (4ft) of the ground.

100,000-hour LED lifespan based on IES LM-80 results and TM-21 calculations.

#### Finish:

Our environmentally friendly polyester powder coatings are formulated for high-durability and long-lasting color, and contains no VOC or toxic heavy metals.

#### **Color Consistency:**

7-step MacAdam Ellipse binning to achieve consistent fixture-to-fixture color.

# **Color Stability:**

LED color temperature is warrantied to shift no more than 200K in CCT over a 5 year period.

# **Color Uniformity:**

RC's range of CCT (Correlated color temperature) follows the guidelines of the American National Standard for Specifications for the Chromaticity of Solid State Lighting (SSL) Products, ANSI C78.377-2008.

#### **Cold Weather Starting:**

The minimum starting temperature is -40°F/-40°C.

#### THD:

7.35% at 120V

### Driver:

Automatic Voltage Sensing Driver for 120-277 volts.

#### **Ambient Temperature:**

Suitable for use in 50°C (122°F) ambient temperatures.

#### Driver:

Two Multi-chip 10W high output long life LED Driver Constant Current, Class 2

### **Thermal Management:**

Integral cast aluminum mounting pad and external fins for optimal heat sinking to ensure cool operation with maximum LED life and light output.

#### **Housing:**

Precision die cast aluminum housing, lens frame and mounting plate.

#### **Two Mounting Options:**

Junction Box with 5 Conduit Entry Points and Threaded Plugs for surface mounting plus Cover Plate for mounting over 4" recessed junction box included with WPLED20 RCL.

## **Green Technology:**

RC LEDs are Mercury, Arsenic and UV free.

#### Dark Sky Approved:

The International Dark Sky Association has approved this product as a full cutoff, fully shielded luminaire.

# For use on LEED Buildings:

IDA Dark Sky Approval means that this fixture can be used to achieve LEED Credits for Light Pollution Reduction.

#### Patents:

The LPACK design is protected under patents in the U.S. Pat. D634873, Canada Pat. 133207, China Pat. ZL201030129137, Taiwan Pat. D139540 and Mexico Pat. 32491

Page 1 of 2



Email: sales@rclightingca On the web at: www.rclighting.ca Note: Specifications are subject to change without notice

Page 2 of 2

# IESNA LM-79 & IESNA LM-80 Testing:

RC LED luminaires have been tested by an independent laboratory in accordance with IESNA LM-79 and 80, and have received the Department of Energy "Lighting Facts" label.

#### Gaskets:

High Temperature Silicone.

# Warranty:

RC warrants that our LED products will be free from defects in materials and workmanship for a period of five (5) years from the date of delivery to the end user, including coverage of light output, color stability, driver performance and fixture finish.

# **Equivalency:**

The WPLED20 is Equivalent in delivered lumens to a 150W Metal Halide Wallpack.

# **HID Replacement Range:**

The WPLED20 can be used to replace 100-175W Metal Halide Wallpacks based on delivered lumens.

