

E-Z-Code®

EZL-100 Thermal Label Printer



**Won't Smear
Easy to Use**

At last, a label printer designed for electricians and the way they work. T&B's new EZL-100 Label Printer packs everything you need to make wire marking fast and simple.

- **One-touch Hotkeys** create labels instantly for Wire Wrapping, Terminal Blocks, Device Covers, Patch Panels, and Labels in a series
- **Symbols** for commonly used electrical and datacom applications including ohm, ground, phone, data and fax
- **Five Print Sizes** including XS, S, M, L and XL
- **Horizontal and Vertical** print orientation
- **Automatically Underlines 6 and 9** to prevent confusion on wire and cable
- **Memory** to automatically recall last label and stores up to eight custom labels
- **Battery Life Indicator** to warn for low battery power on the job
- **Auto-shutoff** saves battery life by turning power off after five minutes (if idle)
- **Backlit Display** can be turned on in low light conditions
- **Multiple Line Printing** permits up to four lines per label
- **Barcode Printing** of two of the most commonly used barcodes - Code 39 and 128
- **Durable/Non-smearing** thermal transfer technology
- **Multiple Power Sources** uses six "AA" batteries or AC adapter (not included)
- **Large Display** with 2-line x 15 character views (30 characters total)



Easy Bar Code Printing



Great for Rough Surface Cables



High-Visibility Print

Quality labels that stick and last

- **Flexible Nylon Material** – excellent for wire and cable wrapping on curved, textured and highly textured
- **Permanent Polyester Material** – good for general labeling on flat or textured surfaces
- **Prints on heavy duty 1/4", 3/8", 1/2" and 3/4" tapes**
- **EZ-Peel Labels** in an easy-to-load cassette

Specifications

Dimensions: 4.5" (114mm) wide x 8.3" (212mm) high x 2.8" (70mm) deep
 Weight: 2.0 lbs. (890 grams)
 Power: 9 volts DC, using 6 "AA" Batteries or AC Adapter

| Surface Applications | White Flex. Nylon | Yellow Flex. Nylon | White Perm. Polyester | Metallized Polyester |
|----------------------|-------------------|--------------------|-----------------------|----------------------|
| Wire | • | • | | |
| Cable | • | • | | |
| Curved | • | • | | |
| Smooth | • | • | • | • |
| Flat | • | • | • | • |
| Textured | • | • | • | • |
| Highly Textured | • | • | | |
| Length | 11.5' | 11.5' | 18.0' | 18.0' |
| Width | 1/2", 3/4" | 1/2", 3/4" | 3/8", 1/2", 3/4" | 3/8", 1/2", 3/4" |



Please ask your Thomas & Betts Sales Representative for more information about our quality E-Z-Code® identification products.

Ordering Information

| Cat No. | Description | Wt.Ea.(lbs) | UPC |
|----------------|-----------------------------------|-------------|--------------|
| EZL-100 | Thermal Transfer Handheld Printer | 2.00 | 786210-90086 |
| Labels | | | |
| EZ-WP38 | White Permanent Polyester 3/8" | .06 | 786210-90073 |
| EZ-WP12 | White Permanent Polyester 1/2" | .06 | 786210-90075 |
| EZ-WP34 | White Permanent Polyester 3/4" | .06 | 786210-90077 |
| EZ-MP38 | Metallic Permanent Polyester 3/8" | .06 | 786210-90078 |
| EZ-MP12 | Metallic Permanent Polyester 1/2" | .06 | 786210-90080 |
| EZ-MP34 | Metallic Permanent Polyester 3/4" | .06 | 786210-90081 |
| EZ-WN12 | White Flexible Nylon 1/2" | .06 | 786210-90082 |
| EZ-WN34 | White Flexible Nylon 3/4" | .06 | 786210-90083 |
| EZ-YN12 | Yellow Flexible Nylon 1/2" | .06 | 786210-90084 |
| EZ-YN34 | Yellow Flexible Nylon 3/4" | .06 | 786210-90085 |

Printer package includes (1) 3/4" White Nylon Quick Load Cassette Tape, Quick Start Card and User Manual. AC power adapter not included.

| Cat No. | MOQ | Suggested Resale |
|------------------|-----|------------------|
| EZL-100 | 3 | 239.99 |
| EZ-WN34 | 5 | 25.55 |
| EZ-WN12 | 5 | 23.01 |
| EZ-YN34 | 5 | 25.55 |
| EZ-YN12 | 5 | 23.01 |
| EZ-WP34 | 5 | 24.32 |
| EZ-WP12 | 5 | 21.71 |
| EZ-WP38 | 5 | 21.71 |
| EZ-MP34 | 5 | 24.32 |
| EZ-MP12 | 5 | 21.71 |
| EZ-MP38 | 5 | 21.71 |
| EZL-MERCH | 1 | 2995.70 |

Note: EXL-MERCH includes 9 – EZL-100, 12 – EZ-WN34, 12 – EZ-WP34, 6 – EZ-WN12, and 6 – EZ-WP12.

Head Office

Thomas & Betts Limited
 700 Thomas Avenue
 Saint-Jean-sur-Richelieu, Quebec
 J2X 2M9
 Tel.: (450) 347-5318
 Fax: (450) 347-1976

| Atlantic Region | Quebec Region | Ontario Region | Western Region | Thomas & Betts Limited |
|---|--|---|--|---|
| Thomas & Betts Limited 106 Chain Lake Drive Unit 2C Halifax, Nova Scotia B3S 1A8 Tel.: (902) 450-1307 Toll Free: 1-877-862-4357 Fax: (902) 450-1309 | Thomas & Betts Limited 7900 Taschereau Boulevard Building D, Suite 108 Brossard, Quebec J4X 1C2 Tel.: (450) 466-1102 Toll Free: 1-800-465-1399 Fax: (450) 466-1163 | Thomas & Betts Limited 2233 Argentia Road Suite 116 Mississauga, Ontario L5N 2X7 Tel.: (905) 858-1010 Toll Free: 1-877-291-7771 Fax: (905) 858-1080 | Thomas & Betts Limited 6531-148 th Street #1 Surrey British Columbia V3S 3C5 Tel.: (604) 598-9811 Toll Free: 1-866-540-8220 Fax: (604) 598-9840 | Thomas & Betts Limited 4836 Eleniak Road Edmonton, Alberta T6B 2S1 Tel.: (780) 424-7092 Toll Free: 1-888-664-5666 Fax: (780) 424-7093 Toll Free: 1-866-424-4082 |

www.tnb-canada.com

E-Z-Code®



EZL100-Kit



The E-Z-Code® EZL100-Kit features the EZL-100 label printer with everything you need to make wire marking fast and simple.

The EZL100-Kit features a rugged, hard-sided case, a printer, two label cassettes, a complete set of batteries, and an AC adapter. The EZL100-Kit gets quickly started and provides handy storage for your wire marking materials. If you already own the EZL-100 Printer, you may also purchase the hard-side case or any of the accessories separately. Contact your local T&B distributor about the EZL-100 Printer, kit, case and accessories. Don't forget to ask about the complete line of time-saving products offered by

Thomas & Betts.

Easy to Use and Won't Smear!



Great for Rough Surface Cables



High-Visibility Print

Simple, Accurate Wire Marking at the Touch of a Button.

- One-touch Hotkeys create labels instantly for wire wrapping, terminal blocks, device covers, patch panels, and labels in series.
- Symbols for commonly used electrical and datacom applications including ohm, ground, phone, date and fax.
- Five print sizes including XS, S, M, L and XL.
- Horizontal and vertical print orientation.
- Memory to automatically recall last label and stores up to eight custom labels.
- Large display with 2-line x 15 character views (30 characters total).

Ordering Information

| Cat. Number | Description | UPC Number |
|--------------------|---|-------------|
| EZL100-KIT | EZL100-Kit includes EZL-100 printer, EZ-MP34 and EZ-WN34 tapes, EZL-ADP adapter and batteries | 78621095275 |
| EZL100-CASE | Hard case for EZL-100 printer | 78621095276 |
| EZL-100 | Thermal Transfer Printer | 78621090086 |
| EZ-MP34 | Metallic Polyester 3/4" width Tape | 78621090081 |
| EZ-WN34 | White Nylon 3/4" width Tape | 78621090083 |
| EZL-ADP | Adapter for EZL-100 Printer 9V, 1.5A | 78621090082 |

Quality Labels That Stick and Last

- Flexible Nylon Material - excellent for wire and cable wrapping on curved, textured and highly textured surfaces.
- Permanent Polyester Material - good for general labeling on flat or textured surfaces.
- Prints on heavy duty 1/4", 3/8", 1/2" and 3/4" tapes.
- EZ-Peel Labels in an easy-to-load cassette.



Heat Shrinkable Markers For EZL-100 Printer

Heat-shrinkable sleeves are now available for T&B's EZL-100 Wire Marker Printer. Panel builders, maintenance electricians and other OEMs have the flexibility to print heat-shrink sleeves on the spot when they're needed.

The sleeves can be shrunk onto the wire or cable using a heat gun without the need for sticky adhesives. The sleeves may also be aligned and held in place on the wire before shrinking. Since the sleeves are a continuous roll, installers may select different lengths using the same cassette.

- 1/4", 3/8", 1/2" and 3/4" sizes
- Available in bright yellow and white colors
- Clear, non-smudging lettering and chemical/solvent resistance
- Flame retardant, Polyolefin material, 3:1 shrink ratio offers extra protection and insulation to the wire or cable

Meets the performance requirements of MIL-DTL-23053/5 classes 1 and 3

E-Z-Code® Heat Shrinkable Wire Markers

| Cat. Number | Description | Std. Qty. | Weight/Ea | UPC Number |
|-------------|-------------------------------|-----------|-----------|-------------|
| EZ-WHS14 | 1/4" White Heat Shrink Label | (5) | 0.06 | 78621094907 |
| EZ-WHS12 | 1/2" White Heat Shrink Label | (5) | 0.06 | 78621094846 |
| EZ-WHS38 | 3/8" White Heat Shrink Label | (5) | 0.06 | 78621094845 |
| EZ-WHS34 | 3/4" White Heat Shrink Label | (5) | 0.06 | 78621094847 |
| EZ-YHS14 | 1/4" Yellow Heat Shrink Label | (5) | 0.06 | 78621094909 |
| EZ-YHS12 | 1/2" Yellow Heat Shrink Label | (5) | 0.06 | 78621094868 |
| EZ-YHS38 | 3/8" Yellow Heat Shrink Label | (5) | 0.06 | 78621094908 |
| EZ-YHS34 | 3/4" Yellow Heat Shrink Label | (5) | 0.06 | 78621094873 |

Materials, Specifications

Material: Flame retardant polyolefin, 3:1 shrink ratio
Width: 1/4", 3/8", 1/2", 3/4" (6, 9, 12, 19 mm)
Length: 5' Continuous Roll in Cassette (1.5 M)
Colors: White and Yellow

Recommended cable diameter range: (minimum to maximum)

1/4" (6mm): .046" - .092" (1.18mm - 2.33mm)
 3/8" (9mm): .068" - .168" (1.73mm - 3.73mm)
 1/2" (12mm): .116" - .202" (2.97mm - 5.13mm)
 3/4" (19mm): .182" - .342" (4.62mm - 8.69mm)

- contact T&B Technical Services for a complete report detailing testing and competitive analysis.

Prices are subject to change without notice. All orders will be billed at prices in effect at time of shipment. Products for which standard packaging is in parenthesis ex.: (50) can be purchased only in multiples of standard packaging and multiples thereof.