


Channels and Concrete Inserts

Welded Combinations




EXAMPLES

Two A1200 channels back to back are ordered as A1202.
Two A1200 channels back to side are ordered as A1202C.

Back to back steel channel is riveted at every 4 inches.
Aluminum back to back channel are extruded profiles.
All other combinations are spot welded at every 4 inches.


End Caps and Closure Strips

A804 End Cap



Cat. No.	For Channel	Wt./C lb.
A804EG	A1200	10
	A1400 AR1600	10
B804EG	B1400 BR1600	5
C804EG	C1200	8
E804EG	E1200	15
H804	H1200	20

Safety End Cap



1-5/8 in. x 1-5/8 in. White Plasticsol

Cat. No.	For Channel	Wt./C lb.
A804NEOPWH	A1200 AR1600	1.75
	A1400	
B804NEOPWH	B1200 BR1600	5
H804NEOPWH	H1200	2


A243-1EGC End Cap



For A1200 Channel

Wt./C 16 lb.


A208




A208HDGC
A208EG
Does not include stud nut or bolts.

A208
A208SS6C
For A and AR Series channel. Wt./C 275 lb.

A213 Inside Joiner



For A1200 Series only.
Available only in GoldGalv® finish.



AB844PGC
Pre-Galvanized Closure Strip

AB844PCGY
Plastic Closure Strip
Colour: Grey

AB844PC
Plastic Closure Strip
Colour: Gold

For all channel. Standard lengths 10 ft.