

Baseplates



RX3i baseplates are available in 7, 12 and 16 slot configurations to meet the needs of your application. The RX3i Universal baseplates support hot swap capability to reduce downtime. Expansion bases are available in 5 and 10 slot versions to maximize flexibility.

	IC695CHS007	IC695CHS012	IC695CHS016	IC694CHS398	IC693CHS399	IC694CHS392	IC693CHS393
Product Name	PACSystems RX3i 7 slot high speed controller base supports only 5 serial bus slots supported. Not expandable.	PACSystems RX3i 12 slot high speed controller base supports PCI and serial bus	PACSystems RX3i 16 slot high speed controller base supports PCI and serial bus	PACSystems RX3i serial 5-slot Expansion Baseplate (serial bus only)	PACSystems RX3i serial 5-slot Remote Baseplate (serial bus only)	PACSystems RX3i serial 10-slot Expansion Baseplate (serial bus only)	PACSystems RX3i serial 10-slot Remote Baseplate (serial bus only)
Lifecycle Status	Active	Active	Active	Active	Active	Active	Active
Module Type	Universal Controller and I/O Base	Universal Controller and I/O Base	Universal Controller and I/O Base	Standard I/O	Standard I/O	Standard I/O	Standard I/O
Backplane Support	Supports both PCI and High Speed Serial	Supports both PCI and High Speed Serial.	Supports both PCI and High Speed Serial.	Supports High Speed Serial Only. No PCI support.	Supports High Speed Serial Only. No PCI support.	Supports High Speed Serial Only. No PCI support.	Supports High Speed Serial Only. No PCI support.
Module Hot Swap Support	Yes	Yes	Yes	No	No	No	No
Baseplate Option	Controller Base and Ethernet Expansion Base. No local base expansion	Controller Base and Ethernet Expansion Base	Controller Base and Ethernet Expansion Base	Expansion	Expansion	Expansion	Expansion
Distance	N/A	N/A	N/A	Up to 50 feet	Up to 700 feet	Up to 50 feet	Up to 700 feet
Number of Slots	7	12	16	5	5	10	10
Dimension (W x H x D) in. (mm)	10.43 x 5.57 x 5.80 (265 x 141.5 x 147.32)	18.01 x 5.57 x 5.80 (457.5 x 141.5 x 147.32)	23.7 x 5.57 x 5.80 (601.98 x 141.5 x 147.32)	10.43 x 5.12 x 5.59 (245 x 130 x 142)	10.43 x 5.12 x 5.59 (245 x 130 x 142)	17.44 x 5.12 x 5.59 (443 x 130 x 142)	17.44 x 5.12 x 5.59 (443 x 130 x 142)
Internal Power Used	600 mA @ 3.3 VDC; 240 mA @ 5 VDC	600 mA @ 3.3 VDC; 240 mA @ 5 VDC	600 mA @ 3.3 VDC; 240 mA @ 5 VDC	170 mA @ 5 VDC	480 mA @ 5 VDC	150 mA @ 5 VDC	460 mA @ 5 VDC



Universal Bases Power Supplies

The RX3i power supply modules simply snap in just like I/O, and they work with any model CPU. Each version provides auto-ranging so there is no need to set jumpers for different incoming power levels, and they are current limiting so a direct short will shut the power supply down to avoid damage to the hardware. Advanced diagnostics and built-in smart switch fusing are among the other performance and safety features. The multipurpose power supplies can be configured for incremental capacity or redundancy.

	IC695PSA040	IC695PSD040	IC695PSA140	IC695PSD140
Product Name	Power Supply, 120/240 VAC, 125 VDC (Can not be on the same backplane with more than one power supply)	Power Supply, 24 VDC (Can not be on the same backplane with more than one power supply)	Multipurpose Power Supply, 120/240 VAC, 125 VDC. Supports multiple multipurpose power supplies.	Multipurpose Power Supply, 24 VDC. Supports multiple multipurpose power supplies.
Lifecycle Status	Active	Active	Active	Active
Module Type	Universal Base Power Supply	Universal Base Power Supply	Universal Base Power Supply	Universal Base Power Supply
Backplane Support	Universal Backplane Only. Uses PCI Bus.	Universal Backplane Only. Uses PCI Bus.	Universal Backplane Only. Uses PCI Bus.	Universal Backplane Only. Uses PCI Bus.
Number of Slots Module Occupies on Backplane	2	1	2	1
Power Source	100-240 VAC or 125 VDC	24 VDC	100-240 VAC or 125 VDC	24 VDC
Redundant and Added Capacity Support	No	No	Yes, Up to 4 Multipurpose power supplies supported on a Universal base	Yes, Up to 4 Multipurpose power supplies supported on a Universal base
Output Source	40 watts total. 30 watts max at 3.3 VDC; 30 watts max at 5 VDC; 40 watts at 24 VDC Relay, no 24 VDC isolated available.	40 watts total. 30 watts max at 3.3 VDC; 30 watts max at 5 VDC; 40 watts at 24 VDC Relay, no 24 VDC isolated available	40 watts total. 30 watts max at 3.3 VDC; 30 watts max at 5 VDC; 40 watts at 24 VDC Relay, no 24 VDC isolated available	40 watts total. 30 watts max at 3.3 VDC; 30 watts max at 5 VDC; 40 watts at 24 VDC Relay, no 24 VDC isolated available.
Number of Redundant Power Supplies Supported	N/A	N/A	Two Multipurpose Power Supplies are supported on the Universal Base configured for redundancy	Two Multipurpose Power Supplies are supported on the Universal Base configured for redundancy