# **ECSC SERIES**




Plastic Pictogram Exit Combo Unit

# FEATURES

- Energy efficient, long-life white LEDs consuming 4.2W at normal operation
- Energy efficient, long-life white LEDs consuming 4.2W at normal operation
- Dual voltage input capability 120/347VAC
- 3.6V Nickel-Cadmium battery provides minimum 90 minutes of emergency lighting
- Fully adjustable LED glare-free lens
- 3.6V 1W long life LED light source, 6000K
- Adjustable light heads for forward or backward lighting
- Automatic, temperature compensated, pulse type charger
- Low voltage disconnect prevents over discharge of battery
- Automatic brownout protection
- Battery lock-out prevents discharge during installation
- Comes standard with three pictogram legends for direction selection
- Red LED charger monitor
- Injection-molded off-white thermoplastic ABS housing
- Fast and easy installation with snap-together design
- Ceiling, wall or end mount installation
- CSA C22.2 no.141-10 listed
- Comes standard with one (1) year warranty

# DIMENSIONS

Dimensions are approximate and subject to change





### **POWER CONSUMPTION AND UNIT RATING**

MODEL	AC SPECS			DC	SPECS
ECSC-2LEDWR	120/347VAC	0.5/0.4 A	4.2/3.6W	Ni-Cd battery	Min. 90 minutes

\*NOTE: The ECS Family cannot be combined with other Emergi-Lite® Products on the same emergency A.C. circuit.

### **ORDERING INFORMATION**

SERIES	VOLTAGE	LAMP
ECSC	Blank= 120/347VAC	-2LEDWR= 2X 1W LED

EXAMPLE: ECSC-2LEDWR

·



All information and specifications contained in this catalogue sheet are subject to change due to engineer design, errors and omissions. © 2014. Thomas & Betts Limited. All rights reserved.

