

S202UDC-K15



Miniature Circuit Breaker - S200UDC - 2P - K - 15 ampere



General Information

Extended Product Type	S202UDC-K15
Product ID	2CDS272517R0457
EAN	4016779825252
Catalog Description	Miniature Circuit Breaker - S200UDC - 2P - K - 15 ampere
Long Description	<p>System pro M compact S200UDC current limiting miniature circuit breakers are specially designed for DC applications in the scope of UL489.</p> <p>They have two different tripping mechanisms, the delayed thermal tripping mechanism for overload protection and the electromechanic tripping mechanism for short circuit protection. They are available in different characteristics (K,Z), configurations (1P,2P) and rated currents (up to 63A).The Short-circuit current rating SCCR acc. UL489 is 14 kA. The S200UDC is suitable for DC voltages up to 125 VDC (2 pole). All MCBs of the product range S200UDC comply with UL489, allowing the use for commercial and industrial applications.</p>

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85362010

Popular Downloads

Data Sheet, Technical Information	2CDC002052D0202
Instructions and Manuals	2CDC002052D0202

Dimensions

Product Net Width	35 mm
Product Net Depth / Length	69 mm
Product Net Height	85 mm
Product Net Weight	0.3 kg

Technical

Standards	UL 489
Number of Poles	2
Tripping Characteristic	K
Rated Current (I_n)	15 A
Power Loss	3.69 W

at Rated Operating Conditions per Pole 1.845 W

Rated Insulation Voltage (U _i)	acc. to IEC/EN 60664-1 440 V
Operational Voltage	Minimum 12 V DC
Rated Frequency (f)	DC Hz
Housing Material	Insulation Group I, RAL 7035
Actuator Type	Insulation group II, black, sealable
Contact Position Indication	Red ON / Green OFF
Degree of Protection	IP20
Remarks	IP40 in enclosure with cover; Please note polarity of device
Electrical Endurance	6000 AC cycle 20000 cycle
Terminal Type	Screw Terminals
Screw Terminal Type	Failsafe Bi-directional Cylinder-lift Terminal
Connecting Capacity	Busbar 10 / 10 mm ² Flexible with Ferrule 0.75 ... 16 mm ² Flexible 0.75 ... 16 mm ² Rigid 0.75 ... 25 mm ² Stranded 0.75 ... 25 mm ²
Tightening Torque	2.8 N·m
Recommended Screw Driver	Pozidriv 2
Mounting on DIN Rail	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Mounting Position	Any

Environmental

Ambient Air Temperature	Operation -25 ... +55 °C Storage -40 ... +70 °C
Resistance to Shock acc. to IEC 60068-2-27	30g / 3 shocks / 11 ms
Resistance to Vibrations acc. to IEC 60068-2-6	5g, 20 cycles at 5 ... 150 ... 5 Hz with load 0.8 In
Environmental Conditions	28 cycles with 55 °C / 90-96 % and 25 °C / 95-100 %

Technical UL/CSA

Maximum Operating Voltage UL/CSA	125 V DC
Connecting Capacity UL/CSA	Busbar 18-8 AWG Conductor 18-4 AWG
Tightening Torque UL/CSA	25 in·lb
Interrupting Rating acc. to UL1077	(125 V DC) 14 kA
Short-Circuit Current Rating (SCCR)	14 kA

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	2CDK400630D2701
Environmental Information	2CDK400030D0201
Instructions and Manuals	2CDC002052D0202

Container Information

Package Level 1 Units	5 piece
-----------------------	---------

Package Level 1 Width	105 mm
Package Level 1 Depth / Length	183 mm
Package Level 1 Height	80 mm
Package Level 1 Gross Weight	1.55 kg
Package Level 1 EAN	4016779825634

Classifications

Object Classification Code	F
ETIM 4	EC000042 - Miniature circuit breaker (MCB)
ETIM 5	EC000042 - Miniature circuit breaker (MCB)
ETIM 6	EC000042 - Miniature circuit breaker (MCB)
ETIM 7	EC000042 - Miniature circuit breaker (MCB)
eClass	7.0 27141901
UNSPSC	39121614

Accessories

Identifier	Description	Type	Quantity	Unit Of Measure
2CDS200908R0001	S2C-A1U - Arbeitsstromauslöser	S2C-A1U	1	piece
2CDS200908R0002	S2C-A2U - Arbeitsstromauslöser	S2C-A2U	1	piece
2CDS200914R0001	S2C-H6RU - Hilfskontakt	S2C-H6RU	1	piece
2CDS200917R0001	S2C-TC20U - Klemmenabdeckung	S2C-TC20U	1	piece
2CDS200924R0001	S2C-S6RU - Signal- / Hilfskontakt	S2C-S6RU	1	piece

Categories

Low Voltage Products and Systems → Modular DIN Rail Products → Miniature Circuit Breakers MCBs

