



MADE IN CANADA




FABRIQUÉ AU CANADA

Canadian made and engineered for over 30 years, **Hubbell® BANANA BOX™** are designed to provide the fastest and easiest installation in the industry. Each **BANANA BOX™** is engineered to provide the greatest amount of versatility on the market. Installation can be done using virtually any type of fastener and each box incorporates many labour saving features. A genuine **Hubbell BANANA BOX™** is distinguished by the bright yellow colour, providing high visibility when installing and wiring in low light levels.



Complementing the complete line of Banana Box™, Hubbell is proud to introduce the next generation of Stove/Dryer/Junction Box, the 2026. Exclusive design features include: larger cubic capacity of 58.5 IN (958 mL), flexible options of knock outs and NMD self clamps, inside mounting holes and external mounting holes (flange version only).



















Features	Benefits
Energy efficient vapour barrier flange models	<ul style="list-style-type: none"> <li>• Superior energy savings</li> <li>• Reduces air leakage through exterior walls</li> <li>• Eliminates need for separate vapour/air barriers</li> </ul>
Superior cubic capacity	<ul style="list-style-type: none"> <li>• Additional volume makes termination easier</li> <li>• Excellent for deeper body devices</li> </ul>
Auto depth positioning	<ul style="list-style-type: none"> <li>• Engraving at 1/2, 5/8 and 1" to ensure accurate and consistent box placement and help in reducing installation time</li> <li>• The flange box has a preset flange at 1/2"</li> <li>• The non-flanged box allows for installation in a double drywall</li> </ul>

Features	Benefits
Cable entries	<ul style="list-style-type: none"> <li>• For greater flexibility and additional time savings, the box is designed with 2 self-clamping wire entry tabs as well as 2 knock-outs 3/4" (1), 1/2" (1)</li> </ul>
Mounting holes	<ul style="list-style-type: none"> <li>• Provision for 4 Inside Mounting Holes</li> <li>• The flange box has 8 additional external mounting holes on the flange for easier installation</li> </ul>
Mounting Screws	<ul style="list-style-type: none"> <li>• Include 4 device mounting screws for additional time and cost savings</li> </ul>
Oversized nailing/screw flange	<ul style="list-style-type: none"> <li>• Resists hammer impact when nailing</li> <li>• Easier to mount on stud or joint</li> </ul>
Lightweight, rugged, non-metallic construction	<ul style="list-style-type: none"> <li>• Highly visible, easier to locate wires in low light levels</li> <li>• Withstands high impact in the coldest temperatures</li> </ul>

## PRODUCT OFFERING:

Standard BANANA BOXES	
2001R	Single-gang 18 cu.in. 
2021R	Single-gang 18 cu.in. 
2002R	2-gang 37 cu.in. 
2003R	3-gang 54 cu.in. 
2026R	Stove/Dryer/Junction 58.5 cu.in. 
2027R	Ceiling 27.15 cu.in. 

Specialty Boxes	
2016R	Trailer Box Single-gang 17 cu.in. 
2014R	Fast Wire Clamp for Trailer Box 

Flanged Vapour/Air Barrier BANANA BOXES		
2011FBAR	Single-gang 18 cu.in.	
2002FBAR	2-gang 37 cu.in.	
2003FBAR	3-gang 54 cu.in.	
2026FBAR	Stove/Dryer/Junction 58.5 cu.in.	
2006FR	Stove/Dryer/Junction 58.5 cu.in.	
2027FBAR	Ceiling 27.15 cu.in.	